

## T9 Circline Plus

FC40/830  
0001966



### Product features

- T9 Circline Plus



## PRODUCT OVERVIEW

Product name	FC40/830
Technology	Fluorescent
Watt (Rated) (W)	40
Lamp shape	Ring
Type	T9 Circline Plus
Cap/Base	G10q
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940728
E-number Norway	3845366
Luminous flux (lm)	2900
Colour temperature (K)	3000
Light colour	Warm White
Colour Code	830
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Photobiological Risk Group	Not applicable
Wattage (W)	40
Product Voltage (V)	115
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	12000
Product EAN number	5410288019666

## DATA TABLE

### General data

Product name	FC40/830
Technology	Fluorescent
Watt (Rated) (W)	40
Lamp shape	Ring

## T9 Circline Plus

FC40/830

0001966

Type	T9 Circline Plus
Cap/Base	G10q
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940728
E-number Norway	3845366

### Optical data

Luminous flux (lm)	2900
Luminous flux (Rated) (lm)	2900
Ambient temperature for maximum luminous flux (°C)	25
Colour temperature (K)	3000
Light colour	Warm White
Colour Code	830
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Adjustable chromaticity	N
Photobiological Risk Group	Not applicable
Rated lumen maint. factor (%) at 4000 h 50Hz	78
Rated lumen maint. factor (%) at 6000 h 50Hz	77
Rated lumen maint. factor (%) at 8000 h 50Hz	76
Rated lumen maint. factor (%) at 12000 h 50Hz	74

### Electrical data

Wattage (W)	40
Watt (Rated) - High frequency (W)	40
Current (A)	0.415
Product Voltage (V)	115
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Lamp Energy Label (class)	G
kWh per 1000 hours burning time	44

### Lifetime data

Average life (Nominal) (h)	12000
Average life (Rated) (h)	12000
Rated survival factor (%) at 2000 h 50Hz	99
Rated survival factor (%) at 4000 h 50Hz	97
Rated survival factor (%) at 6000 h 50Hz	92
Rated survival factor (%) at 8000 h 50Hz	85

## T9 Circline Plus

FC40/830  
0001966

Rated survival factor (%) at 12000 h 50Hz	50
---	----

### Physical data

Nominal Product Height (mm)	29
Nominal Product Diameter (mm)	400
Max. Length base to base (mm) - A	400
Length base to pin Min-Max (mm) - B	400
Max. Lamp Diameter (mm) - D	29
Weight (kg)	0.234


### Packaging

Single packaging type	Carton
Product EAN number	5410288019666
Packaging single length / height (cm)	28.5
Packaging single width (cm)	40.5
Packaging single depth (cm)	3.1
DUN14 (outer)	15410288019663
Units per outer package	12
Packaging outer length / height (cm)	43.0
Packaging outer width (cm)	42.3
Packaging outer depth (cm)	42.7


### Safety data

Lamp mercury content (mg)	3.5
Breakage cleaning instructions	Applicable
Special purpose lamp	No
Suitable for household illumination	Yes


## PHOTOMETRY



## TECHNICAL DRAWINGS



T9 Circline Plus  
FC40/830  
0001966



**40**  
kWh/1000h



# SYLVANIA


T9 Circline Plus

FC40/830

0001966



0001966



**40**  
kWh/1000h



2019/2015