

ERSADUR longlife soldering tip series 212

- ANALOG 20 A
- DIGITAL 2000 A with MICRO TOOL soldering iron
- MICRO-CON 60 iA with MICRO TOOL soldering iron
- REWORK 80
- SMD 8000
- SMT UNIT 60 A/AS
- TWIN 40 A/AS
- TWIN 80 A with MICRO TOOL soldering iron



<p>0212SDF</p> <p>pencil point, 0.2 mm ϕ</p>	<p>0212BDF</p> <p>pencil point, 0.4 mm ϕ</p>	<p>0212ADLF*</p> <p>pencil point, 1.0 mm ϕ, reinforced</p>	<p>0212CDF</p> <p>chisel-shaped, 1.0 mm</p>
<p>0212EDLF</p> <p>chisel-shaped, 1.8 mm</p>	<p>0212KDLF*</p> <p>chisel-shaped, 1.8 mm, extended</p>	<p>0212FDLF</p> <p>chisel-shaped, 2.2 mm, reinforced</p>	<p>0212GD</p> <p>chisel-shaped, 3.2 mm, reinforced</p>
<p>0212VD</p> <p>chisel-shaped, 5.0 mm, reinforced</p>	<p>0212RD</p> <p>pencil point, 0.2 mm ϕ, bent</p>	<p>0212ID</p> <p>bent, 0.6 mm ϕ, reinforced</p>	<p>0212ND</p> <p>angled face, 2.0 mm, reinforced</p>
<p>0212WD</p> <p>MiniMicroWell, 1.6 mm ϕ</p>	<p>0212MS</p> <p>MicroWell, 2.1 mm ϕ</p>	<p>0212OD</p> <p>SolderWell, 3.0 mm ϕ</p>	

Pairs of desoldering tips, series 462

- i-CON 1V/2 V
 - i-CON VARIO 2
 - i-CON VARIO 4
- each with CHIP TOOL VARIO



<p>0462PDLF005</p> <p>pencil point, 0.5 mm ϕ</p>	<p>0462CDF010</p> <p>chisel-shaped, 1 mm</p>	<p>0462CDF018</p> <p>chisel-shaped, 1.8 mm</p>	<p>0462SDF002</p> <p>pencil point, 0.2 mm ϕ, bent</p>
<p>0462MDLF007</p> <p>chisel-shaped, 0.7 mm, bent</p>	<p>0462MDLF015</p> <p>chisel-shaped, 1.5 mm, bent</p>	<p>0462FDLF060</p> <p>desoldering tips, 6 mm</p>	