

WiFi data logger system

testo Saveris 2 – temperature and humidity monitoring re-thought

Data transfer by wireless LAN

All measurement data always available, anywhere, on any instrument

Alarms when limit values are violated

With testo Saveris 2 App for easier configuration, push alarms and WiFi range analysis

Cost-free online data store (Testo Cloud)



testo Saveris 2 App
for free download



The testo Saveris 2 WiFi data logger system is the modern solution for monitoring temperature and humidity values in storerooms and work rooms.

Installing the system is child's play, and can be carried out either via a browser, or with the testo Saveris 2 App. The WiFi data loggers reliably record temperature and humidity at adjustable intervals and transmit the measurement values by wireless LAN to the Testo Cloud.


The stored readings can be analyzed at any time, anywhere, using an internet-enabled smartphone, tablet or PC.

Limit value violations are immediately reported by e-mail, optionally by SMS or via the testo Saveris 2 App as a push notification. This allows critical processes to be kept always under control, even if you are not on site.

The long battery life additionally ensures that the testo Saveris 2 system needs to be serviced only rarely.

Temperature and humidity monitoring re-invented.

The data logger system testo Saveris 2 allows you full control of ambient conditions at all times - no matter where you are.



Ordering data WiFi data loggers

testo Saveris 2-T1

testo Saveris 2-T1; WiFi data logger (wireless LAN) with display and internal NTC temperature sensor, incl. USB cable, wall bracket, batteries and calibration certificate



Order no. 0572 2031

testo Saveris 2-H1

testo Saveris 2-H1; WiFi data logger (wireless LAN) with display for measuring temperature and relative humidity, internal capacitive sensor incl. USB cable, wall bracket, batteries and calibration certificate



Order no. 0572 2034

testo Saveris 2-T2

testo Saveris 2-T2; WiFi data logger (wireless LAN) with display for measuring temperature, two connections for external NTC temperature probes or door contacts, incl. USB cable, wall bracket, batteries and calibration certificate



Order no. 0572 2032

testo Saveris 2-H2

testo Saveris 2-H2; WiFi data logger (wireless LAN) with display for measuring temperature and relative humidity, connection for one external humidity probe, incl. USB cable, wall bracket, batteries and calibration certificate



Order no. 0572 2035

testo Saveris 2-T3

testo Saveris 2-T3; WiFi data logger (wireless LAN) with display for measuring temperature, two connections for external TC temperature probes (Types K, T, J), incl. USB cable, wall bracket, batteries and calibration certificate



Order no. 0572 2033

testo Saveris 2 - set for temperature monitoring in refrigerators

testo Saveris 2-T2; WiFi data logger (wireless LAN) with display for measuring temperature, two connections for external NTC temperature probe or door contact, incl. two ribbon cable temperature probes, two temperature simulation flasks for filling with glycol, USB cable, wall bracket, batteries and calibration protocol



Order no. 0572 2103



testo Saveris 2 App

With the App for iOS and Android, you now operate the wireless LAN data logger system testo Saveris 2 even more easily and flexibly.

More efficient commissioning*:

- Easy recognition and selection of the WiFi network
- Faster parallel commissioning of several loggers

Easy network analysis*:

- Test the strength and range of your WiFi network
- Create and send status reports

Reliable alarm functions*:

- Push notifications of limit value violations
- Combinable with e-mail or SMS alarms

*These functions are available only in the Android version of the testo Saveris 2 App.

Please note that in order to use the WiFi data logger system testo Saveris 2, a WiFi data logger, registration in the Testo Cloud (www.saveris.net) and a wireless LAN-capable network are absolutely necessary.




testo Saveris 2 Cloud

Our packages

The Testo Cloud is the central operating element for setting up your testo Saveris 2 system. Here you can configure your WiFi data loggers, set limit value alarms and evaluate your measurement data. In order to have access to the Testo Cloud, you must first register at www.saveris.net.

Depending on the desired range of functions, you have a choice between the free Basic and more extensive Advanced functionality for use of the Testo Cloud.

In both packages, you have access to an API interface, in order to export measurement data to your systems.

	Basic 	Advanced			
Measuring cycle	15 min. (fixed)	1 min to 24 h (flexible)			
Communication rate	15 min. (fixed)	1 min to 24 h (flexible)			
Data storage	max. 3 months	max. 2 years			
Reports	manual (.pdf/.csv)	manual (.pdf/.csv) automatic (.pdf/.csv)			
Data analysis	For one measurement channel in each case	For up to 10 measurement channels simultaneously			
Number of users per account	1	10			
Number of WiFi data loggers per account	Unlimited	Unlimited			
Alarm options	Upper/lower alarm limits	<ul style="list-style-type: none"> Upper/lower alarm limits Alarm delay Time-controlled alarms 			
System notifications	<ul style="list-style-type: none"> Notification of low battery WiFi connection interrupted Power supply interrupted 	<ul style="list-style-type: none"> Notification of low battery WiFi connection interrupted Power supply interrupted 			
E-mail alarm	Yes	Yes			
SMS alarm	No	<ul style="list-style-type: none"> incl. 25 SMS per logger and year Option of purchasing additional SMS packages 			
		<table border="1"> <tr> <td>12-month licence order no. 0526 0735</td> <td>24-month licence order no. 0526 0732</td> <td>36-month licence order no. 0526 0733</td> </tr> </table>	12-month licence order no. 0526 0735	24-month licence order no. 0526 0732	36-month licence order no. 0526 0733
12-month licence order no. 0526 0735	24-month licence order no. 0526 0732	36-month licence order no. 0526 0733			

Accessories

Other accessories	Order no.
Door contact for WiFi data logger testo Saveris 2-T2	0572 2152
Mains unit for testo Saveris 2 WiFi data loggers	0572 2020
Batteries for wireless probes (4 x AA alkali manganese batteries)	0515 0414
Batteries for operating WiFi data loggers testo Saveris 2 below -10 °C (4 x Energizer L91 Photo-Lithium)	0515 0572
Magnetic adapter for testo Saveris 2 wall bracket, for attachment to magnetic surfaces	0554 2001
ISO temperature calibration certificate; temperature probe; calibration points -18 °C, 0 °C, +40 °C; per channel/instrument	0520 0153
DAkkS temperature calibration certificate; temperature probe; calibration points -18 °C, 0 °C, +40 °C; per channel/instrument	0520 0262
ISO humidity calibration certificate; calibration points 11.3 %RH and 75.3 %RH at +25°C/+77 °F; per channel/instrument	0520 0076
DAkkS humidity calibration certificate; humidity probe; calibration points 11.3 %RH and 75.3 %RH at +25°C; per channel/instrument	0520 0246

Technical data







WiFi data logger	testo Saveris 2-T1	testo Saveris 2-T2	testo Saveris 2-T3			testo Saveris 2-H1	testo Saveris 2-H2
Temperature measurement							
Sensor type	NTC internal	NTC	TC Type K	TC Type J	TC type T	NTC internal	NTC
Measuring range	-30 to +50 °C	-50 to +150 °C	-195 to +1350 °C	-100 to +750 °C	-200 to +400 °C	-30 to +50 °C	Measuring range and accuracy correspond to probe
Accuracy ± 1 digit	± 0.5 °C	± 0.3 °C	±(0.5 + 0.5 % of m.v.) °C			± 0.5 °C	
Resolution	0.1 °C						
Humidity measurement							
Measuring range	-					0 to 100 %RH	Measuring range and accuracy correspond to probe
Accuracy	-					±2 %RH	
Resolution	-					0.1% RH	
Temperature/humidity measurement via external probes							
Connection of external probes	-	External temperature probes	External temperature probes			-	External humidity/temperature probes
Operating temperature	-30 to +50 °C						
Storage temperature (without batteries)	-40 to +70 °C						
Protection class	IP 65	IP65	IP54			IP30	IP54
Measuring cycle	Basic: 15 min. (fixed) / Advanced: 1 min to 24 h (flexible)						
Communication rate	Basic: 15 min. (fixed) / Advanced: 1 min to 24 h (flexible)						
Memory	10000 readings/channel						
Standards / permits	EN 12830	EN 12830	-				
Battery life	24 months at +25 °C and 15 min measurement and standard communication rate at -30 °C and 15 min measurement and communication rate with Energizer batteries 0515 0572						
Voltage supply	4 x AA AIMn Mignon batteries; mains unit optional; for temperatures under -10 °C please use Energizer batteries 0515 0572						
Dimensions	95 x 75 x 30.5 mm						
Weight (incl. batteries)	240 g						
Door contact	No	Optional	No				
Communication							
WiFi (wireless LAN)	Signal transmission: wireless; frequency band: 2.4 GHz; supported wireless LAN standards: IEEE 802.11 b/g/n and IEEE 802.1X Possible encryption methods: without encryption, WEP, WPA, WPA2, WPA2 Enterprise The data loggers communicate via the standard protocol MQTT and are SNTP time synchronization-capable.						

Temperature probes for testo Saveris 2-T2

Probe type	Dimensions probe shaft/ probe shaft tip	Measuring range	Accuracy	t ₉₉	Order no.
Stump probe, IP 54		-20 to +70 °C	±0.2 °C (-20 to +40 °C) ±0.4 °C (+40.1 to +70 °C)	15 s	0628 7510
Stationary probe with aluminium sleeve, IP 65, fixed cable 2.4 m		-30 to +90 °C	±0.2 °C (0 to +70 °C) ±0.5 °C (remaining meas. range)	190 s	0628 7503
Accurate immersion/penetration probe, cable length 6 m, IP 67, fixed cable		-35 to +80 °C	±0.2 °C (-25 to +74.9 °C) ±0.4 °C (remaining meas. range)	5 s	0610 1725
Surface probe fixed cable, 2 m		-50 to +80 °C	±0.2 °C (0 to +70 °C)	150 s	0628 7516
Penetration probe NTC with ribbon cable, cable length 2 m, IP 54, fixed cable,		-40 to +125 °C	±0.5 % of m.v. +100 to +125 °C) ±0.2 °C (-25 to +80 °C) ±0.4 °C (remaining meas. range)	8 s	0572 1001
Pipe wrap probe with Velcro tape for pipe diameters up to max. 75 mm, Tmax. +75 °C, fixed cable		-50 to +70 °C	±0.2 °C (-25 to +70 °C) ±0.4 °C (-50 to -25.1 °C)	60 s	0613 4611
External temperature probe 12 mm, plug-in, without cable		-30 to +50 °C	±0.2 °C (-30 to +50 °C)		0572 2153



More probes at www.testo.com!

Temperature probes for testo Saveris 2-T3

Probe type	Dimensions probe shaft/ probe shaft tip	Measuring range	Accuracy	t ₉₉	Order no.
Stationary probe with stainless steel sheath, TC Type K	 40 mm Ø 6 mm Connection: Fixed cable 1.9 m	-50 to +205 °C	Class 2*	20 s	0628 7533
Penetration probe TC with ribbon cable, Type K, cable length 2 m, IP 54	 60 mm Ø 5 mm 30 mm Ø 3.6 mm	-40 to +220 °C	Class 1	7 s	0572 9001
Magnetic probe, adhesive power approx. 10 N, with magnets, for higher temperatures, for measurements on metal surfaces, TC Type K	 75 mm Ø 21 mm Connection: Fixed cable 1.6 m	-50 to +400 °C	Class 2*		0602 4892
Pipe clamp probe for pipe diameters 5 to 65 mm, with replaceable measuring head, measuring range short-term up to +280 °C, TC Type K	 Connection: Fixed cable 1.2 m	-60 to +130 °C	Class 2*	5 s	0602 4592
Pipe wrap probe with Velcro tape, for measuring temperatures on pipes with diameters up to max. 120 mm, Tmax +120 °C, TC Type K	 395 mm 20 mm Connection: Fixed cable 1.5 m	-50 to +120 °C	Class 1*	90 s	0628 0020
Flexible, low-mass immersion measurement tip, ideal for measurements in small volumes such as Petri dishes or for surface measurements (e.g. fixed with adhesive tape), TC Type K, 2 m, FEP-insulated thermal wire, temperature-proof to 200 °C, oval cable with dimensions: 2.2 mm x 1.4 mm	 Ø 0.25 mm 500 mm	-200 to +1000 °C	Class 1*	1 s	0602 0493

*Acc. to norm EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (Type K), Class 2 to -40 to +1200 °C (Type K), Class 3 to -200 to +40 °C (Type K)

Humidity/temperature probes for testo Saveris 2-H2

Probe type	Dimensions probe shaft/ probe shaft tip	Measuring range	Accuracy	Order no.
Humidity/temperature probe 12 mm, fixed cable, cable length 1.3 m		-30 to +70 °C 0 to 100 %RH	± 0.3 °C ± 2 %RH at +25 °C (2 to 98 %RH) ± 0.03%RH/K ± 1 digit	0572 2155
External humidity/temperature probe 12 mm, plug-in, without cable	 105 mm Ø 20 mm	-30 to +50 °C 0 to 100 %RH	± 0.3 °C ± 2 %RH	0572 2154

More probes at www.testo.com!

