

Bandsaw blades, bi-metal, bulk stock, type UNI MAX PRO 10°
 Universal series use -1300 N/mm² medium cross-sections, thick-walled solid material pipes



Application

Cutting of solid material, beams and profiles with medium cross-sections in steel, stainless steel, cast iron and non-ferrous metals.

Advantage

- Positive tooth geometry ensures a soft cut with a long service life on production bandsaws.
- Microfinishing technology ensures a long service life and reduces the running-in of bandsaw blades.



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	80	40	25	20	20			65	65	40	40			60					

Art. No.	14044 195
Length	2835 mm
Width	27 mm
Thickness	0.9 mm
Type	UNI MAX 10° Pro
Min./max. contact length of full material	50-150 mm
Number of teeth per inch	3/4
Min./max. contact length of profiles	5-50 mm

EAN-Code

4050293382013