

■ Features :

- Universal AC input / Full range
- Low leakage current <250 μ A
- Protections: Short circuit / Overload / Over voltage
- Cooling by free air convection
- Medical safety approved (2 x MOPP between primary to secondary)
- 100% full load burn-in test
- Fixed switching frequency at 45KHz
- 3 years warranty




SPECIFICATION

| MODEL | | MPT-65A | | | MPT-65B | | | MPT-65C | | |
|--------------------------|---|---|------------|----------|---------------------------------|------------|----------|----------|------------|----------|
| OUTPUT | OUTPUT NUMBER | CH1 | CH2 | CH3 | CH1 | CH2 | CH3 | CH1 | CH2 | CH3 |
| | DC VOLTAGE | 5V | 12V | -5V | 5V | 12V | -12V | 5V | 15V | -15V |
| | RATED CURRENT | 5.5A | 2.5A | 0.5A | 5.5A | 2.5A | 0.5A | 5.5A | 2A | 0.5A |
| | CURRENT RANGE | 0.4 ~ 7A | 0.2 ~ 3.2A | 0 ~ 0.7A | 0.4 ~ 7A | 0.2 ~ 3.2A | 0 ~ 0.7A | 0.4 ~ 7A | 0.2 ~ 2.6A | 0 ~ 0.7A |
| | RATED POWER | 60W | | | 63.5W | | | 65W | | |
| | OUTPUT POWER (max.) | 72W with 18CFM min. Forced air convection | | | | | | | | |
| | RIPPLE & NOISE (max.) Note.2 | 60mVp-p | 120mVp-p | 60mVp-p | 60mVp-p | 160mVp-p | 100mVp-p | 60mVp-p | 180mVp-p | 100mVp-p |
| | VOLTAGE ADJ. RANGE | CH1:4.5 ~ 5.5V | | | | | | | | |
| | VOLTAGE TOLERANCE Note.3 | ±4.0% | +10,-7% | ±5.0% | ±4.0% | +10,-7% | ±5.0% | ±4.0% | +10,-7% | ±5.0% |
| | LINE REGULATION | ±1.0% | ±2.0% | ±1.0% | ±1.0% | ±2.0% | ±1.0% | ±1.0% | ±2.0% | ±1.0% |
| | LOAD REGULATION | ±3.0% | ±4.0% | ±1.0% | ±3.0% | ±4.0% | ±1.0% | ±3.0% | ±4.0% | ±1.0% |
| | SETUP, RISE TIME | 800ms, 20ms/230VAC | | | 800ms, 20ms/115VAC at full load | | | | | |
| | HOLD UP TIME (Typ.) | 80ms/230VAC | | | 12ms/115VAC at full load | | | | | |
| INPUT | VOLTAGE RANGE | 90 ~ 264VAC | | | 127 ~ 370VDC | | | | | |
| | FREQUENCY RANGE | 47 ~ 440Hz | | | | | | | | |
| | EFFICIENCY(Typ.) | 74% | | | 74% | | | 74% | | |
| | AC CURRENT (Typ.) | 1.6A/115VAC | | | 1A/230VAC | | | | | |
| | INRUSH CURRENT (Typ.) | COLD START 20A/115VAC | | | 40A/230VAC | | | | | |
| | LEAKAGE CURRENT Note.7 | Earth leakage current < 250 μ A/264VAC , Touch current < 60 μ A/264VAC | | | | | | | | |
| PROTECTION | OVERLOAD | 73 ~ 95W rated output power Protection type : Hiccup mode, recovers automatically after fault condition is removed | | | | | | | | |
| | OVER VOLTAGE | 5.75 ~ 6.75VDC on CH1 Protection type : Hiccup mode, recovers automatically after fault condition is removed | | | | | | | | |
| ENVIRONMENT | WORKING TEMP. | -10 ~ +55℃ (Refer to "Derating Curve") | | | | | | | | |
| | WORKING HUMIDITY | 20 ~ 90% RH non-condensing | | | | | | | | |
| | STORAGE TEMP., HUMIDITY | -20 ~ +85℃, 10 ~ 95% RH | | | | | | | | |
| | TEMP. COEFFICIENT | ±0.04%/℃ (0 ~ 50℃) on +5V output | | | | | | | | |
| | VIBRATION | 10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes | | | | | | | | |
| SAFETY & EMC (Note 4) | SAFETY STANDARDS | ANSI/AAMI ES60601-1, TUV EN60601-1, IEC60601-1 approved | | | | | | | | |
| | WITHSTAND VOLTAGE | I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:0.5KVAC 1min. | | | | | | | | |
| | ISOLATION RESISTANCE | I/P-O/P, I/P-FG:100M Ohms / 500VDC / 25℃ / 70% RH | | | | | | | | |
| | EMC EMISSION | Compliance to EN55011 (CISPR11) Class B, EN61000-3-2,-3 | | | | | | | | |
| | EMC IMMUNITY | Compliance to EN61000-4-2,3,4,5,6,8,11, EN60601-1-2, medical level, criteria A | | | | | | | | |
| OTHERS | MTBF | 275.1Khrs min. MIL-HDBK-217F (25℃) | | | | | | | | |
| | DIMENSION | 127*76*42mm (L*W*H) | | | | | | | | |
| | PACKING | 0.27Kg; 54pcs/16.8Kg/1.35CUFT | | | | | | | | |
| NOTE | 1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25℃ of ambient temperature. 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. 3. Tolerance : includes set up tolerance, line regulation and load regulation. 4. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com) 5. Mounting holes M1 and M2 should be grounded for EMI purposes. 6. Heat Sink HS1,HS2 can not be shorted. 7. Touch current was measured from primary input to DC output. | | | | | | | | | |

Mechanical Specification

Unit:mm



AC Input Connector (CN1) : Molex 5277-02 or equivalent


| Pin No. | Assignment | Mating Housing | Terminal |
|---------|------------|--------------------------|--------------------------|
| 1 | AC/N | Molex 5195 or equivalent | Molex 5194 or equivalent |
| 2 | AC/L | | |

⚠ HS1,HS2 can not be shorted


DC Output Connector (CN2) : Molex 5273-06 or equivalent

| Pin No. | Assignment | Mating Housing | Terminal |
|---------|------------|--------------------------|--------------------------|
| 1 | +V | Molex 5195 or equivalent | Molex 5194 or equivalent |
| 2,3 | +5V | | |
| 4,5 | COM | | |
| 6 | -V | | |

Block Diagram



Derating Curve



Static Characteristics

