


OBF507



Fibre-optic amplifier

OBF-FAKG/T/AS



- 1 mounting on DIN rail
2 setting pushbuttons



Product characteristics

Type of light	red light
Housing	rectangular
Dimensions [mm]	36 x 15 x 60

Application

Design	Fibre-optic amplifiers for glass fibre optics, for fibre optics with metal sheath, FE/FT-50
--------	---

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 50
Protection class	III
Reverse polarity protection	yes
Type of light	red light

OBF507



Fibre-optic amplifier

OBF-FAKG/TIAS

Outputs				
Electrical design		PNP/NPN; (automatic load detection PNP/NPN)		
Output function		light-on/dark-on mode; (programmable)		
Max. voltage drop switching output DC	[V]	2.5		
Permanent current rating of switching output DC	[mA]	100		
Switching frequency DC	[Hz]	1000		
Short-circuit protection		yes		
Type of short-circuit protection		pulsed		
Overload protection		yes		
Time function	[s]	0.001...0.09		
Detection zone				
Range	[m]	0...1; (Through-beam sensor)		
Range	[mm]	0...150; (Diffuse reflection sensor)		
Range adjustable		yes		
Operating conditions				
Ambient temperature	[°C]	-25...60		
Protection		IP 65		
Tests / approvals				
EMC		EN 60947-5-2		
MTTF	[years]	837		
Mechanical data				
Weight	[g]	67		
Housing		rectangular		
Dimensions	[mm]	36 x 15 x 60		
Materials		PPE modified		
Lens alignment		side lens		
Displays / operating elements				
Display	switching status	1 x LED, yellow		
	operation	1 x LED, green		
	unsafe zone	1 x LED, red		
	excess gain	4 x LED, green		
Remarks				
Remarks	light-on mode corresponds to the NC output function for through-beam fibre optics			
	corresponds to the NO output function for diffuse-reflection fibre optics			
	dark-on mode corresponds to the NO output function for through-beam fibre optics			
	corresponds to the NC output function for diffuse-reflection fibre optics			
Pack quantity	1 pcs.			
Electrical connection				
Connector: 1 x M8				

Fibre-optic amplifier

OBF-FAKG/T/AS

