

Product type designation

MM FO CORD LC/LC, 50/125

Product description

Multimode glass fiber-optic cable, preassembled
MM FO CORD LC/LC; 50/125; PREASSEMBLED WITH 2X LC
DUPLEX CONNECTORS; LENGTH 1.0 M



Figure similar

Suitability for use	Cable for applications in the control cabinet
Version of the assembled FO cable	Assembled with 2x LC DUPLEX connectors
Cable designation	I-V(ZN)H 2x50/125 OM2
Cable length	1 m

Optical data

Damping ratio per length	
<ul style="list-style-type: none"> • at 850 nm / maximum • at 1300 nm / maximum 	<p>3.5 dB/km</p> <p>1.5 dB/km</p>
Bandwidth length product	
<ul style="list-style-type: none"> • at 850 nm • at 1300 nm 	<p>500 GHz·m</p> <p>1300 GHz·m</p>

Mechanical data

Number of fibers / per FOC core	1
Number of FO cores / per FOC cable	2
Version of the FO conductor fiber	Multi-mode gradient fiber 50/125 µm, OM 2
Design of the FOC core	Fixed core
Outer diameter	
<ul style="list-style-type: none"> • of the optical fibers • of the optical fiber sheath • of the FOC core sheath 	<p>50 µm</p> <p>125 µm</p> <p>2.8 mm</p>
Width / of cable sheath	5.9 mm
Thickness / of cable sheath	2.8 mm
Material	

<ul style="list-style-type: none"> • of the fiber-optic cable core • of the optical fiber sheath • of the FOC core sheath • of the fiber-optic cable sheath • of the strain relief 	Quartz glass Quartz glass FR-LSZH LSZH Aramid fibers
Color	
<ul style="list-style-type: none"> • of the FOC core sheath 	Green/green
Bending radius	
<ul style="list-style-type: none"> • with single bend / minimum permissible 	42 mm
Tensile load / during operation / maximum	500 N
Continuous lateral force per length	100 N/cm
Weight per length	19 kg/km

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport • during installation 	-20 ... +70 °C -25 ... +70 °C -25 ... +70 °C -10 ... +70 °C
Burning behavior	Flame-resistant acc. to IEC 60332-3-22 (Cat. A)
Protection class IP	IP20

Product properties, functions, components / general

Product property	
<ul style="list-style-type: none"> • halogen-free • silicon-free 	Yes Yes
Product component / Rodent protection	No

Standards, specifications, approvals

Certificate of suitability	
<ul style="list-style-type: none"> • RoHS conformity 	Yes

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> • to website: Selector SIMATIC NET SELECTION TOOL • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx Download Manager • to website: Industry Online Support 	http://www.siemens.com/snst http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/automation/net/catalog http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified: 16.03.2015