

SCREW RING GAUGES

Description

Norms: DIN 13

Applications

Thread Ring Gauge hardened steel, ground and lapped With „Go“ and „No-Go“ thread rings
Dimensions for thread

Strong points

Metric Threads Go thread ring No-Go thread ring



Characteristics

MDM	Nominal diameter (inch)
13828990	
13828991	M1,6X0,35
13829294	M2X0,40
13829295	M2X0,40
13829296	M2,5X0,45
13829297	M2,5X0,45
13828992	M3X0,50
13828993	M3X0,50
13828994	M4X0,70
13828995	M4X0,70
13828996	M5X0,80
13828997	M5X0,80
13828998	M6X1,00
13828999	M6X1,00
13829000	M7X1,00
13829001	M7X1,00
13829002	M8X1,25
13829003	M8X1,25
13829004	M9X1,25
13829005	M9X1,25
13829006	M10X1,50
13829007	M10X1,50
13829008	M11X1,50
13829009	M11X1,50
13829010	M12X1,75
13829011	M12X1,75
13829012	M14X2,00
13829013	M14X2,00
13829014	M16X2,00
13829015	M16X2,00
13829016	M18X2,50
13829017	M18X2,50
13829018	M20X2,50
13829019	M20X2,50
13829020	M22X2,50
13829021	M22X2,50
13829022	M24X3,00
13829023	M24X3,00
13829024	M27X3,00
13829025	M27X3,00
13829026	M30X3,50
13829027	M30X3,50