
218-Y/H03VV-F BS EN 50525-2-11 Flexible Cable





RoHS Compliant

Application:

Light duty cable for use in domestic premises, kitchens and offices. For use with light portable appliances such as radios, table lamps and office equipment.

Cable Standards:

BS EN 50525-2-11 (previously BS 6500, CENELEC HD21.5), VDE 281, BS EN/IEC 60332-1-2

Construction:

Conductor : Class 5 flexible stranded copper conductor according to BS EN 60228 (previously BS 6360)

Insulation : PVC (Polyvinyl Chloride) Type TI2 according to BS EN 50363
Sheath : PVC (Polyvinyl Chloride) Type TM2 according to BS EN 50363

Characteristics:

Voltage Rating (Uo/U) : 300/300V

Temperature Rating : Flexed: -5°C to +70°C

Min. Bending Radius : Flexed: 6 × overall diameter

Core Identification : 2 core: Blue & Brown

3 core: Blue, Brown & Green/Yellow

Sheath Colour : White

Electrical Characteristics

Current Carrying Capacity and Mass Supportable

Nominal Cross	Current Carry	ing Capacity	May Maca Supportable by Twin Flevible Cord
Sectional Area mm ²	Single-Phase AC Amps	Three-Phase AC Amps	Max. Mass Supportable by Twin Flexible Cord kg
0.5	3	3	2
0.75	6	6	3

The above table is in accordance with Table 4F3B of the 17th Edition of IEE Wiring Regulations.

Voltage Drop

Nominal Cross Sectional Area mm²	DC or Single-Phase AC mV/A/m	Three-Phase AC mV/A/m	
0.5	93	80	
0.75	62	54	

Conductor operating temperature: 60°C

The above table is in accordance with Table 4F3B of the 17th Edition of IEE Wiring Regulations.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



18/06/20 V1.0

218-Y/H03VV-F BS EN 50525-2-11 Flexible Cable



Conductors:

Class 5 Flexible Stranded Copper Conductors for Multi-Core Cables

Nominal Cross	Max. Diameter of Wires in Conductor	Max. Resistance of Conductor at 20°C	
Sectional Area mm ²	mm	Plain Wires Ω/km	
0.5	0.21	39	
0.75	0.21	26	

The above table is in accordance with BS EN 60228 (previously BS 6360)

De-Rating Factors:

60°C Thermoplastic or Thermosetting Insulated Cords

Air Temperature	35°C	40°C	45°C	50°C	55°C
De-Rating Factor	0.91	0.82	0.71	0.58	0.41

Dimensions:

Part Number	No. of Cores	Nominal Cross Sectional Area mm ²	Max. No. of Strands × Strand Size	Nominal Thickness of Insulation mm	Nominal Thickness of Sheath mm	Nominal Overall Diameter mm	Nominal Weight kg/km
PP-2182Y-0.75MMWHT	2	0.75	24 × 0.19mm	0.5	0.6	5.5	46
PP-2183Y-0.50MMWHT	3	0.5	16 × 0.19mm	0.5	0.6	5.3	44
PP-2183Y-0.75MMWHT	3	0.75	24 × 0.19mm	0.5	0.6	5.8	55

Part Number Table

Description	Colour	Reel Length (m)	Part Number
0.40 M / 1100 M / 5 DO 5M 50505 0 44		100	PP-2182Y-0.75MMWHT
218-Y / H03VV-F BS EN 50525-2-11 Flexible Cable	D-2-11 White		PP-2183Y-0.50MMWHT
r lexible dable			PP-2183Y-0.75MMWHT

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

