Surface Mount Schottky Barrier Diode





Applications:

- High speed switching applications.
- Circuit protecting: SOT-23
- Voltage clamping

Features:

- · SOT-23 Package for surface mount application
- · Protects from line to Vcc and line to ground
- · Low forward voltage and reverse recovery characteristics
- · Epoxy meets UL 94 V-0 flammability rating
- · Moisture sensitivity Level 1
- · Halogen free available upon request by adding suffix "-HF"
- · Mounting Position : Any
- Weight: 0.008 grams (approx.)

Maximum Ratings:

T_A = 25°C unless otherwise specified.

Characteristic	Symbol	Limits	Unit
RMS Reverse Voltage	VR(RMS)	49	V
Repetitive Peak Reverse Voltage Working Peak Reverse Voltage Diode Reverse Voltage	Vrrm Vrwm Vr	70	٧
Forward Continuous Current	lF	70	mA
Non-Repetitive Peak Forward Surge Current at t_{p} <1s	IFSM	100	mA
Power Dissipation	Po	200	mW
Thermal Resistance, Junction to Ambient Air	RθjA	625	°C/W
Junction and Storage Temperature Range	Tj, Tstg	-65 to +150	°C

Electrical Characteristics:

T_A = 25°C unless otherwise specified.

Characteristic	Symbol	Min.	Тур.	Max.	Unit
Device Marking	-	74		-	V
Repetitive Peak Reverse Voltage	Vrrm	-	70	-	V
Reverse Breakdown Voltage Tested with 10µA Pulse	V(BR)R	70	-	-	
Leakage Current Pulse Test tp <300μs @ For BAS70 V _R = 50V	lr	-	10	200	nA
Forward Voltage Pulse Test tp <300µs at I _F = 1mA at I _F = 15mA	VF	410 1000	-	-	mV

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Surface Mount Schottky Barrier Diode



Characteristic	Symbol	Min.	Тур.	Max.	Unit
Reverse Recovery Time from I _F = 10mA through I _R = 10mA to I _R = 1mA	trr	-	-	5	ns
Thermal Resistance Junction to Ambient Air	RthJA	-	-	430	k/W
Capacitance at V _R = 0V, F = 1MHz	Ctot	-	-	2	pF

Typical Characteristics:

T_A = 25°C unless otherwise specified.








Fig. 3 Typical Capacitance






Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro





Surface Mount Schottky Barrier Diode



Dimension:







SOT-23			
Min.	Max.		
2.8	3.04		
2.1	2.64		
1.2	1.4		
0.89	1.03		
1.78	2.05		
0.45	0.6		
0.013	0.1		
0.89	1.12		
0.085	0.18		
0.37	0.51		
	Min. 2.8 2.1 1.2 0.89 1.78 0.45 0.013 0.89 0.085		

Dimensions: Millimetres

Part Number Table

Description	Part Number
Surface Mount Schottky Barrier Diode	BAS70-04+

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

