

PCKN clamp holder, negative, left

For face turning using CN indexable insert

ATORN[®]

Application


For face turning using CN indexable insert 80°.

Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type C, 75° pitch angle, 80° tip angle, 0° clearance angle

Advantage

- very stable geometry for face turning with large feed depths and challenging conditions
- negative body geometry ensures good stability and absorption of force for large cutting depths
- wide range of delivery: suitable for both finishing and roughing



Art. No.	17837 216
ISO name	PCKN R/L 2525 M12
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Length of head	28 mm
Programming size	32 mm
Suitable for indexable inserts	CN.. 1204..
Tool design	Left
DIN	4983

EAN-Code

4050293127478