

**PRODUCT**

# Complete Test Station Kit

**FEATURES**

- This wrist strap and footwear tester has been designed to measure both high and low fail and pass functions.
- It also has a low battery indicator to indicate battery replacement
- Can be powered by a 9 volt PP3 alkaline battery
- This product is CE approved
- Footplate included



PRODUCT CODE	SIZE (mm)	NOTES
093-0019	129 x 63 x 25	Each - Includes wall mount and footplate

SPECIFICATIONS	
Power Supply	9 volt PP3 alkaline battery. (PSU-02 9 volt 100mA UN-regulated)
Test Voltage	Nominal 9 volts-stepped to 100 volts
Temperature Range (40°F to 120°F)	Operating 5°C to 49°C Storage -15°C to +60°C
Relative Humidity	0% to 90% (non-condensing)
Accuracy	+/- 10%
Repeatability	+/- 10%
Weight	150g
Dimensions of Tester	130mm x 70mm x 25mm


To request a quotation or for more information, please call **+44 (0)1473 836200**  
 email [info@antistat.co.uk](mailto:info@antistat.co.uk) or visit [www.antistat.co.uk](http://www.antistat.co.uk)

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2021 Antistat.

**USER GUIDE**

A unique checker that measures the resistance of wrist straps and if foot plate is also connected, tests footwear.

1. When testing, the operator simply connects to the test via the 4mm banana plug socket.
2. To test, make finger contact with the stainless steel push button, and “press to test”. A green LED will illuminate for pass or the red LED will illuminate for fail.
3. An audible buzzer will sound if the red fail LED illuminates.
4. If the resistance through the coil cord wrist strap and person exceeds 35 meg ohms the red fail LED will light, if the resistance is below 7500 kilohms the red fail LED will light.
5. If the 9 volt PP3 battery falls below 6.5 volts during test, the yellow battery low LED will light up.



TECHNICAL PROPERTIES	
Lower Limit	750k +/-10%
Upper Limit	35Meg +/-10%
Power	9V alkaline battery

To request a quotation or for more information, please call **+44 (0)1473 836200**  
email [info@antistat.co.uk](mailto:info@antistat.co.uk) or visit [www.antistat.co.uk](http://www.antistat.co.uk)

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2021 Antistat.