

STATIC SHIELDING BUBBLE BAGS & FILMS

20-006-xxxx / 90-161-xxxx

Recyclable, environmental friendly, transparent, electrostatic protective, heat sealable, flexible structure, offering excellent electrostatic shielding properties and abrasion resistance Available in rolls or bags

Film construction:

Dissipative coating

Polyester

Aluminium

Polyethylene

Dissipative coating

Pink polyethylene bubble film

Standard compliance:

IEC 61340-5-1 94/62/EC & 2002/95/EC (ROHS directives)



Material and features:

Material Colamination of a static shielding film and a pink antistatic

polythene bubble film

Thickness: $148 \mu + /- 10\%$

Surface resistance: < 10e11 Ohm (both surface), IEC 61340-2-3

Energy penetration: < 30 NJ

Static decay time: < 0.05 seconds

Bubble diameter: 10mm

Roll specifications:

Length: 100 m

Width: from 305mm to 1524mm

Part numbers: 90-161-xxxx

Bag specifications:

All bags dimensions are internal dimensions. The 1st dimension is the opening, the 2nd is the height.

Dimensions two-layers: from 100x100mm to 3000x1500mm Dimensions three-layers: from 100x150mm to 3000x1500mm

Seal sizes: 12 mm
Printing: No print
Shelf life: 2 years
Part numbers: 20-006-xxxx