

COAXIAL TERMINATION, 50 Ohm, N, jack (female)

65010_N-50-2/133_N

Properties

- Various bandwidth
- Impedance matched
- Standard or precision types
- Low and medium power



| Product configuration | | |
|-----------------------|---------------|--|
| Interface | Gender | Standard |
| N | jack (female) | IEC 60169-16_MIL-STD-348A/304_CECC 22210 |

| Electrical data | |
|---------------------|------------------|
| Impedance | 50Ω |
| Operating frequency | 0 GHz ... 18 GHz |
| VSWR | 1.3 |
| Return loss | 17.7 dB |

| Electrical Data (power) | |
|-------------------------|---|
| Average power | 10 W at 25 °C ambient temperature. Linearly derated to 1 W at 100 °C ambient temperature. |
| Peak power | 500 W, 5 μs pulse width, 1% duty cycle |

| Interface and material data | | |
|-----------------------------|--------------------------------|-------------------|
| Interface | N / jack (female) | |
| Piece parts | Material | Plating |
| Centre contact | Copper Beryllium Alloy | Gold Plating |
| Outer conductor | Brass | Tri-metal Plating |
| Body | Aluminium | Anodized |
| Insulator | PTFE (Polytetrafluoroethylene) | |
| Piece parts | Material | Plating |

| Mechanical data | |
|-----------------|---------|
| Weight | 0.08 kg |

COAXIAL TERMINATION, 50 Ohm, N, jack (female)

65010_N-50-2/133_N

| Environmental data | |
|-----------------------|-------------------|
| Operation temperature | -55 °C ... 100 °C |

| Ordering Information Table | |
|----------------------------|---------------------|
| Item number | Item description |
| 85218431 | 65010_N-50-2/133_NE |

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1733 / Date of publication: 28.11.2023 / uncontrolled copy