



2001-02-15

PRODUKTINFORMATION

Vi reserverar oss mot fel samt förbehåller oss rätten till ändringar utan föregående meddelande

ELFA artikelnr

70-128-67 LL5817 schottkydiod MELF

70-128-75 LL5818 schottkydiod MELF

70-128-83 LL5819 schottkydiod MELF



LL5817 THRU LL5819

1.0 AMP. Surface Mount Schottky Barrier Rectifiers




Voltage Range
20 to 40 Volts
Current
1.0 Ampere

MELF

Features

- ✧ Surge overload ratings to 25 amperes peak
- ✧ Ideal for printed circuit board
- ✧ Reliable low cost construction utilizing molded plastic technique results in inexpensive product
- ✧ Mounting position: Any
- ✧ Weight: 0.12 gram



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	LL5817	LL5818	LL5819	Units
Maximum Recurrent Peak Reverse Voltage	20	30	40	V
Maximum RMS Voltage	14	21	28	V
Maximum DC Blocking Voltage	20	30	40	V
Maximum Average Forward Rectified Current @ T _L = 90°C	1.0			A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	25			A
Maximum Instantaneous Forward Voltage @ 1.0A	0.450	0.550	0.600	V
Maximum Instantaneous Forward Voltage @ 3.0A	0.750	0.875	0.900	V
Maximum DC Reverse Current @ T _A =25°C at Rated DC Blocking Voltage @ T _A =100°C	1.0 10			mA mA
Typical Thermal Resistance R _{θJA} (Note 1)	80			°C/W
Typical Junction Capacitance (Note 2)	110			pF
Operating and Storage Temperature Range T _J , T _{STG}	- 65 to + 125 / - 65 to + 150			°C

Notes: 1. Thermal Resistance Junction to Ambient

2. Measured at 1 MHz and Applied Reverse Voltage of 4.0 Volts D.C.

RATINGS AND CHARACTERISTIC CURVES (LL5817 THRU LL5819)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2- TYPICAL JUNCTION CAPACITANCE




FIG.3- TYPICAL FORWARD CHARACTERISTICS




FIG.4- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT

