

Product Data Sheet 3258 J/2H3PU-011

ebm papst

The engineer's choice



3258 J/2H3PU-011**INDEX**

| | |
|--|-----------|
| 1 General | 3 |
| 2 Mechanics | 3 |
| 2.1 General..... | 3 |
| 2.2 Connections..... | 3 |
| 3 Operating Data | 4 |
| 3.1 Electrical Interface - Input..... | 4 |
| 3.2 Electrical Operating Data | 5 |
| 3.3 Electrical Interface - Output..... | 6 |
| 3.4 Electrical Features | 6 |
| 3.5 Aerodynamics | 8 |
| 3.6 Sound Data..... | 9 |
| 4 Environment..... | 9 |
| 4.1 General..... | 9 |
| 4.2 Climatic Requirements | 9 |
| 4.3 Mechanical Requirements..... | 10 |
| 5 Safety..... | 11 |
| 5.1 Electrical Safety | 11 |
| 5.2 Approval Tests..... | 11 |
| 6 Reliability..... | 11 |
| 6.1 General..... | 11 |

1 General

| | |
|-------------------------------------|------------------------|
| Fan type | Fan |
| Rotating direction looking at rotor | Clockwise |
| Airflow direction | Air outlet over struts |
| Bearing system | Ball bearing |
| Mounting position - shaft | Any |


2 Mechanics

2.1 General

| | |
|---|---|
| Width | 92,0 mm |
| Height | 92,0 mm |
| Depth | 38,0 mm |
| Mass | 0,26 kg |
| Housing material | Plastic |
| Impeller material | Plastic |
| Max. torque when mounted across both mounting flanges | Wire outlet corner: 50 Ncm Remaining corners: 110 Ncm |
| Screw size | ISO 4762 - M4 degreased, without an additional brace and without washer |

2.2 Connections

| | |
|-----------------------|---------------------------|
| Electrical connection | Wires |
| Lead wire length | L = 310 mm +/- 10,0 mm |
| Tolerance | |
| Wire size (AWG) | |
| Insulation diameter | 1,7 mm |



| Wire | Color | Operation | Wire size | Insulation diameter |
|------|--------|-----------|-----------|---------------------|
| 1 | red | + UB | AWG 22 | |
| 2 | blue | - GND | AWG 22 | |
| 3 | violet | PWM | AWG 22 | |
| 4 | white | Tacho | AWG 22 | |

The auxiliaries shown on the schematic diagram (which are required for the intended use) are not part of our delivery.



3 Operating Data

3.1 Electrical Interface - Input

| | |
|---------------|-----|
| Control input | PWM |
|---------------|-----|

Features

| | | |
|---------------------------------|-----------------------|-----------------------------------|
| Input type | Open collector | |
| PWM - Frequency | | 1 kHz - 30 kHz typical: 25 kHz |
| Max. voltage for logic "Low" | | 0,2 V |
| Maximum source current | short circuit current | <= 1 mA |
| Typical time until warm restart | After shutdown by PWM | ~ 9 s |



3.2 Electrical Operating Data

Measurement conditions: Normal air density = 1,2 kg/m³; Temperature 23°C +/- 3°C; Motor axis horizontal; warm-up time before measuring 5 minutes (unless otherwise specified). In the intake and outlet area should not be any solid obstruction within 0,5 m.


$\Delta p = 0$: corresp. to free air flow (see chapter aerodynamics)
 I: corresp. to arithm. mean current value

| Name | Condition | | | |
|----------|-----------------------|----------|--|-----------|
| PWM 0001 | PWM: 100 %; f: 25 kHz | f: 1 kHz | | f: 30 kHz |

| Features | Condition | Symbol | Values | | |
|----------------------------------|----------------------------|----------------|------------------------|------------------------|------------------------|
| Voltage range | | U | 36 V | | 56 V |
| Nominal voltage | | U _N | | 48 V | |
| Power consumption Tolerance | $\Delta p = 0$ PWM 0010 | P | 20 W +- 20 % | 34 W +- 15 % | 44,8 W +- 15 % |
| Current consumption Tolerance | $\Delta p = 0$ PWM 0010 | I | 560 mA +- 20 % | 710 mA +- 15 % | 800 mA +- 20 % |
| Speed Tolerance | $\Delta p = 0$ PWM 0010 | n | 6.200 1/min +- 15 % | 7.450 1/min +- 10 % | 8.150 1/min +- 15 % |
| Starting current consumption | | | | <= 1.400 mA | |

3.3 Electrical Interface - Output

| | |
|------------|---------------------|
| Tacho type | /2 (open collector) |
|------------|---------------------|




| Features | Note | Values |
|---------------------------|---|--------------------------------|
| Tacho operating voltage | U_{BS} | $\leq 60 \text{ V}$ |
| Tacho signal Low | $U_{S \text{ low}}$ I sink: 2 mA | $\leq 0,4 \text{ V}$ |
| Tacho signal High | $U_{S \text{ high}}$ I source: 0 mA | 60 V |
| Maximum sink current | I_{sink} | $\leq 4 \text{ mA}$ |
| External resistor | External resistor Ra from UBS to US required. All voltages measured to GND. | |
| Tacho frequency | $(3 \times n) / 60$ | |
| Tacho isolated from motor | No | |
| Slew rate | | $\Rightarrow 0,5 \text{ V/us}$ |

n = revolutions per minute (1/min)

3.4 Electrical Features

| | | |
|--------------------------------|---|--|
| Electronic function | Speed-Controlled | |
| Reversed polarity protection | Rectifying diode | |
| Max. residual current at U_N | $I_F \leq 200 \mu\text{A}$ | |
| Locked rotor protection | Auto restart | |
| Locked rotor current at U_N | $I_{block} \text{ approx. } 1.800 \text{ mA}$ | |
| Clock signal at locked rotor | $t_3 / t_4 \text{ typical: } 1 \text{ s} / 9 \text{ s}$ | |



First pulse t_5 typical 1,6s (1,3 .. 1,9s) followed by t_4 . Afterwards cyclical t_3/t_4 .

3.5 Aerodynamics


Measurement conditions:

Measured with a double chamber intake rig acc. to DIN EN ISO 5801.
 Normal air density = 1,2 kg/m³; Temperature 23°C +/- 3°C;
 In the intake and outlet area should not be any solid obstruction within 0,5 m. Motor shaft horizontal.
 The information is only valid under the specified test conditions and may be changed by the installation conditions. If there are deviations from the standard test conditions, the characteristic values must be checked under the installed conditions. Power consumption of the fan motor when operating at normal voltage is shown. Depending on the operating conditions of the application, the power input may be higher.

a.) Operation condition:

| | | | |
|------------------------------|----------------------|----------|-----------|
| 7.450 1/min at free air flow | PWM 100 %; f: 25 kHz | f: 1 kHz | f: 30 kHz |
|------------------------------|----------------------|----------|-----------|

| | | |
|---|-----------------------|--|
| Max. free-air flow ($\Delta p = 0$ / $\dot{V} = \text{max.}$) | 265 m ³ /h | |
| Max. static pressure ($\Delta p = \text{max.} / \dot{V} = 0$) | 355 Pa | |



3.6 Sound Data

Measurement conditions: Sound pressure level: 1 meter distance between microphone and the air intake.
 Sound power level: According to DIN 45635 Part 38 (ISO 10302)
 Measured in a semianechoic chamber with a background noise level of $L_p(A) < 5 \text{ dB}(A)$
 For further measurement conditions see chapter aerodynamics.

a.) Operation condition:

| | | | |
|------------------------------|----------------------|----------|-----------|
| 7.450 1/min at free air flow | PWM 100 %; f: 25 kHz | f: 1 kHz | f: 30 kHz |
|------------------------------|----------------------|----------|-----------|

| | | |
|---|-------------------|--|
| Optimal operating point | 180 m3/h @ 185 Pa | |
| Sound power level at the optimal operating point | 7,5 bel(A) | |
| Sound pressure level at free air flow, measured in rubber bands | 64,0 dB(A) | |

4 Environment

4.1 General

| | | |
|--|--------|--|
| Min. permitted ambient temperature TU min. | -20 °C | |
| Max. permitted ambient temperature TU max. | 70 °C | |
| Min. permitted storage temperature TL min. | -40 °C | |
| Max. permitted storage temperature TL max. | 85 °C | |

4.2 Climatic Requirements

| | | |
|--------------------------------|---|--|
| IP-protection type (certified) | IP 68 (for fan only, not for connector if applicable) **) | |
| Humidity requirements | humid temperature, cyclic; according to DIN EN 60068-2-38, 10 cycle and condensation water check; according to DIN EN ISO 6270-2, 14 days | |
| Salt fog requirements | salt fog, cyclic, in operation; according to DIN EN 60068-2-52, 3 cycle | |

Permitted application area:

The product is for the use in open and unsheltered areas. Direct exposure to water as well as saline ambient conditions are allowed provided that this does not prevent the normal operation.

Pollution degree 3 (according DIN EN 60664-1)

It occurs conductive pollution or dry non-conductive pollution which becomes conductive due to condensation.

**) The specification of the IP protection refers to the conditions mentioned in certification of the fan. The above mentioned short description of the protection scope is not final. For detailed information of the respective protection scope and definitions, see certification as well as DIN EN 60529 (protection by housings) and ISO 20653 (for vehicles) with the letter K.

Short description of the IP-protection type:

Solid particle Protection: Dust tight.

Protection against deliberate contact: Protected against contact to hazardous parts with a wire.

Protection against water: The fan test according to IP68 (Based on IEC 60529), is conducted in non-operating mode. The fan is tested by a complete immersion in water for a period of 2h at a water-level of 1,2m. Electrical connections are not immersed since they are customer specific.

4.3 Mechanical Requirements

| severity level | stationary use | | |
|----------------|--------------------------|--|--|
| 1 | storage / transportation | Random vibration not in use IEC 60068-2-64 Frequency range / ASD G_{RMS} Axes of vibration Test duration | Random vibration 5 - 20 Hz : $1,0 \text{ m}^2 / \text{s}^3$ 20 - 500 Hz : - 3 dB / Oct 0,91 G 3 3 x 5 h |
| | storage / transportation | Bump not in use IEC 60068-2-29 Shock spectrum Acceleration Duration Number of bumps (+X, -X, -Y, +Y, -Z, +Z) Total bumps | Bump half sine 18 G 6 ms 100 in each direction 600 |
| | stationary use | Random vibration in use IEC 60068-2-64 Frequency range / ASD G_{RMS} Axes of vibration Test duration | Random vibration 5 - 20 Hz : $2,0 \text{ m}^2 / \text{s}^3$ 20- 150 Hz : - 3 dB / Oct 0,83 G 3 3 x 5 h |
| | stationary use | Bump in use IEC 60068-2-29 Shock spectrum Acceleration Duration Number of bumps (+X, -X, -Y, +Y, -Z, +Z) Total bumps | Bump half sine 5 G 11 ms 100 in each direction 600 |

5 Safety

5.1 Electrical Safety

| | | |
|--|------------------|--|
| Dielectric strength DIN EN 60950 (VDE 0805) and DIN EN 60335 (VDE 0700) A.) Type test Measuring conditions: After 48h of storage at 95% R.H. and 25°C. No arcing or breakdown is allowed! All connections together to ground. | 500 VAC / 1 Min. | |
| B.) Routine test Measuring conditions: At indoor climate. No arcing or breakdown is allowed! All connections together to ground. | 850 VDC / 1 Sec. | |
| Isolation resistance Measuring conditions: After 48h of storage at 95% R.H. and 25°C measured with U=500 VDC for 1 min. | RI > 10 MΩ | |
| Clearance / creepage distance | 1,0 mm / 1,2 mm | |
| Protection class | III | |

5.2 Approval Tests

| | | |
|-----|---|---|
| CE | EC Declaration of Conformity | Yes |
| EAC | Eurasian Conformity | Yes |
| UL | Underwriters Laboratories | Yes / UL507, Electric Fans |
| VDE | Association for Electrical, Electronic and Information Technologies | Yes / Approval acc. to EN 60950 (VDE 0805) - Information technology equipment |
| CSA | Canadian Standards Association | Yes / C22.2 No. 113 Fans and Ventilators |
| CCC | China Compulsory Certification | Yes / GB 12350 Safety Requirements for small Power Motors |


6 Reliability

6.1 General

| | | |
|--|-----------|--|
| Life expectancy L10 at TU = 40 °C | 85.000 h | |
| Life expectancy L10 at TU max. | 42.500 h | |
| Life expectancy L10 acc. to IPC 9591 at TU = 40 °C | 142.500 h | |

Copying of this document, and giving it others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved.
in the event of the grant of a patent or of the registration of a utility model or design,
Refer to protection notice DIN ISO 16166 !

Schutzvermerk nach DIN ISO 16166 beachten!
Refer to protection notice DIN ISO 16166!



1) Maße für Montagegewand
1) dimension for worktop mounting

-Anzahl und Laenge der Litzen siehe Produktspezifikation
number and length of the wires, look at the product specification

-Kein Axialspiel bei Kugellager durch Federausgleich
no axial clearance of ball bearings conditional on a pre-load spring

| SAP-Status/State | Aend.-Nr. / Change-No. | CATIA-System-Version/ CATIA-System-Version | CAD-Umgebung/ CAD-Environment | Werkstoff / Material: 9293512001 CPR000 - | Volumen / Volume (mm³): |
|--|------------------------|---|----------------------------------|--|----------------------------------|
| | | | | | Gewicht / Mass (g): |
| Artikel / Title: | | | | | |
| Tolerierung / Tolerances: | | Datum | Name | Zchz.-Nr. / Drawing No: | Ers.f.Zchz. / Replaces: |
| Allgemeintoleranzen / Gen. Tolerances: | | Bearb./ Drawn | | | |
| | | Gepr./ Checked | | | |
| | | Freig./ Releas. | | | |
| ebmpapst | | Dokumenttyp / Type of Document | Teildokument (Blatt/Page) | Index / Index | Format / Size: Massstab/Scale |
| | | ebm-papst St.Georgen GmbH & Co KG | | | |