

F202 A-16/0,01



Products Low Voltage Products and Systems Modular DIN Rail Products Residual Current Devices RCDs
Residual Current Devices RCDs

General Information

Extended Product Type:	F202 A-16/0,01
Product ID:	2CSF202101R0160
EAN:	8012542782407
Catalog Description:	F202 A-16/0,01 Residual Current Dev.
Long Description:	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications.

Additional Information

Country of Origin:	Italy (IT)
Customs Tariff Number:	85363010
Data Sheet, Technical Information:	2CSC400002D0209
Declaration of Conformity - CE:	2CSC423001D2701
EAN:	8012542782407
EPLAN Catalog Tree:	Electrical engineering / Protection devices / Ground fault current circuit breaker
EPLAN Function Definition:	Ground fault current circuit-breaker / Ground fault current circuit breakers, 4 connection points / Ground fault current circuit breaker, two-pole 1/2 2/1 3/4 4/3
ETIM 4:	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5:	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6:	EC000003 - Residual current circuit breaker (RCCB)
Environmental Information:	S-P-00080
Instructions and Manuals:	2CSF423001D6402
Invoice Description:	F202 A-16/0,01 Residual Current Dev.
Maximum Operating Voltage UL/CSA:	277 V AC
Minimum Order Quantity:	1 piece
Number of Poles:	2
Object Classification Code:	Q
Operating Characteristic:	Instantaneous
Options Provided:	-
Package Level 1 EAN:	8012542782407
Package Level 1 Gross Weight:	0.225 kg
Package Level 1 Height:	0.078 m
Package Level 1 Length:	0.096 m
Package Level 1 Units:	1 piece
Package Level 1 Width:	0.041 m
Position of Neutral Terminals:	Right
Power Loss:	at Rated Operating Conditions per Pole 1.5 W
Product Main Type:	F200
Product Name:	Residual Current Device
Product Net Depth:	0.069 m
Product Net Height:	0.085 m
Product Net Weight:	0.200 kg
Product Net Width:	0.035 m
Rated Current (I_n):	16 A
Rated Frequency (f):	50 ... 60 Hz
Rated Operational Voltage:	230 V AC
Rated Residual Current:	10 mA
Rated Voltage (U_r):	230/400 V
RoHS Information:	2CSC423001K0201
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q3
Selling Unit of Measure:	piece
Short Description:	Residual Current Device F202 A-16/0,01
Standards:	IEC/EN 61008 UL 1053
Type of Residual Current:	A type
Accessories Available:	Yes

