
Model Number

NCB50-FP-A2-P1


Features

- 50 mm flush
- 4-wire DC

Connection



Dimensions



Technical Data

General specifications		
Switching element function		PNP NO/NC
Rated operating distance	Sn	50 mm
Installation		flush
Output polarity		DC
Assured operating distance	sa	0 40.5 mm
Reduction factor r _{Al}		0.38
Reduction factor r _{Cu}		0.35
Reduction factor r ₃₀₄		0.83
Nominal ratings		
Operating voltage	U_B	10 60 V DC

Operating voltage	U_B	10 60 V DC
Switching frequency	f	0 80 Hz
Hysteresis	Н	typ. 3 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	Ud	≤ 3 V

Operating current 0 ... 200 mA 0 ... 0.5 mA ≤ 20 mA Off-state current
No-load supply current Time delay before availability ≤ 300 ms Operating voltage display LED, green Switching state indication LED, yellow

Functional safety related parameters MTTF_d
Mission Time (T_M)
Diagnostic Coverage (DC) 680 a 20 a

0 % Ambient conditions

Ambient temperature -25 ... 70 °C (-13 ... 158 °F)

Mechanical specifications Connection type
Core cross-section screw terminals up to 2.5 mm² Housing material PBT Sensing face PBT PBT

Housing base Protection degree IP68 Compliance with standards and directives

Standard conformity

EN 60947-5-2:2007 Standards IEC 60947-5-2:2007

Approvals and certificates


UL approval cULus Listed, General Purpose CSA approval cCSAus Listed, General Purpose

Certified by China Compulsory Certification (CCC) CCC approval

Installation hint

These sensors are especially designed for embeddable mounting in conveyor floors. Due to its precise location in metal base plates the sensor is afforded a high degree of mechanical protection. No clearance is required between the sensor and the base plate, avoiding the need for protective guarding to prevent possible foot injury.

The large sensing range ensures positive detection, and thus provides consistent control and monitoring of the conveyor.



Warning! Once the metal screening has been removed, the sensor can no longer be embeddable mounted.