

Electronics

SCHRACK

Interface Plug-in Relay XT

- 1 pole 16 A, 2 pole 8 A, 1 CO contact or 2 CO contacts
- DC- or AC coil, sensitive coil 400 mW
- Reinforced insulation, protection class II (VDE 0700)
- 4 kV / 8 mm coil-contact
- Manual test tab, optionally lockable¹⁾
- Version with mechanical and/or electrical indicator optionally available
- Suitable for use in Tyco standard RT sockets
- Recycleable p
- RoHS complia

Applications

Panel boards, m

Approvals in process calus E214025 Technical data of approved types on request

nechanical engineering	200 <u>M</u>
iant (Directive 2002/95/EC)	2)
packaging	

Contact data	1-pole	2-pole
Contact configuration	1 CO	2 CO
Contact set	single	contact
Type of interruption	micro disc	connection
Rated current	16 A	8 A
Rated voltage / max.switching voltage AC	240/40	00 VAC
Maximum breaking capacity AC	4000 VA	2000 VA
Limiting making capacity,max 4 s, df 10%	30 A	15 A
Contact material		i 90/10
Mechanical endurance DC coil	> 10	x 10 ⁶
AC coil		x 10 ⁶
Rated frequency of operation with / without load	6 / 60	0 min ⁻¹

Contact	ratings	
Туре	Load	Cycles
XT37*	16 A, 250 VAC, CO contact, 70°C, DF 50%, EN61810-1	3x10 ³
XT48*	8 A, 250 VAC, CO contact, 70°C, DF 50%, DC coils, EN61810-1	5x10 ³
XT48*	8 A, 250 VAC, CO contact, 70°C, DF 50%, AC coils, EN61810-1	3x10 ³
XT31*	16 A, 250 VAC, CO contact, 70°C, DF 50%, EN61810-1	3x10 ³
XT42*	8 A, 250 VAC, CO contact, 70°C, DF 50%, DC coils, EN61810-1	5x10 ³
XT42*	8 A, 250 VAC, CO contact, 70°C, DF 50%, AC coils, EN61810-1	3x10 ³
XT37*	16 A, 250 VAC, CO General Purpose 70°C, DF 50%, UL508	3x10 ³
XT48*	8 A, 250 VAC, CO General Purpose 70°C, DF 50%, DC coils, UL508	3x10 ³
XT48*	8 A, 250 VAC, CO General Purpose 70°C, DF 50%, AC coils, UL508	3x10 ³
XT31*	16 A, 250 VAC, CO General Purpose 70°C, DF 50%, UL508	3x10 ³
XT42*	8 A, 250 VAC, CO General Purpose 70°C, DF 50%, DC coils, UL508	3x10 ³
XT42*	8 A, 250 VAC, CO General Purpose 70°C, DF 50%, AC coils, UL508	3x10 ³

Coil data	
Rated coil voltage range DC coil	6110 VDC
AC coil	24230 VAC
Coil power DC coil	typ 400 mW
AC coil	typ 0.75 VA
Operative range	2
Coil insulation system according UL1446	class F





If the test button is pulled out too forcefully, it may bypass the momentary testing position and go straight into the locked position.


Delivery status is with testing possibility only, to reach locking position please remove the locking plastic pip according drawing



F0289-A











SCHRACK

Interface Plug-in Relay XT (Continued)

Coil versions, DC-coil

Coil	LED &	Rated	Operate	Release	Coil	Rated coil	opt. LED
code	PD*	voltage	voltage	voltage	resistance	power	power
		VDC	VDC	VDC	Ohm	mW	mW
012	LB2	12	8.4	1.2	360±10%	400	10
024	LC4	24	16.8	2.4	1440±10%	400	19
048	LE8	48	33.6	4.8	5520±10%	417	39
110	MB0	110	77.0	11.0	28800±12%	420	87

All figures are given for coil without preenergization, at ambient temperature +23°C
*) Protection diode PD; standard polarity: +A1 / -A2
Other coil voltages on request

Coil versions, AC-coil 50 Hz

OUII VC	0.0.00						
Coil	LED	Rated	Operate	Release	Coil	Rated coil	opt. LED
code		voltage	voltage	voltage	resistance	power	power
			50 Hz	50 Hz		50 Hz	50 Hz
		VAC	VAC	VAC	Ohm	VA	VA
524	R24	24	18.0	3.6	350±10%	0.76	0.012
615	S15	115	86.3	17.3	8100±15%	0.76	0.054
730	T30	230	172.5	34.5	32500±15%	0.74	0.073

All figures are given for coil without preenergization, at ambient temperature +23°C Other coil voltages on request

Insulation

Dielectric strength coil-contact circuit	5000 V _{rms} in combination with RT78726
	4000 V _{rms} in combination with RT78725
open contact circuit	1000 V _{rms}
adjacent contact circuits	2500 V _{rms}
Clearance / creepage coil-contact circuit	≥ 8 / 8 mm
Material group of insulation parts	≥ Illa
Tracking index of relay base	PTI 175 V
Insulation to IEC 60664-1	
Type of insulation coil-contact circuit	reinforced
open contact circuit	functional

Type of insulation coil-contact circuit open contact circuit adjacent contact circuits

Rated insulation voltage 250 V


Pollution degree 3 240 V


Overvoltage category III

Other data	1-pole	2-pole	
RoHS - Directive 2002/95/EC	compliant		
Flammability class according to UL94	V-0		
Ambient temperature range DC coil	-40+	70°C	
AC coil	-40+	70°C	
Operate- / release time DC coil	9 / 6 ms		
Bounce time DC coil, NO / NC contact	4 / 12 ms		
Vibration resistance (function), NO / NC contact	20 / 5 g, 30 500 Hz		
Shock resistance (destruction)	100 g		
Category of protection	RT	II	
Mounting distance	4,5 mm, dense pa	cking of sockets	
Relay weight	16 g		
Packaging unit	10 / 250 pcs		

Accessories


For Details see datasheet	Accessories Interface Power Relay XI







Terminal assignment

Bottom view on pins







change.



General Purpose Relays



Interface Plug-in Relay XT (Continued)

Product key	X T 4
Туре	
Version	
3 1-pole, 16 A, pinning 5 mm	
4 2-pole, 8 A, pinning 5 mm	
Contact configuration	
1 1 CO contact	7 1 CO contact with test button and mechanical indicator
2 2 CO contacts	8 2 CO contacts with test button and mechanical indicator
Contact material	
4 AgNi 90/10	
Coil	,
Coil code: please refer to coil versions tal	ole, preferred types in bold print

Product key	Contacts	Cont. material	Coil	Coil	Part number
XT374LC4	1 CO contact	AgNi 90/10	DC-coil	24 VDC	1887112-1
XT374R24	16 A	test button,	AC-coil	24 VAC	1887113-3
XT374T30		mechanical		230 VAC	1887113-1
XT484LC4	2 CO contacts	and electrical	DC-coil	24 VDC	1887212-1
XT484R24	8 A	indicator	AC-coil	24 VAC	1887213-3
XT484T30				230 VAC	1887213-1

'Schrack' section.