

AS-I CABLE, TRAPEZOIDAL, F. EXTERNAL  
 AUXILIARY VOLTAGE, UP TO 24V, BLACK, RUBBER,  
 2X 1.5QMM CONSISTS OF 100 M CABLE



Figure similar

**General technical data:**

<b>Design of the product</b>		AS-Interface shaped cables
<b>Colour</b>		black (DC 24 V)
<b>Material</b>		rubber
<b>Quantity</b>		100 m roll

**Mechanical data:**

<b>Without silicone precipitation</b>		yes
bending radius according to DIN VDE 0298 Part 300		
• fixed min	m	12
• freely movable min	m	24
<b>Without halogens</b>		yes
<b>Flexibility</b>		very good
<b>Bending behavior according according to DIN VDE 0472 Part 603</b>		no break after 30000 reverse bending cycles
<b>Core colours</b>		brown, blue

**Ambient conditions:**

<b>Fire behavior</b>		flammable
<b>resistance to oil</b>		conditionally resistant
<b>Ozone and weather resistant</b>		conditionally resistant
<b>Temperature range</b>		
• stationary	°C	-40 ... +85
• moved	°C	-25 ... +85

**Certificates/ approvals:**

<b>Approvals Canada</b>	<b>CSA</b>	no
-------------------------	------------	----

Approvals USA	UL		no
Monitored expertise (VDE)			no
General Product Approval	Shipping Approval	other	



[Declaration of Conformity](#)

[Environmental Confirmations](#)

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RX90200AA00>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3RX90200AA00/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RX90200AA00&lang=en>

last modified:

09.03.2015