

TBN 2 G

TBN Breaking Torque wrench KNICKER

0.4-200 N · m / fixed setting

Code	ETIM
7090690	ECO02132 Drehmomentschlüssel
EAN	UNSPSC
4002805760000	27-11-17-15 Drehmomentschlüssel
Country of Origin	eCl@ss
England	21-04-02-22 Drehmomentschlüssel
Customs tariff no.	
82041100	



Article description

- Use:
- Controlled screw tightening in the range of 0.4 - 2 N · m
- Serial / production-line
- Extremely long-term work
- Features:
- Pre-set production torque wrench - without scale
- With 9x12 mm rectangular-cavity-end
- For bi-directional tightening (the wrench only has to be turned by 180°!)
- Working accuracy: +/- 4 % tolerance of set torque
- Acc. to DIN EN ISO 6789, traceable to national standards
- Breaking of the handgrip by 20° when the pre-set torque value is achieved makes over-tightening unlikely
- Automatic resetting to the starting position
- Lightweight, but robust and corrosion-resistant construction design
- Very convenient non-slip rubber handgrip
- No. TBN 2 G: EPA (Electrostatic Protected Area) compliant, for use in electrostatically sensitive applications
- The pre-setting can be made at the factory or by the user on suitable torque testers
- If ordering, please specify the N·m value - if a fixed factory pre-setting is desired (price on request)
- Scope of delivery:
- Torque wrench TBN Breaking Torque wrench
- Special adjusting key for changing the pre-set torque value
- Test certificate acc. to DIN EN ISO 6789
- Delivery in sturdy cardboard packaging

Article information

Contents (Qty of pieces)	1 tlg.	Precision +/-	+/- 6 %
Total length [mm]	133 mm	Direction of tightening	Left and right
Torque (min.) [N·m]	0,4 N·m	Fixed setting	1
Torque (max.) [N·m]	2 N·m	Test certificate	DIN EN ISO 6789-2:2017
Net weight [kg]	0,11 kg	Torque (max.) [lbf·in]	3,6 lbf·in
Material	Tubular steel construction	Torque (min.) [lbf·in]	18 lbf·in
REACH registration available	0	Drive connector rectangular	9 x 12 mm
Epa-/Esd-Model	1	Drive type/drive	Rectangular cavity
Trigger mechanism	Long travel triggering		