



IEC 1/2"UNF-20 Melt Bolt Thermocouple with Type 'J' Thermocouple Plug
 A choice of 76mm (3") or 152mm (6") bolt lengths with 5mm immersion



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.


Contact Details

Email sales@labfacility.com

Website www.labfacility.com

- Type 'J' (Iron/Constantan) Melt Bolt Thermocouple
- Typically used in plastics extruders and injection moulders
- Designed to withstand high pressure applications experienced with molten plastics & polymers
- Stainless steel bolt with 1/2"UNF-20 thread
- Choice of 76mm or 152mm bolt lengths
- 5mm long (x 3mm diameter) immersion length
- Temperature range to 500°C
- Insulated hot junction
- Standard plug termination (round pin)
- Tolerance & colour code in accordance with IEC-584 specification

T/C Type	Thread	Bolt Length ('L')	Tip Immersion Length	order Code
J (Iron/Con)	1/2"UNF-20	76mm (3" inch)	5.0mm (3.0mm diameter)	XF-1022-FAR
J (Iron/Con)	1/2"UNF-20	152mm (6" inch)	5.0mm (3.0mm diameter)	XF-1023-FAR



FAR179-0917 IEC 1/2"UNF-20 Melt Bolt Thermocouple with Type 'J' Thermocouple Plug