

gPV Cartridge Fuses

22mm × 58mm

multicomp PRO

**RoHS
Compliant**



Features

- 1500V DC, 22mm × 58mm PV fuse link with glass-fiber body
- Rated Current: 20A to 45A
- Breaking Capacity: 10 kA at 1500V DC (1A to 65A)
10 kA at 1300V DC (70A, 80A)
- Time Constant: 1ms to 3ms
- Special design with silver plated caps for high-power PV applications
- Standard: UL 248-19; IEC 60269-6
- Approvals: UL (File: E490190)
- Standard: IEC 60269-6
- BH400, BH401 holders for DIN rail mounting

Electrical Characteristics


Part Number	Rated Current (A)	Breaking capacity	I ² t (A ² s)		Dissipation (W)	
			Pre-Arcing	Total	0.8I _n	1I _n
MP006252	20	10kA @1500V DC	400	2200	4.2	5.2
MP006253	25		500	2750	5.1	6.3
MP006254	30		600	3300	5.1	6.3
MP006255	35		700	3850	6	7.5
MP006256	40		800	4400	7.2	9
MP006257	45		900	4950	7.2	9

Note: (1) Typical pre-arcing I²t measured at 10*I_n current

Time Vs Current Characteristic

Rated Current	UL			IEC		
	100%	135%	200%	100%	135%	200%
20A to 45A	Temperature Stabilization	<1 h	<4 min	Temperature Stabilization	<1 h	<4 min

Diagram



Dimensions : Millimetres

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO


gPV Cartridge Fuses

22mm × 58mm

multicomp PRO

Time Current Curve

Average Current Curve(I-T Curve)



Part Number Table

Description	Part Number
gPV Cartridge Fuse, 20A, 1500V DC, 22mm × 58mm	MP006252
gPV Cartridge Fuse, 25A, 1500V DC, 22mm × 58mm	MP006253
gPV Cartridge Fuse, 30A, 1500V DC, 22mm × 58mm	MP006254
gPV Cartridge Fuse, 35A, 1500V DC, 22mm × 58mm	MP006255
gPV Cartridge Fuse, 40A, 1500V DC, 22mm × 58mm	MP006256
gPV Cartridge Fuse, 45A, 1500V DC, 22mm × 58mm	MP006257

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO