

TE Internal #: 6-1768017-1

Standard Labels, Blank Labels, Die-Cut Label Style, Permanent, UL Listed No, Label Width 22.86 mm [.9 in], Label Height .25 in [6.35 mm], White

[View on TE.com >](#)



Identification & Labeling > Labels > Standard Labels



Label Type: **Blank Labels**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent**

UL Listed: **No**

Label Width: **22.86 mm [.9 in]**

## Features

### Product Type Features

Label Type	Blank Labels
------------	--------------

### Body Features

Label Color	White
-------------	-------

### Usage Conditions

Operating Temperature Range	0 – 70 °C[32 – 158 °F]
-----------------------------	------------------------

### Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Recommended Printer Ribbon	See Printer Ribbon Matrix
Printer Technology	Thermal Transfer
Label Style	Die-Cut
Label Width	22.86 mm[.9 in]
Label Height	6.35 mm[.25 in]
Label Material	Polyester

### Industry Standards

UL Listed	No
-----------	----

### Packaging Features

Packaging Quantity	10000
--------------------	-------



Other

Label Adhesive Type	Permanent
---------------------	-----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-1768017-0  
EET-0615V-9

Customers Also Bought



TE Part #7-1415055-1  
Force Guided Power Relay, 4 Poles



TE Part #2-104257-4  
25 MTE RCPT HSG SR LATCH .100




TE Part #1393154-9  
PT380024



TE Part #1703013-2  
ROUND CONNECTOR SYSTEM, PIN AND SOCKET



TE Part #2-216780-2  
RJ11 Connectors



TE Part #4-1768018-7  
EET-1325V-9



TE Part #1241969-8  
FASTIN FASTON HOUSING 8P



TE Part #165416  
P.G.RING DIN



TE Part #5-103955-1  
10X2 MTE PIN SR RIBBED .100CL



TE Part #2151433-1  
OCEAN-2.0-APPLICATOR-S-079F098O

## Documents

### Product Drawings

[EET-0623V-9](#)

English

### Datasheets & Catalog Pages

[EET V-9](#)

English