

98 42 914 0201



Pushing Performance

HARTING News 2009



People | Power | Partnership

Transforming customer wishes into concrete solutions

Intro-
duction



Headquartered in Espelkamp in East Westphalia, Germany, the HARTING Technology Group develops tailored solutions and products revolving around electrical and electronic connector technologies. These offerings focus on power and data transmission applications, as well as on network solutions. Founded in 1945 in Minden, HARTING is currently employing a workforce of more than 3200 members of staff worldwide.

In today's increasingly knowledge and information shaped societies, the capability to network and integrate with customers and suppliers, as well as technology and business partners is playing the decisive role.

And this applies to national as well as international levels. With 40 Subsidiary companies and Representatives in 27 countries, HARTING is committed to maintaining close proximity to markets and customers. Always at hand on location, HARTING is able to rapidly record market impulses and respond flexibly.



HARTING Subsidiary company



HARTING Representatives



WE ASPIRE TO TOP PERFORMANCE.

Connectors ensure functionality. As core elements of electrical and optical wiring, connection and infrastructure technologies, they are essential in enabling the modular construction of devices, machines and systems across a very wide range of industrial applications. Their reliability is a crucial factor guaranteeing smooth functioning in the manufacturing area, in telecommunications, applications in medical technology – in fact, connectors are at work in virtually every conceivable application area. Thanks to the consistent further development of our technologies, customers enjoy investment security and benefit from durable, long term functionality.

ALWAYS AT HAND, WHEREVER OUR CUSTOMERS MAY BE.

Increasing industrialization is creating growing markets characterized by widely diverging demands and requirements. The search for perfection, increasingly efficient processes and reliable technologies is a common factor in all sectors across the globe.

HARTING is providing these technologies – in Europe, America and Asia. The **HARTING** professionals at our international subsidiaries engage in close, partnership based interaction with our customers, right from the very early product development phases, in order to realize customer demands and requirements in the best possible manner.

Our people on location form the interface to the centrally coordinated development and production departments. In this way, our customers can rely on consistently high, superior product quality – worldwide.

OUR CLAIM: PUSHING PERFORMANCE.

HARTING provides more than optimally attuned components.

In order to serve our customers with the best possible solutions, **HARTING** is able to contribute a great deal more and play a closely integrative role in the value creation process.

From ready assembled cables through to control racks or ready-to-go control desks: Our aim is to generate the maximum benefits for our customers – without compromise!

QUALITY CREATES RELIABILITY – AND WARRANTS TRUST.

The **HARTING** brand stands for superior quality and reliability – worldwide. The standards we set are the result of consistent, stringent quality management that is subject to regular certifications and audits.

EN ISO 9001, the EU Eco-Audit and ISO 14001:2004 are key elements here. We take a proactive stance to new requirements, which is why **HARTING** ranks among the first companies worldwide to have obtained the new IRIS quality certificate for rail vehicles.

HARTING TECHNOLOGY CREATES ADDED VALUE FOR CUSTOMERS.

Technologies by HARTING are at work worldwide. HARTING's presence stands for smoothly functioning systems, powered by intelligent connectors, smart infrastructure solutions and mature network systems. In the course of many years of close, trust-based cooperation with its customers, the HARTING Technology Group has advanced to one of the worldwide leading specialists for connector technology. Extending beyond the basic functionalities demanded, we offer individual customers specific and innovative solutions. These tailored solutions deliver sustained effects, provide investment security and enable customers to achieve strong added value.

OPTING FOR HARTING OPENS UP AN INNOVATIVE, COMPLEX WORLD OF CONCEPTS AND IDEAS.



In order to develop connectivity and network solutions serving an exceptionally wide range of connector applications and task scopes in a professional and cost optimized manner, HARTING not only

commands the full array of conventional tools and basic technologies. Over and beyond these capabilities, HARTING is constantly harnessing and refining its broad base of knowledge and experience to create new solutions that ensure continuity at the same time. In securing this know-how lead, HARTING draws on a wealth of sources from both in-house research and the world of applications alike.

Salient examples of these sources of innovative knowledge include microstructure technologies, 3D design and construction technology, as well as high temperature or ultrahigh frequency applications that are finding use in telecommunications or automation networks, in the automotive industry, or in industrial sensor and actuator applications, RFID and wireless technologies, in addition to packaging and housing made of plastics, aluminum or stainless steel.

HARTING SOLUTIONS EXTEND ACROSS TECHNOLOGY BOUNDARIES.

Drawing on the comprehensive resources of the group's technology pool, HARTING devises



practical solutions for its customers. Whether this involves industrial networks for manufacturing automation, or hybrid interface solutions for wireless telecommunication infrastructures, 3D circuit carriers with microstructures, or cable assemblies for high-temperature applications in the automotive industry - **HARTING** technologies offer far more than components, and represent mature, comprehensive solutions attuned to individual customer requirements and wishes. The range covers ready-to-use cable configurations, completely assembled backplanes and board system carriers, as well as fully wired and tested control panels.

In order to ensure the future proof design of RF- and EMC-compatible interface solutions, the central **HARTING** laboratory (certified to EN 45001) provides simulation tools, as well as experimental, testing and diagnostics facilities all the way through to scanning electron microscopes. In the selection of materials and processes, lifecycle and environmental aspects play a key role, in addition to product and process capability considerations.

HARTING KNOWLEDGE IS PRACTICAL KNOW-HOW GENERATING SYNERGY EFFECTS.

HARTING commands decades of experience with regard to the applications conditions of connectors in telecommunications, computer and network technologies and medical technologies, as well as industrial automation technologies, such as the mechanical engineering and plant engineering areas, in addition to the power generation industry or the transportation sector. **HARTING** is highly conversant with the specific application areas in all of these technology fields.

The key focus is on applications in every solution approach. In this context, uncompromising, superior quality is our hallmark. Every new solution found will invariably flow back into the **HARTING** technology pool, thereby enriching our resources. And every new solution we go on to create will draw on this wealth of resources in order to optimize each and every individual solution. In this way, **HARTING** is synergy in action.



Contents

Page

Installation Technology

Han® 3 HPR high construction	10
Han® 3 A plastic hood with integrated cable gland	11
Han® 40/64 EEE	12
Han® Q 8/0 with Han-Quick Lock® termination	14
Han® 7 D with Han-Quick Lock® termination	16
Han® 8 D with Han-Quick Lock® termination	18
Han-Modular®	
Han-Modular® DD Module with Han-Quick Lock® termination	20
Han-Modular® EE Module with Han-Quick Lock® termination	22
Han-Modular® Twin panel feed through housing	24
Han-Modular® ECO plastic hoods and housings	26
Han-Modular® Compact Fixing bracket	29
Han-Modular® Docking frame	30
Han-Modular® 40 A Module with crimp termination	32
Han-Modular® 100 A Module with crimp termination	34
Han-Modular® GigaBit Module	36
Han® HC Modular	
Han® HC Modular 350 with crimp termination	40
Han® HC Modular 650 with crimp termination	42
Han® HC Modular Tools with crimp termination	46
Han-Power®	
Han-Power® T with 3 x Han® Q 2/0	45
Han-Power® T Modular Twin	46

Contents

Page

Automation IT

HARTING eCon 4000	48
HARTING eCon 4080-B3	50
HARTING eCon 4080-BPoE1	51
HARTING sCon	52
HARTING sCon 3000	54
HARTING sCon 3100-AA	56
HARTING mCon	57
HARTING mCon 3000	59
HARTING mCon 3100-AV	62
HARTING mCon 3100-AAV	63
HARTING mCon 3061-ADV	64
HARTING mCon 3063-ADV	65
HARTING mCon 3082-ADV	66
HARTING mCon 4000	67
HARTING mCon 4080-B1V	69
HARTING mCon 4080-B3V	70
HARTING mCon 9000	71
HARTING mCon 9070-BV	73
HARTING mCon 9080-BV	74

Contents

Page

Cable and cable assemblies

Industrial cable, 8-wire, category 5	75
HARTING RJ Industrial® IP 20 Patch cables for category 5 / 5e	78
HARTING RJ Industrial® IP 20 Patch cables for category 6	80
Hybrid cable assembly Han® 3 A Hybrid RJ45	82
Fibre optic cable assembly HARTING PushPull LC duplex multimode	83
Hybrid fibre optic cable assembly	
Han® 3 A Hybrid LC duplex multimode	84

Device Connectivity

CPM press-in machines	85
---------------------------------	-----------

DIN 41612

Technical characteristics	86
Connectors type 3B	87
Connectors type 3C	90

SMC (Surface Mount Compatible) connectors

with a **CTI value > 400**

Connectors type 2B	94
Connectors type B	96
Connectors type 2C	98
Connectors type C	100
Connectors type 2R	102
Connectors type R	104

Connectors and housings for railway with **NFF classification**

Technical characteristics	106
Interface connectors I	108
Connectors type F	110
D 20 housings	111

Contents

Page

D-Sub	
IP 67 plastic hoods, with and without metallization	112
Turned crimp contacts in performance level 1	113
 Micro Card Edge	
Technical characteristics and general information	114
Connectors with 40 contacts	116
Connectors with 100 contacts	117
 Han® PushPull metal (variant 14)	
Genderchanger RJ45	118
Genderchanger Power 4/0 L	119
Connectors Power 4/0 L, available in metal or plastic	120
Accessories	122
 HARTING PushPull metal (variant 4)	
RJ45 panel feed through set and accessories	124
RJ45 connectors	125
LC duplex panel feed through set and connector	126
Power 4/0 panel feed through set	127
Power 4/0 connectors	128
 Han® M12 5 pins with crimp termination	130
 Summary Catalogues	144
Addresses	145

Available by June 2009



Hood, high construction

Features

- High construction, therefore large cabling space
- M25 cable entry
- Suitable for harsh environments
- Highly EMC resistant
- Suitable for sensitive interconnections that have to be protected and shielded
- Captive locking screws

Technical characteristics

Material	Zinc die-cast
Surface	Epoxy powder paint, RAL 9005 (black) RoHS conform Black chrome plated: not RoHS conform
Locking element	
- screw locking	M4
- material	Stainless steel
- tightening torque	2 Nm
Limiting temperatures	-40 °C ... +125 °C
Protection degree acc. to DIN EN 60 529 in locked position	IP 68

Identification	Part-Number	Size	Drawing	Dimensions in mm
----------------	-------------	------	---------	------------------

Hood Han® 3 HPR
high construction

black chrome plated


19 40 003 0411

3 A

epoxy powder paint

19 40 703 0411

3 A



Available by July 2009



Plastic hood with integrated cable gland

Features

- Construction height reduced by 25 % when compared to the existing standard solution
- Large range of cable diameters (9 - 17 mm) can be used
- Reduced logistical effort due to integrated cable gland
- Also available as variant with glued seal for Han-Brid® inserts

Technical characteristics

Material	Plastic
Locking element	Plastic
Protection degree acc. to DIN EN 60 529 in locked position	IP 65 / 67
Cable diameter	9 - 17 mm

Identification

Part-Number

Size

Drawing

Dimensions in mm

Hood Han® 3 A
with integrated cable gland

without glued seal


19 20 003 0410

3 A

with glued seal
for Han-Brid® inserts

19 20 003 0413

3 A



Features

- 40 / 64 contacts with crimp termination
- Up to 64 Han E® contacts in hoods/housings type Han® 24 B
- Polarised insert
- Contacts available with either hard silver plated or hard gold plated surface
- Suitable for hoods/housings of series Han® B, Han® EMV, Han® HPR, Han® M


Technical characteristics

Specifications	DIN EN 60 664-1 DIN EN 61 984
Inserts	
Number of contacts	40, 64 + PE
Electrical data acc. to DIN EN 61 984	16 A 500 V 6 kV 3
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	3 kV
Pollution degree	3
Insulation resistance	≥ 10 ¹⁰ Ω
Material	Polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles
Contacts	
Material	Copper alloy
Surface	
- hard silver plated	3 µm Ag
- hard gold plated	2 µm Au over 3 µm Ni
Contact resistance	≤ 1 mΩ
Crimp termination	
- mm ²	0.14 – 4.0 mm ²
- AWG	26 – 12

Current Carrying Capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature. Measuring and testing techniques according to DIN EN 60 512-5.


Han® 64 EEE: Wire gauge: 2.5 mm²




Contact arrangement

View from termination side

Han® 40 EEE



Han® 64 EEE



Number of contacts

40 / 64 +

Han® 40 EEE: Available by May 2009
Han® 64 EEE: Available



Inserts

Identification	Contact No.	Part Number		Dimensions in mm
		Male insert	Female insert	
Crimp termination order crimp contacts separately	40	09 32 040 3001	09 32 040 3101	
	64	09 32 064 3001	09 32 064 3101	

Identification	Wire gauge mm²	Part Number		Dimensions in mm																																				
		Male contacts	Female contacts																																					
Crimp contacts silver plated	0.14-0.37	09 33 000 6127	09 33 000 6227																																					
	0.5	09 33 000 6121	09 33 000 6220																																					
	0.75	09 33 000 6114	09 33 000 6214																																					
	1	09 33 000 6105	09 33 000 6205																																					
	1.5	09 33 000 6104	09 33 000 6204																																					
	2.5	09 33 000 6102	09 33 000 6202																																					
	3	09 33 000 6106	09 33 000 6206																																					
	4	09 33 000 6107	09 33 000 6207																																					
gold plated	0.14-0.37	09 33 000 6117	09 33 000 6217	<table border="1"> <thead> <tr> <th>Identification</th> <th colspan="2">Wire gauge</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>no groove</td> <td>0.14-0.37</td> <td>mm² AWG 26-22</td> <td>7.5 mm</td> </tr> <tr> <td>no groove</td> <td>0.5</td> <td>mm² AWG 20</td> <td>7.5 mm</td> </tr> <tr> <td>1 groove*</td> <td>0.75</td> <td>mm² AWG 18</td> <td>7.5 mm</td> </tr> <tr> <td>1 groove</td> <td>1</td> <td>mm² AWG 18</td> <td>7.5 mm</td> </tr> <tr> <td>2 grooves</td> <td>1.5</td> <td>mm² AWG 16</td> <td>7.5 mm</td> </tr> <tr> <td>3 grooves</td> <td>2.5</td> <td>mm² AWG 14</td> <td>7.5 mm</td> </tr> <tr> <td>wide groove</td> <td>3</td> <td>mm² AWG 12</td> <td>7.5 mm</td> </tr> <tr> <td>no groove</td> <td>4</td> <td>mm² AWG 12</td> <td>7.5 mm</td> </tr> </tbody> </table>	Identification	Wire gauge		Stripping length	no groove	0.14-0.37	mm² AWG 26-22	7.5 mm	no groove	0.5	mm² AWG 20	7.5 mm	1 groove*	0.75	mm² AWG 18	7.5 mm	1 groove	1	mm² AWG 18	7.5 mm	2 grooves	1.5	mm² AWG 16	7.5 mm	3 grooves	2.5	mm² AWG 14	7.5 mm	wide groove	3	mm² AWG 12	7.5 mm	no groove	4	mm² AWG 12	7.5 mm
	Identification	Wire gauge			Stripping length																																			
	no groove	0.14-0.37	mm² AWG 26-22		7.5 mm																																			
	no groove	0.5	mm² AWG 20		7.5 mm																																			
	1 groove*	0.75	mm² AWG 18		7.5 mm																																			
	1 groove	1	mm² AWG 18		7.5 mm																																			
	2 grooves	1.5	mm² AWG 16		7.5 mm																																			
	3 grooves	2.5	mm² AWG 14		7.5 mm																																			
wide groove	3	mm² AWG 12	7.5 mm																																					
no groove	4	mm² AWG 12	7.5 mm																																					
0.5	09 33 000 6122	09 33 000 6222																																						
0.75	09 33 000 6115	09 33 000 6215																																						
1	09 33 000 6118	09 33 000 6218																																						
1.5	09 33 000 6116	09 33 000 6216																																						
2.5	09 33 000 6123	09 33 000 6223																																						
4	09 33 000 6119	09 33 000 6221																																						

* on the back crimp collar



Features

- Innovative Han-Quick Lock® termination technology
- Field assembly without special tools
- Compatible with Han® Q 8/0 standard inserts with crimp terminal
- Reduced wiring times
- Insert suitable for plastic hoods and housings of the sizes Han-Compact®
- Space-saving and compact design
- Leading protective ground contact

Technical characteristics

Specifications	DIN EN 60 644-1 DIN EN 61 984
Inserts	
Number of contacts	8 + PE
Electrical data acc. to DIN EN 61 984	16 A 500 V 6 kV 3
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Termination	Han-Quick Lock®
Insulation resistance	≥ 10 ¹⁰ Ω
Material insert	Polycarbonate
Material seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles

Contacts

Material	Copper alloy
Surface	
- hard silver plated	3 μm Ag
Contact resistance	≤ 3 mΩ
Han-Quick Lock®	
- mm ²	0.5 – 2.5 mm ²
- AWG	20 – 14
Maximum insulation cross section	ø = 3.6 mm


Plastic hoods/ housings

Material	Polycarbonate
Locking element	Polyamide
Flammability acc. to UL 94	V 0
Hoods/ housings seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 in locked position	IP 65

Current Carrying Capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature. Measuring and testing techniques according to DIN EN 60 512-5.

- ① Wire gauge: 0.5 mm²
- ② Wire gauge: 1.5 mm²
- ③ Wire gauge: 2.5 mm²





Number of contacts

8 +

Available by July 2009



Inserts with Han-Quick Lock® Termination


Identification	Part-Number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Han® Q 8/0 Quick Lock


Male insert



09 12 008 2633





contact arrangement view termination side



Female insert




09 12 008 2733




Assembly Manual

Remove cable jacket and strip the fine stranded wires




Push fine stranded wires into the Han-Quick Lock® contact and push the blue slide with a screw driver¹⁾ until it comes to a stop



Removal Manual

Please insert the screw driver¹⁾ at an angle of 45° into the opening and lever the blue slide out



¹⁾ Screw driver: 0.4 x 2.5 mm or 0.5 x 3.0 mm



Features

- Innovative Han-Quick Lock® termination technology
- Field assembly without special tools
- Compatible with Han® 7 D standard inserts with crimp terminals
- Reduced wiring times
- Insert suitable for plastic hoods and housings using the Han® 3 A size
- Space-saving and compact design
- Leading protective ground contact


Technical characteristics

Specifications	DIN EN 60 644-1 DIN EN 61 984
Inserts	
Number of contacts	7 + PE
Electrical data acc. to DIN EN 61 984	10 A 250 V 4 kV 3
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Termination	Han-Quick Lock®
Insulation resistance	≥ 10 ¹⁰ Ω
Material insert	Polycarbonate
Material seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles
Contacts	
Material	Copper alloy
Surface	
- hard silver plated	3 μm Ag
Contact resistance	≤ 3 mΩ
Han-Quick Lock®	
- mm ²	0.34 – 1.5 mm ²
- AWG	22 – 16
Maximum insulation cross section	ø = 3.0 mm
Plastic hoods/ housings	
Material	Polycarbonate RAL 7032
Locking element	Polyamide RAL 7032
Flammability acc. to UL 94	V 0
Hoods/ housings seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 in locked position	IP 65

Number of contacts

7 +

Available by June 2009



Inserts with Han-Quick Lock® Termination

Identification Part-Number Drawing Dimensions in mm


Han® 7 D Quick Lock

Male insert




09 21 007 2632

M



Contact arrangement view termination side





Female insert




09 21 007 2732

F




Assembly Manual

Remove cable jacket and strip the fine stranded wires




Push fine stranded wires into the Han-Quick Lock® contact and push the black slide with a screw driver¹⁾ until it comes to a stop



Removal Manual

Please insert the screw driver¹⁾ at an angle of 45° into the opening and lever the black slide out



¹⁾ Screw driver: 0.4 x 2.5 mm



Features

- Innovative Han-Quick Lock® termination technology
- Field assembly without special tools
- Compatible with Han® 8 D standard inserts with crimp terminals
- Reduced wiring times
- Insert suitable for metal hoods and housings using the Han® 3 A size
- Space-saving and compact design
- Leading protective ground contact

Technical characteristics

Specifications	DIN EN 60 644-1 DIN EN 61 984
Inserts	
Number of contacts	8
Electrical data acc. to DIN EN 61 984	10 A ~50V/-120V 0,8 kV 3
Rated current	10 A
Rated voltage	~50 V / -120 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Termination	Han-Quick Lock®
Insulation resistance	≥ 10 ¹⁰ Ω
Material insert	Polycarbonate
Material seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles
Contacts	
Material	Copper alloy
Surface	
- hard silver plated	3 μm Ag
Contact resistance	≤ 3 mΩ
Han-Quick Lock®	
- mm ²	0.34 – 1.5 mm ²
- AWG	22 – 16
Maximum insulation cross section	ø = 3.0 mm
Metal hoods/ housings	
Material	Die cast aluminium
Locking element	Metal
Flammability acc. to UL 94	V 0
Hoods/ housings seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 in locked position with seal screw	IP 44 IP 65



Number of contacts

8

Available by June 2009



Inserts with Han-Quick Lock® Termination

Identification Part-Number Drawing Dimensions in mm


Han® 8 D Quick Lock

Male insert




09 36 008 2632

M



Contact arrangement view termination side





Female insert




09 36 008 2732

F




Assembly Manual

Remove cable jacket and strip the fine stranded wires




Push fine stranded wires into the Han-Quick Lock® contact and push the black slide with a screw driver¹⁾ until it comes to a stop



Removal Manual

Please insert the screw driver¹⁾ at an angle of 45° into the opening and lever the black slide out



¹⁾ Screw driver: 0.4 x 2.5 mm

Features


- Innovative Han-Quick Lock® termination technology
- Field assembly without special tools
- Mating compatible with standard Han® DD Modul with crimp terminal
- Reduced wiring times

Technical characteristics


Specifications	DIN EN 60 644-1 DIN EN 61 984
Inserts	
Number of contacts	12
Electrical data acc. to DIN EN 61 984	10 A 250 V 4 kV 3
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Termination	Han-Quick Lock®
Insulation resistance	≥ 10 ¹⁰ Ω
Material insert	Polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles
Contacts	
Material	Copper alloy
Surface	
- hard silver plated	3 µm Ag
Contact resistance	≤ 3 mΩ
Han-Quick Lock®	
- mm ²	0.34 – 1.5 mm ²
- AWG	22 – 16

Assembly Manual

Remove cable jacket and strip the fine stranded wires




Push fine stranded wires into the Han-Quick Lock® contact and push the black slide with a screw driver¹⁾ until it comes to a stop



Removal Manual

Please insert the screw driver¹⁾ at an angle of 45° into the opening and lever the black slide out




¹⁾ Screw driver: 0.4 x 2.5 mm



Number of contacts

12

Available by October 2009



Inserts with Han-Quick Lock® termination

Identification	Part-Number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Han® DD module


with Han-Quick Lock® terminal

Male insert




09 14 012 2632

M



Contact arrangement
View termination side





Female insert



09 14 012 2732

F



Features


- Innovative Han-Quick Lock® termination technology
- Field assembly without special tools
- Mating compatible with standard Han® EE module with crimp terminal
- Reduced wiring times

Technical characteristics


Specifications	DIN EN 60 644-1 DIN EN 61 984
Inserts	
Number of contacts	8
Electrical data acc. to DIN EN 61 984	16 A 400 V 6 kV 3
Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Pollution degree 2 also	16 A 400/690 V 6 kV 2
Termination	Han-Quick Lock®
Insulation resistance	≥ 10 ¹⁰ Ω
Material insert	Polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles
Contacts	
Material	Copper alloy
Surface	
- hard silver plated	3 μm Ag
Contact resistance	≤ 1 mΩ
Han-Quick Lock®	
- mm ²	0.5 – 2.5 mm ²
- AWG	20 – 14

Assembly Manual

Remove cable jacket and strip the fine stranded wires




Push fine stranded wires into the Han-Quick Lock® contact and push the blue slide with a screw driver¹⁾ until it comes to a stop



Removal Manual

Please insert the screw driver¹⁾ at an angle of 45° into the opening and lever the blue slide out




¹⁾ Screw driver: 0.4 x 2.5 mm or 0.5 x 3.0 mm



Number of contacts

8



Inserts with Han-Quick Lock® termination

Identification	Part-Number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------


Han® EE module
with Han-Quick Lock® terminal

Male insert



09 14 008 2633

M




Female insert



09 14 008 2733

F




Features

- Compact and space saving
- High degree of flexibility due to modular assembly
- Easy and quick assembly
- Robust design
- Hood consists of two parts
- Good EMC shielding between the two modules

Technical characteristics

Hoods/Housings

Material	aluminium die-cast
Surface	powder-coated
Panel feed through housing/ Shielding frame	zinc die-cast alloy
Locking element	Han-Easy Lock®
Hoods/Housings sealing	NBR
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 65
Mechanical working life - mating cycles	≥ 500
PE contact wire gauge	10 mm ² / AWG 8
Stripping length	10 mm
Tightening torque	1 Nm



- ① Hood with top entry
- ② Carrier hood
- ③ Bulkhead mounted housing with locking lever
- ④ Switch cabinet panel
- ⑤ Panel feed through housing
- ⑥ Thread M32



Hoods and housings

Identification	Part number	Drawing	Dimensions in mm
Hood Top entry M32	19 14 002 0402		
Shielding frame	09 14 000 9924		
Carrier hood	09 14 002 0311		
Bulkhead mounted housing	09 14 002 0301		
Panel feed through housing	09 14 000 9928 NEW		

Features

- Suitable for all Han-Modular® single modules
- The variant with PE connection uses pin 1 of the Han® module as PE
- Slim, space saving design
- Low cost plastic hoods and housings


Technical characteristics

Specifications	DIN EN 60 664-1 DIN EN 61 984
Material	
Hood/housing	Polycarbonate
Seal	NBR
Cable gland	Polyamide
Limiting temperatures	-40 °C ... +85 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles
Protection degree acc. to DIN EN 60 529 in locked position	IP 20 / IP 65












Overview of suitable modules




Available by August 2009











Plastic hoods and housings for 1 module

Identification	Flexible A ... F	Fixed a ... f	Drawings	Dimensions in mm
<p>Hood with PE marking (Pin 1 = PE) IP 65 top entry</p> 	<p>09 14 001 0421</p>			
<p>Hood with PE marking (Pin 1 = PE) IP 20 top entry</p> 	<p>09 14 001 0423</p>			
<p>Bulkhead mounted housing with PE marking (Pin 1 = PE) IP 20 / IP 65</p> 	<p>09 14 001 0321</p>		 <p>panel cut out</p>	
<p>Coding Pin</p> 	<p>09 14 000 9929</p>		<p>Delivery frame: 8 pieces per frame</p>	

Available by August 2009



Plastic hoods and housings for 1 module

Identification	Flexible A ... F	Fixed a ... f	Drawings	Dimensions in mm
<p>Hood without PE IP 65 top entry</p> 	<p>09 14 001 0420</p>			
<p>Hood without PE IP 20 top entry</p> 	<p>09 14 001 0422</p>			
<p>Bulkhead mounted housing without PE IP 20 / IP 65</p> 	<p>09 14 001 0320</p>			
<p>Coding Pin</p> 	<p>09 14 000 9929</p>			<p>Delivery frame: 8 pieces per frame</p>



Fixing bracket

Features

- Compact and space saving
- High degree of flexibility due to modular assembly
- Pre-assembled modules can easily be snapped into pre-assembled housings
- Easy and quick assembly
- Robust design

Technical characteristics

Material	zinc die-cast alloy
Surface	nickel plated
Locking element	stainless steel
Fixing bracket	copper alloy, nickel plated
Hood/housing seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 in locked position	IP 65
Mechanical working life	≥ 500 cycles
PE contact	
Wire gauge	10 mm ² / AWG 8
Stripping length	10 mm
Tightening torque	1 Nm

Identification

Part Number


Drawing

Dimensions in mm

Bulkhead mounted housing




09 14 001 0301



Fixing bracket



09 14 000 9947










Features

- Suitable for all Han-Modular® modules
- Very robust design
- Solid pre-leading guid pins and float bushes
- Can be fixed with standard M4 screws
- Due to the plastic material used in the docking frame without PE, the panel will need to be grounded separately.

Technical characteristics

Specifications	DIN EN 60 664-1 DIN EN 61 984
Material	
Docking Frame	polycarbonate
Float washer	zinc die-cast alloy
Floating tolerance	± 2 mm
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles



Identification	Float mount A ... F	Fixed a ... f	Drawings	Dimensions in mm
<p>Docking frame for 4 modules</p> 	<p>09 14 016 1701</p>	<p>09 14 016 1711</p>		<p>floating tolerance: ± 2 mm</p>
<p>Docking frame for 6 modules</p> 	<p>09 14 024 1701</p>	<p>09 14 024 1711</p>		<p>floating tolerance: ± 2 mm</p>
<p>Float washer to enable the frame to be float mounted using standard M4 fixing screws</p> 	<p>09 14 000 9936</p>			


Features

- Crimp termination
- Plug compatible with Han® 40 A module axial screw termination

Technical characteristics

Specifications	DIN EN 60 664-1 DIN EN 61 984
Inserts	
Number of contacts	2
Electrical data acc. to DIN EN 61 984	40 A 1000 V 8 kV 3
Rated current	40 A
Rated voltage	1000 V
Rated impulse voltage	8 kV
Pollution degree	3
Insulation resistance	≥ 10 ¹⁰ Ω
Material	Polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles
Contacts	
Power contacts	
Material	Copper alloy
Surface	
- hard-silver plated	3 μm Ag
Contact resistance	≤ 0.3 mΩ
Crimp terminal	
- mm ²	1,5 - 10 mm ²
- AWG	16 ... 8

Current Carrying Capacity



Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5

- ① 24 B Hood/housing with 6 modules, wire gauge: 10 mm²
- ② 24 B Hood/housing with 6 modules, wire gauge: 6 mm²

Number of contacts

2



40 A module with crimp termination


Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
Han® 40 A module crimp terminal	09 14 002 3002	09 14 002 3102		Contact arrangement View termination side

Identification	Wire gauge mm ²	Part-Number		Drawings	Dimensions in mm																								
		Male contacts (M)	Female contacts (F)																										
Crimp contacts silver plated					<table border="1"> <thead> <tr> <th colspan="2">Wire gauge</th> <th>∅</th> <th>Stripping length of stranded wire</th> </tr> </thead> <tbody> <tr> <td>1.5 mm²</td> <td>AWG 16</td> <td>1.75 mm</td> <td>9.0 mm</td> </tr> <tr> <td>2.5 mm²</td> <td>AWG 14</td> <td>2.25 mm</td> <td>9.0 mm</td> </tr> <tr> <td>4.0 mm²</td> <td>AWG 12</td> <td>2.85 mm</td> <td>9.6 mm</td> </tr> <tr> <td>6.0 mm²</td> <td>AWG 10</td> <td>3.50 mm</td> <td>9.6 mm</td> </tr> <tr> <td>10 mm²</td> <td>AWG 8</td> <td>4.30 mm</td> <td>15 mm</td> </tr> </tbody> </table> <p>Stripping length a = 15 mm for cable ≥ 5mm Stripping length a = 18 mm for cable > 6.4mm</p>	Wire gauge		∅	Stripping length of stranded wire	1.5 mm ²	AWG 16	1.75 mm	9.0 mm	2.5 mm ²	AWG 14	2.25 mm	9.0 mm	4.0 mm ²	AWG 12	2.85 mm	9.6 mm	6.0 mm ²	AWG 10	3.50 mm	9.6 mm	10 mm ²	AWG 8	4.30 mm	15 mm
Wire gauge		∅	Stripping length of stranded wire																										
1.5 mm ²	AWG 16	1.75 mm	9.0 mm																										
2.5 mm ²	AWG 14	2.25 mm	9.0 mm																										
4.0 mm ²	AWG 12	2.85 mm	9.6 mm																										
6.0 mm ²	AWG 10	3.50 mm	9.6 mm																										
10 mm ²	AWG 8	4.30 mm	15 mm																										
	1.5	09 32 000 6104	09 32 000 6204																										
	2.5	09 32 000 6105	09 32 000 6205																										
	4	09 32 000 6107	09 32 000 6207																										
	6	09 32 000 6108	09 32 000 6208																										
	10	09 32 000 6109	09 32 000 6209																										


Features

- Crimp termination
- Remove of the contacts from the mating side
- Connect PE contact with special cable shoe
- Plug compatible with Han® 100 A module axial screw termination
- For crimp dies acc. to DIN 46 235


Assembly Details




Cut the cable head square and strip the insulation



The copper strands must be cleaned from dirt and oxid film



Copper strands must not be drilled




Insert the cable strand completely into the crimp ferrule.
Insertion check via inspection hole

Technical characteristics

Specifications	DIN EN 60 664-1 DIN EN 61 984
Inserts	
Number of contacts	2
Electrical data acc. to DIN EN 61 984	100 A 1000 V 8 kV 3
Rated current	100 A
Rated voltage conductor - ground	1000 V
Rated voltage conductor - conductor	1000 V
Rated impulse voltage	8 kV
Pollution degree	3
Insulation resistance	≥ 10 ¹⁰ Ω
Material	Polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles
Max. insulation diameter	14 mm
Contacts	
Power contacts	
Material	Copper alloy
Surface	
- hard-silver plated	3 μm Ag
Contact resistance	≤ 0.3 mΩ
Crimp terminal	
- mm ²	16 - 35 mm ²
Crimp dies	acc. to DIN 46 235

Current Carrying Capacity



Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5

with 3 modules in hoods/housings size 24 B

- ① Wire gauge: 16 mm²
- ② Wire gauge: 25 mm²
- ③ Wire gauge: 35 mm²

Number of contacts

2



100 A module with crimp termination

Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
Han® 100 A module Crimp terminal 	09 14 002 3051	09 14 002 3151		Contact arrangement view termination side

Identification	Wire gauge mm ²	Part-Number		Drawings	Dimensions in mm												
		Male contacts (M)	Female contacts (F)														
Crimp contacts silver plated 	16	09 11 000 6116	09 11 000 6216		<table border="1"> <thead> <tr> <th>Wire gauge</th> <th>ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>16 mm²</td> <td>5.5 mm</td> <td>19.0 mm</td> </tr> <tr> <td>25 mm²</td> <td>7.0 mm</td> <td>19.0 mm</td> </tr> <tr> <td>35 mm²</td> <td>8.2 mm</td> <td>16.0 mm</td> </tr> </tbody> </table>	Wire gauge	ø	Stripping length	16 mm ²	5.5 mm	19.0 mm	25 mm ²	7.0 mm	19.0 mm	35 mm ²	8.2 mm	16.0 mm
Wire gauge	ø	Stripping length															
16 mm ²	5.5 mm	19.0 mm															
25 mm ²	7.0 mm	19.0 mm															
35 mm ²	8.2 mm	16.0 mm															
	25	09 11 000 6125	09 11 000 6225														
	35	09 11 000 6135	09 11 000 6235														
* Crimp zone acc. to DIN EN 46 235 * for stranded wire acc. to IEC 60228 class 5																	

Identification	Wire gauge mm ²	Part-Number	
		Removal tool 	

Features


- Shielding bus separate from housing potential
- Ideal for the transmission of sensitive signals (e.g. bus signals)
- Suitable for Gigabit Ethernet Cat. 6

Technical characteristics

Specifications	DIN EN 60 664-1 DIN EN 61 984
Inserts	
Number of contacts	8
Insulation resistance	≥ 10 ¹⁰ Ω
Material	Polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles
GigaBit Contacts	
Number of contacts	8 + shielding
Electrical data acc. to DIN EN 61 984	5 A 50 V 0.8 kV 3
Rated current	5 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Material	
- Insulator	Polycarbonate
- Outer conductor	Zinc alloy
Contact resistance	≤ 4 mΩ
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Outer surface finish	Nickel
Cable diameter	5 ... 12 mm
D-Sub crimp contacts	
Crimp terminal	
- mm ²	0.08 ... 0.52 mm ²
- AWG	28 ... 20
Turned contacts	Performance level 1

Number of contacts

1 (8)



Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
Han® GigaBit module 	09 14 001 3011	09 14 001 3111	<p>M</p> <p>F</p>	<p>Contact arrangement View termination side</p>

Identification	Wire gauge mm ²	Part-Number		Drawings	Dimensions in mm												
		Male contacts (M)	Female contacts (F)														
Crimp contacts 8 + shielding crimp contacts order separately 		09 14 008 3011	09 14 008 3111	<p>M</p> <p>F</p>													
D-Sub crimp contacts 	0.08-0.21	61 03 000 0078	61 03 000 0080		<table border="1"> <thead> <tr> <th>Wire gauge</th> <th>∅</th> <th>Stripping length of stranded wire</th> </tr> </thead> <tbody> <tr> <td>0.08 - 0.21 mm²</td> <td>AWG 28-24</td> <td>5 mm</td> </tr> <tr> <td>0.13 - 0.33 mm²</td> <td>AWG 26-22</td> <td>5 mm</td> </tr> <tr> <td>0.33 - 0.52 mm²</td> <td>AWG 22-20</td> <td>5 mm</td> </tr> </tbody> </table>	Wire gauge	∅	Stripping length of stranded wire	0.08 - 0.21 mm ²	AWG 28-24	5 mm	0.13 - 0.33 mm ²	AWG 26-22	5 mm	0.33 - 0.52 mm ²	AWG 22-20	5 mm
Wire gauge	∅	Stripping length of stranded wire															
0.08 - 0.21 mm ²	AWG 28-24	5 mm															
0.13 - 0.33 mm ²	AWG 26-22	5 mm															
0.33 - 0.52 mm ²	AWG 22-20	5 mm															
	0.13-0.33	61 03 000 0094	61 03 000 0096														
	0.33-0.52	61 03 000 0073	61 03 000 0074														

Identification	Part-Number	Drawings	Dimensions in mm																																																					
<p>Crimp flange</p> <table border="0"> <tr> <td>D1</td> <td>D2</td> </tr> <tr> <td>3.0</td> <td>4.0</td> </tr> <tr> <td>3.5</td> <td>4.5</td> </tr> <tr> <td>4.0</td> <td>5.0</td> </tr> <tr> <td>4.5</td> <td>5.5</td> </tr> <tr> <td>5.0</td> <td>6.0</td> </tr> <tr> <td>5.5</td> <td>6.5</td> </tr> <tr> <td>6.0</td> <td>7.0</td> </tr> <tr> <td>6.5</td> <td>7.5</td> </tr> <tr> <td>7.0</td> <td>8.0</td> </tr> <tr> <td>7.5</td> <td>8.5</td> </tr> <tr> <td>8.0</td> <td>9.0</td> </tr> <tr> <td>8.5</td> <td>9.5</td> </tr> <tr> <td>9.0</td> <td>10.0</td> </tr> </table>	D1	D2	3.0	4.0	3.5	4.5	4.0	5.0	4.5	5.5	5.0	6.0	5.5	6.5	6.0	7.0	6.5	7.5	7.0	8.0	7.5	8.5	8.0	9.0	8.5	9.5	9.0	10.0	<table border="0"> <tr> <td>61 03 000 0062</td> </tr> <tr> <td>61 03 000 0063</td> </tr> <tr> <td>61 03 000 0064</td> </tr> <tr> <td>61 03 000 0065</td> </tr> <tr> <td>61 03 000 0066</td> </tr> <tr> <td>61 03 000 0166</td> </tr> <tr> <td>61 03 000 0067</td> </tr> <tr> <td>61 03 000 0068</td> </tr> <tr> <td>61 03 000 0069</td> </tr> <tr> <td>61 03 000 0070</td> </tr> <tr> <td>61 03 000 0071</td> </tr> <tr> <td>61 03 000 0165</td> </tr> <tr> <td>61 03 000 0072</td> </tr> </table>	61 03 000 0062	61 03 000 0063	61 03 000 0064	61 03 000 0065	61 03 000 0066	61 03 000 0166	61 03 000 0067	61 03 000 0068	61 03 000 0069	61 03 000 0070	61 03 000 0071	61 03 000 0165	61 03 000 0072														
D1	D2																																																							
3.0	4.0																																																							
3.5	4.5																																																							
4.0	5.0																																																							
4.5	5.5																																																							
5.0	6.0																																																							
5.5	6.5																																																							
6.0	7.0																																																							
6.5	7.5																																																							
7.0	8.0																																																							
7.5	8.5																																																							
8.0	9.0																																																							
8.5	9.5																																																							
9.0	10.0																																																							
61 03 000 0062																																																								
61 03 000 0063																																																								
61 03 000 0064																																																								
61 03 000 0065																																																								
61 03 000 0066																																																								
61 03 000 0166																																																								
61 03 000 0067																																																								
61 03 000 0068																																																								
61 03 000 0069																																																								
61 03 000 0070																																																								
61 03 000 0071																																																								
61 03 000 0165																																																								
61 03 000 0072																																																								
<p>Crimp ferrule</p> <table border="0"> <tr> <td>D3</td> <td>D4</td> </tr> <tr> <td>5.0</td> <td>6.0</td> </tr> <tr> <td>5.5</td> <td>6.5</td> </tr> <tr> <td>6.0</td> <td>7.0</td> </tr> <tr> <td>6.5</td> <td>7.5</td> </tr> <tr> <td>7.0</td> <td>8.0</td> </tr> <tr> <td>7.5</td> <td>8.5</td> </tr> <tr> <td>8.0</td> <td>9.0</td> </tr> <tr> <td>8.5</td> <td>9.5</td> </tr> <tr> <td>9.0</td> <td>10.0</td> </tr> <tr> <td>9.5</td> <td>10.5</td> </tr> <tr> <td>10.0</td> <td>11.0</td> </tr> <tr> <td>10.5</td> <td>11.5</td> </tr> <tr> <td>11.0</td> <td>12.0</td> </tr> <tr> <td>11.5</td> <td>12.5</td> </tr> <tr> <td>12.0</td> <td>13.0</td> </tr> <tr> <td>12.5</td> <td>13.5</td> </tr> <tr> <td>13.0</td> <td>14.0</td> </tr> </table>	D3	D4	5.0	6.0	5.5	6.5	6.0	7.0	6.5	7.5	7.0	8.0	7.5	8.5	8.0	9.0	8.5	9.5	9.0	10.0	9.5	10.5	10.0	11.0	10.5	11.5	11.0	12.0	11.5	12.5	12.0	13.0	12.5	13.5	13.0	14.0	<table border="0"> <tr> <td>61 03 000 0045</td> </tr> <tr> <td>61 03 000 0046</td> </tr> <tr> <td>61 03 000 0047</td> </tr> <tr> <td>61 03 000 0048</td> </tr> <tr> <td>61 03 000 0049</td> </tr> <tr> <td>61 03 000 0050</td> </tr> <tr> <td>61 03 000 0051</td> </tr> <tr> <td>61 03 000 0052</td> </tr> <tr> <td>61 03 000 0053</td> </tr> <tr> <td>61 03 000 0054</td> </tr> <tr> <td>61 03 000 0055</td> </tr> <tr> <td>61 03 000 0056</td> </tr> <tr> <td>61 03 000 0057</td> </tr> <tr> <td>61 03 000 0058</td> </tr> <tr> <td>61 03 000 0142</td> </tr> <tr> <td>61 03 000 0059</td> </tr> <tr> <td>61 03 000 0127</td> </tr> </table>	61 03 000 0045	61 03 000 0046	61 03 000 0047	61 03 000 0048	61 03 000 0049	61 03 000 0050	61 03 000 0051	61 03 000 0052	61 03 000 0053	61 03 000 0054	61 03 000 0055	61 03 000 0056	61 03 000 0057	61 03 000 0058	61 03 000 0142	61 03 000 0059	61 03 000 0127		
D3	D4																																																							
5.0	6.0																																																							
5.5	6.5																																																							
6.0	7.0																																																							
6.5	7.5																																																							
7.0	8.0																																																							
7.5	8.5																																																							
8.0	9.0																																																							
8.5	9.5																																																							
9.0	10.0																																																							
9.5	10.5																																																							
10.0	11.0																																																							
10.5	11.5																																																							
11.0	12.0																																																							
11.5	12.5																																																							
12.0	13.0																																																							
12.5	13.5																																																							
13.0	14.0																																																							
61 03 000 0045																																																								
61 03 000 0046																																																								
61 03 000 0047																																																								
61 03 000 0048																																																								
61 03 000 0049																																																								
61 03 000 0050																																																								
61 03 000 0051																																																								
61 03 000 0052																																																								
61 03 000 0053																																																								
61 03 000 0054																																																								
61 03 000 0055																																																								
61 03 000 0056																																																								
61 03 000 0057																																																								
61 03 000 0058																																																								
61 03 000 0142																																																								
61 03 000 0059																																																								
61 03 000 0127																																																								
<p>Cable clamp</p> <p>cable diameter approx. 5 ... 7 mm cable diameter approx. ca. 7 ... 10 mm cable diameter approx. ca. 10 ... 12 mm</p>	<table border="0"> <tr> <td>61 03 000 0141</td> </tr> <tr> <td>61 03 000 0042</td> </tr> <tr> <td>61 03 000 0143</td> </tr> </table>	61 03 000 0141	61 03 000 0042	61 03 000 0143																																																				
61 03 000 0141																																																								
61 03 000 0042																																																								
61 03 000 0143																																																								


Features

- Crimp termination
- Plug compatible with Han® HC module axial screw termination
- Designed for thick cable insulations
- For crimp dies acc. to DIN 46 235


Assembly Details




Cut the cable head square and strip the insulation



The copper strands must be cleaned from dirt and oxid film



Copper strands must not be drilled



Insert the cable strand completely into the crimp ferrule.
Insertion check via inspection hole

Technical characteristics

Specifications	DIN EN 60 664-1 DIN EN 61 984
Inserts	
Electrical data acc. to DIN EN 61 984	
Rated current	350 A
Rated voltage	2000 V
Rated voltage	4000 V with adapter
Rated impulse voltage	12 kV / 18 kV
Pollution degree	3
Insulation resistance	≥ 10 ¹⁰ Ω
Material	Polyamide
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles

Contacts

Power contacts	
Material	Copper alloy
Surface	
- hard-silver plated	3 µm Ag
Contact resistance	≤ 0.3 mΩ
Crimp terminal	
- mm ²	35 - 120 mm ²
Max. insulation diameter	22 mm
Crimp dies	acc. to DIN 46 325
Pressing force requirement	130 kN

For more information to create different contact arrangements please refer to main catalogue HARTING Industrial Connectors Han® chapter 14, from page 14 on.



Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
Han® HC module 350 Crimp terminal	09 11 001 3001	09 11 001 3101	<p>M</p> <p>F</p>	

Identification	Wire gauge mm ²	Part-Number		Drawings	Dimensions in mm																		
		Male contacts (M)	Female contacts (F)																				
Crimp contacts* Silver plated																							
	35 ¹⁾	09 11 000 6140	09 11 000 6240	<p>1)</p> <p>4)</p>																			
	50 ²⁾	09 11 000 6141	09 11 000 6241	<p>2)</p> <p>5)</p>																			
	70 ³⁾	09 11 000 6142	09 11 000 6242	<p>3)</p>																			
	95 ⁴⁾	09 11 000 6143	09 11 000 6243																				
	120 ⁵⁾	09 11 000 6144	09 11 000 6244																				
<table border="1"> <thead> <tr> <th>Wire gauge</th> <th>∅</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>35 mm²</td> <td>8.2 mm</td> <td>26 mm</td> </tr> <tr> <td>50 mm²</td> <td>10.0 mm</td> <td>28 mm</td> </tr> <tr> <td>70 mm²</td> <td>11.5 mm</td> <td>28 mm</td> </tr> <tr> <td>95 mm²</td> <td>13.5 mm</td> <td>30 mm</td> </tr> <tr> <td>120 mm²</td> <td>15.5 mm</td> <td>24 mm</td> </tr> </tbody> </table>						Wire gauge	∅	Stripping length	35 mm ²	8.2 mm	26 mm	50 mm ²	10.0 mm	28 mm	70 mm ²	11.5 mm	28 mm	95 mm ²	13.5 mm	30 mm	120 mm ²	15.5 mm	24 mm
Wire gauge	∅	Stripping length																					
35 mm ²	8.2 mm	26 mm																					
50 mm ²	10.0 mm	28 mm																					
70 mm ²	11.5 mm	28 mm																					
95 mm ²	13.5 mm	30 mm																					
120 mm ²	15.5 mm	24 mm																					
* Crimp zone acc. to DIN EN 46 235																							
* for stranded wire acc. to IEC 60 228 class 5																							


Features

- Crimp termination
- Plug compatible with Han® HC module 650 axial screw termination
- Contact in one piece


Assembly Details




Cut the cable head square and strip the insulation



The copper strands must be cleaned from dirt and oxid film



Copper strands must not be drilled



Insert the cable strand completely into the crimp ferrule.
Insertion check via inspection hole

Technical characteristics

Specifications DIN EN 60 664-1
DIN EN 61 984

Inserts


Electrical data acc. to
DIN EN 61 984

Rated current	650 A
Rated voltage	2000 V
Rated voltage	4000 V with adapter
Rated impulse voltage	12 kV / 18 kV
Pollution degree	3
Insulation resistance	$\geq 10^{10} \Omega$
Material	Polyamide
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles

Contacts

Power contacts	
Material	Copper alloy
Surface	
- hard-silver plated	3 μm Ag
Contact resistance	$\leq 0.3 \text{ m}\Omega$
Crimp terminal	
- mm^2	240 mm^2
Max. insulation diameter	33 mm
Pressing force requirement	130 kN

Current Carrying Capacity





The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.



Measuring and testing techniques according to
DIN EN 60 512-5




With 2 modules in hoods/housings size 24 B Han® HPR
Wire gauge: 240 mm^2



Modular High Current Connector System

Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
Han® HC module 650 Crimp terminal 	09 11 001 3011	09 11 001 3111		

Identification	Wire gauge mm ²	Part-Number		Drawings	Dimensions in mm						
		Male contacts (M)	Female contacts (F)								
Crimp contacts* Silver plated  Further cable diameters on request	240	09 11 000 6167	09 11 000 6267		<table border="1"> <thead> <tr> <th>Wire gauge</th> <th>Ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>240 mm²</td> <td>22.5 mm</td> <td>46 mm</td> </tr> </tbody> </table> * for stranded wire acc. to IEC 60 228 class 5	Wire gauge	Ø	Stripping length	240 mm ²	22.5 mm	46 mm
Wire gauge	Ø	Stripping length									
240 mm ²	22.5 mm	46 mm									

Identification	Part-Number		Drawing	Dimensions in mm
	for hood	for housing		
Frames 1 pole 	—	09 11 000 9971	09 11 000 9971	
2 pole 	—	09 11 000 9972	09 11 000 9972	



With 3 x Han® Q 2/0
Part-Number: 09 12 008 4752

Features Han-Power® T


- 1 connection for power input
- 1 connection for power output
- 1 T-connection to device
- 2 power contacts
- Plastic housings are integrated in the moulding
- Plastic connector hood

Technical characteristics

Han-Power® T


Rated voltage	400 V
Rated voltage	600 V (acc. to UL)
Rated current	40 A
Number of contacts	2 power contacts + PE max. 4 - 6 mm ²

Dimensions in mm



Current Carrying Capacity

Control and test procedures acc. to DIN IEC 60 512-5



Han® 3 A Hoods

Material	Polycarbonate RAL 9005
Temperature range	-40 °C ... +125 °C
Protection degree acc. to DIN 60 529	IP 65 / IP 67

Han® Q 2/0

Number of contacts	2 + PE
Electrical data acc. to DIN EN 61 984	40 A 400 V 6 kV 3
Rated current	40 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Material	Polycarbonate
Insulation resistance	≥ 10 ¹⁰ Ω
Temperature range	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles



With Han-Modular® Twin
Part-Number: 09 12 008 4760

Features Han-Power® T



- 1 connection for mixed power input and output
- 1 T-connection to device
- 3 power contacts
- 4 signal contacts
- Metal hood
- Locking lever Han-Easy Lock®

Technical characteristics


Han-Power® T Modular Twin hood

Rated voltage	400 V
Rated current	40 A
Number of contacts	3 power contacts + PE max. 6 mm ² 4 signal contacts max. 4.0 mm ²
Surface	powder coated RAL 7037
Sealing	NBR
Temperature range	-40 °C ... +125 °C
Protection degree acc. to DIN 60 529	IP 65

Han-Modular® Twin Hoods



Wiring diagram



Suitable inserts

Han® C module with crimp termination

Number of contacts	3
Electrical data acc. to DIN EN 61 984	40 A 400/690 V 6 kV 3
Rated current	40 A
Rated voltage	400 V
Conductor - Ground	400 V
Conductor - Conductor	690 V
Rated impulse voltage	6 kV
Pollution degree	3

Han® EE module with crimp termination

Number of contacts	4
Electrical data acc. to DIN EN 61 984	16 A 400 V 6 kV 3
Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Material	Polycarbonate
Insulation resistance	≥ 10 ¹⁰ Ω
Temperature range	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ mating cycles

For more Han-Modular® inserts see chapter 6 in the main catalogue of HARTING Electric GmbH & Co. KG



Ethernet Switch
HARTING eCon 4000
 Ethernet Switches, unmanaged,
 for flat wall mounting

General Description	Features
---------------------	----------

<p>The Fast Ethernet Switches of the product family HARTING eCon 4000 are recommended for use in the widest range of industrial applications and support both Ethernet (10 Mbit/s) and Fast Ethernet (100 Mbit/s). The product family enables the connection of up to 8 network devices over Twisted Pair cables.</p> <p>The eCon 4000 Ethernet Switch product family, with its integrated LEDs, supports fast and easy network diagnosis. The eCon Ethernet Switch operates as an Unmanaged Switch in Store and Forward Switching Mode and supports Auto-crossing, Auto-negotiation and Auto-polarity.</p>	<ul style="list-style-type: none"> • Ethernet Switch according to IEEE 802.3 • Ethernet (10 Mbit/s) and Fast Ethernet (100 Mbit/s) • Auto-crossing • Auto-negotiation • Auto-polarity • Store and Forward Switching Mode, non blocking • Diagnostic LEDs (Link status, Data, Power) • Mounting onto wall, optionally onto top-hat mounting rail
---	---

Advantages	Application fields
------------	--------------------

<ul style="list-style-type: none"> • Robust metal housing and flat housing style • EMC, temperature range and mechanical stability meet the highest demands • Wide range for power supply input • Wide range for type test according to EN 50 155 and EN 50 121-3-2 	<ul style="list-style-type: none"> • Railway applications • Industrial automation • Automotive industry • Wind power
---	--

Technical characteristics

Ethernet interface

Number of ports	8x 10/100Base-T(X)
Cable types according to IEEE 802.3	Shielded Twisted Pair (STP) or Unshielded Twisted Pair (UTP), Category 5
Data rate	10 Mbit/s or 100 Mbit/s
Maximum cable length	100 m (Twisted Pair; with Category 5 cable acc. to DIN EN 50 173-1)
Termination	M12 D-coding
Diagnostics (via LED) Link (per port)	<ul style="list-style-type: none"> • Status Link – ON • Data transfer (Act) – flashing • Data transfer rate (Speed) – 100 Mbit/s: Yellow / 10 Mbit/s: Green
PoE (per port)	<ul style="list-style-type: none"> • no PoE device – OFF • PoE device connected – Green • PoE device with failure – Red
Topology	Line, Star or mixed

Power supply

Input voltage							
eCon 4080-BPoE1							
mode PoE	48 V DC (46 ... 55 V DC)						
mode non PoE	24 / 48 V DC (12 ... 60 V DC)						
eCon 4080-B3	72 / 110 V DC (50.4 ... 137.5 V DC)						
Termination	M12 A-coding, male, for redundant power supply						
Diagnostics (via LED)	<table border="0" style="width: 100%;"> <tr> <td>Pwr x9 (switch)</td> <td>Pwr PoE (mode PoE)</td> </tr> <tr> <td>Power supply – Green</td> <td>> 45 V DC – Green</td> </tr> <tr> <td></td> <td>< 45 V DC – OFF</td> </tr> </table>	Pwr x9 (switch)	Pwr PoE (mode PoE)	Power supply – Green	> 45 V DC – Green		< 45 V DC – OFF
Pwr x9 (switch)	Pwr PoE (mode PoE)						
Power supply – Green	> 45 V DC – Green						
	< 45 V DC – OFF						

Design features

Housing material	Metal (powder coated)
Dimensions (W x H x D)	130 x 166 x 50 mm
Degree of protection acc. to DIN 60529	IP 40 / IP 30 (eCon 4080-BPoE1 only)
Mounting	Wall mounting, flat
Weight	approx. 0.85 kg

Environmental conditions

Operating temperature	–40 °C ... +70 °C
Storage temperature	–40 °C ... +85 °C
Relative humidity	10 % ... 95 % (non-condensing)

Ethernet Switch
HARTING eCon 4080-B3
 8-port Ethernet Switch (110 V DC) for flat installation





Unmanaged	IP 40	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input type="checkbox"/>
-----------	-------	---	---

Number of ports, Copper / Termination	8x 10/100Base-T(X) / M12 D-coding
Input voltage / Termination	72 / 110 V DC / M12 A-coding, male, for redundant power supply
Permissible range (min/max)	50.4 V ... 137.5 V DC
Input current	approx. 40 mA (at 110 V DC)
Housing material	Metal (powder coated)
Dimensions (W x H x D)	130 x 166 x 50 mm
Weight	approx. 0.85 kg
Operating temperature	-40 °C ... +70 °C
Approvals	cUL (in preparation)

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING eCon 4080-B3
 Ethernet Switch 110 V DC
 with 8 ports M12 D-coding
 for wall mounting

20 77 208 3003





Ethernet Switch
HARTING eCon 4080-BPoE1
 8-port Ethernet Switch for flat installation

Unmanaged	IP 30	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input type="checkbox"/>
-----------	-------	---	---

Number of ports, Copper / Termination 8x 10/100Base-T(X) / M12 D-coding / PoE supports 8 ports

Mode PoE

Input voltage / Termination 48 V DC / M12 A-coding, male, for redundant power supply
 Permissible range (min/max) 46 V ... 55 V DC
 Input current max. 3.6 A (at 48 V DC)

Mode Non-PoE



Input voltage / Termination 24 / 48 V DC / M12 A-coding, male, for redundant power supply
 Permissible range (min/max) 12 V ... 60 V DC
 Input current approx. 150 mA (at 24 V DC)

Housing material Metal (powder coated)
 Dimensions (W x H x D) 130 x 166 x 50 mm
 Weight approx. 0.85 kg
 Operating temperature -40 °C ... +70 °C
 Approvals cUL (in preparation)

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING eCon 4080-BPoE1
 Ethernet Switch PoE
 with 8 ports M12 D-coding
 for wall mounting

20 77 208 3009



Introduction

For the user, HARTING's novel and innovative solutions open up new, more convenient and extensive options for configuring Unmanaged Ethernet Switches. The solutions available to date offered only very limited or basic options for making alterations to different settings on an Ethernet Switch.

The user made changes to the settings or the configuration via the DIP switches on the Ethernet Switch. The extensive possibilities for applications were physically restricted by the enormous space requirements of the mechanical solution.

Now for the first time, HARTING's sCon solution makes it possible for the user to realise more configurations than have been possible to date.

Ease of handling and simple operation have been designed in to meet real-life application requirements. Simple and fast configuration is what this solution aims to achieve.

All sCon Ethernet Switches can be configured via a USB connection cable.

At first sight, sCon Ethernet Switches do not differ from the Ethernet Switches available to date. However, the possibilities that sCon has to offer become more than apparent to the user when he connects the Ethernet Switch via the front-side USB socket to a PC, laptop or hand-held PC.




Figure 1 The Start-up menu

Once the sCon Ethernet Switch has been connected to a PC, it can be accessed on-screen in much the same manner as a commercially available USB stick (Figure 1: The Start-up menu).

The user only has to copy the sCon software in advance onto the PC. No administrator rights are required. The Ethernet Switch does not have to be connected to a power supply for configuration purposes. That means that the configuration procedure can take place at the user's location of choice:

in the office, workshop or production facility. The sCon Ethernet Switch automatically detects which power supply is connected: mains supply or power supply via the USB port. Please note that it is not possible to operate the Ethernet Switch purely via the USB port. For normal industrial operations, the power must be supplied via one of the redundant inputs.

Introduction

Making configuration settings by means of DIP switches may appear to be uncomplicated. However, accidentally making an alteration to the configuration can happen more quickly than one would think possible, and in so doing make considerable changes to the previously set procedures. The sCon family prevents these inadvertent alterations to the configuration. No alteration can be made to the configuration without an USB connection and the software.

Each configuration can be archived and the backups retrieved for future projects. By making backups of the configuration, all settings can be conveniently stored in case servicing is necessary.

Archived configurations can be imported and printed out when convenient. These extensive options in sCon ensure that data security enjoys the significance it deserves.

The switch configuration is transmitted only when a new configuration is uploaded via the corresponding 'Send' button. This means that until the data has actually been uploaded, it is still possible to read-in the 'old' data from the sCon Ethernet Switch via the Refresh option. This means it is easily possible to reverse any inadvertent activation in the corresponding menu.




Figure 2 Example of a configuration

Once configured, the Ethernet Switch can be utilised immediately. The configuration remains stored in the Ethernet Switch after the USB cable is removed.

Meeting international standards, the USB port described is recognised as state-of-the-art technology. The standardised possibility for worldwide utilisation with all notebooks, PCs and Palmtops (revisions 1.0, 1.1 and 2.0) mean that this technology is suitable for universal usage.

The intuitive, but extensive options setting via the relevant buttons and the various options offered by sCon extend the range of applications for Unmanaged Ethernet Switches. With sCon, the gap between Unmanaged and manageable switches is getting smaller.

It is true that sCon is a solution for Unmanaged Ethernet Switches; however, it comes very close to Managed Ethernet Switch functionality.

Ethernet Switch HARTING sCon 3000

Ethernet Switch family, unmanaged,
for mounting onto top-hat mounting rail
in control cabinets including sCon functions



General Description

The Fast Ethernet Switches of the product family HARTING sCon 3000 can be configured via a USB port for special or more performance-oriented industrial usages. There are almost no limits to the different possibilities.

Activation of parallel and / or ring redundancy or port prioritisation will clearly increase the availability and reliability of data communications through the sCon 3000.

Features

- Ethernet Switch acc. to IEEE 802.3
- Store and Forward Switching Mode, non-blocking, unmanaged
- Auto-crossing, Auto-negotiation, Auto-polarity
- Diagnostic LEDs (Link status, Act, Power, Data transmission rate, Error)
- Following settings are available via USB port:
 - Alarm signalling contact
 - Auto-negotiation
 - 10/100/1000 Mbit/s
 - Full/Half Duplex
 - Ring and/or parallel redundancy
 - Port enable / disable
 - Port priority
 - Port mirroring
 - Pause Frame

Advantages

- Individually configurable via USB port
- Metal housing
- EMC, temperature range and mechanical stability meet the toughest demands
- Ring and/or parallel redundancy

Application fields

- Industrial automation
- Railway applications
- Power distribution systems
- Automotive industry
- Mechanical engineering

Technical characteristics sCon 3100-AA

Ethernet interface RJ45

Number of ports	8x 10/100Base-T(X), 2x 10/100/1000Base-T(X)
Cable types according to IEEE 802.3	Shielded Twisted Pair (STP) or Unshielded Twisted Pair (UTP), Category 5
Data rate	10 Mbit/s, 100 Mbit/s or 1000 Mbit/s (RJ45)
Maximum cable length	100 m (Twisted Pair; with Category 5 cable acc. to DIN EN 50 173-1)
Termination	RJ45 (Twisted Pair)
Diagnostics (via LED)	<ul style="list-style-type: none"> • Status Link – Green • Data transfer (Act) – Green flashing • Data transfer rate (Speed) – 1000 Mbit/s: Green 100 Mbit/s: Yellow 10 Mbit/s: OFF
Topology	Line, Ring, Star or mixed

Power supply

Input voltage	24 V DC
Termination	5-pole screw terminal, pluggable for redundant power supply
Diagnostics (via LED)	Power supply

Alarm signalling contact

Change-over contact, potential-free, 24 V DC / 0.5 A
3-pole pluggable screw contact

Design features

Housing material	Metal (powder coated)
Dimensions (W x H x D)	60 x 132 x 104 mm (incl. cap, without connectors)
Degree of protection acc. to DIN 60 529 sCon xxxx-AE	IP 30 IP 20
Mounting	<ul style="list-style-type: none"> • 35 mm top-hat rail acc. to EN 60 715 • Panel mounting, vertical assembly
Weight	approx. 0.6 kg

Environmental conditions

Operating temperature	-40 °C ... +70 °C
Storage temperature	-40 °C ... +85 °C
Relative humidity	10 % ... 95 % (non-condensing)



Ethernet Switch HARTING sCon 3100-AA

10-port Ethernet Switch for mounting onto top-hat mounting rail in control cabinets including 2 Gigabit ports and sCon functions extended temperature range


Unmanaged	IP 30	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input type="checkbox"/>
-----------	-------	---	---

Number of ports, Copper / Termination	8x 10/100Base-T(X) / RJ45 (Twisted Pair) 2x 10/100/1000Base-T(X) / RJ45 (Twisted Pair)
Input voltage / Termination	24 / 48 V DC / 5-pole screw terminal, pluggable redundant power supply
Permissible range (min/max)	9.6 V ... 60 V DC
Input current	approx. 240 mA (at 24 V DC)
Alarm signalling contact	Change-over contact, potential-free, 24 V DC / 0.5 A 3-pole pluggable screw contact
Housing material	Metal (powder coated)
Dimensions (W x H x D)	60 x 132 x 104 mm (incl. cap, without connectors)
Weight	approx. 0.6 kg
Operating temperature	-40 °C ... +70 °C
Approvals	UL 508
MTBF	670 000 h

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING sCon 3100-AA
Ethernet Switch
with 10 RJ45 ports
including
Set for assembly on standard rail

20 76 110 1001



Management functions

Basic Functions

	Store and Forward Switching Mode	IEEE 802.3
	Manual and Dynamic IP Address Assignment	
Port-Settings	Auto-negotiation on / off	
	Port Speed 10 Mbit/s / 100 Mbit/s / 1000 Mbit/s	
	Half / Full duplex	
	Port disable / enable	
	Link Up/Down Trap disable / enable	
	Flow Control disable / enable	
Network Discovery	Link Layer Discovery Protocol (LLDP)	802.1AB, 2005
Protocols	IPv4	RFC 791, 903, 951, 1293, 1519
	TCP	RFC 793, 896
	UDP	RFC 768
	Ethernet ARP	RFC 826
	ICMP	RFC 2521, 1191, 1788, 792
File Transfer	Firmware import and export via TFTP	
	Configuration import and export via TFTP	
Time Settings	Manual time setting	
	Simple Network Time Protocol (SNTP)	RFC 1305, RFC 4330
User Management	Admin, Guest and Service Level	
Service	Service Mode via port 1	

QoS

	Quality of Service (QoS)	IEEE 802.1p
--	--------------------------	-------------

VLAN

	Port protocol based VLANs	IEEE 802.1Q Rev D5.0, 2005
--	---------------------------	----------------------------

Redundancy

	Spanning Tree (STP)	IEEE 802.1D (2004)
	Rapid Spanning Tree (RSTP)	IEEE 802.1D (2004)

Security

	Port-Based Network Access Control Port Based Authentication with EAP	802.1x (2004)
	RADIUS Client	RFC 2138
	IP authorized manager	

Link Aggregation

	Link Aggregation (LACP)	ISO/IEC 8802-3:2005 (E), IEEE 802.3-2005 Edition Clause 43 (IEEE 802.3ad)
--	-------------------------	---

Multicast

	IGMP Snooping (v1, v2, v3) with support for querier	RFC 1112, 2236, 3376
--	---	----------------------

DHCP

	DHCP Client	RFC 2131
	DHCP relay agent	RFC 2131
	DHCP Option 82	RFC 3046

Alarm

	Alarms via E-mail (SMTP) and SNMP Traps	
	Signalling contact for low voltage detection or Link break	

Management functions

Diagnostic		
	Port diagnostic	
	Port Mirroring	
	Switch History	
	MAC Address Table	
	RMON (1,2,3 & 9 groups)	RFC 2819
Management		
	Password protected Web-Management interface	
	SNMP (v1, v2c, v3) agent & MIB support	RFC 1155, 1157, 1212, 1213, 1215, 2089, 2578, 3411, 3412, 3413, 3414, 3415, 3416, 3417, 3584
MIB Support		
	Enterprise (HARTING MIB)	
	MIB II	
	MIB II for SNMPv1, SNMPv2, SNMPv3	
	Interface group MIB	
	Bridge MIB	
	MIB for Ethernet-like interfaces (requires support in hardware)	
	VLAN MIB	
	Spanning Tree Protocol MIB	
	Rapid STP MIB	
	Port-based Network Authentication Control MIB	
	Definitions of managed objects for LLDP	
	802.1/LLDP extension MIB	
	802.3/LLDP extension MIB	
	Radius Client MIB	
	IPv4 MIB	
	IGMP MIB	
	DHCP	

The management functions described above are supported by all Ethernet Switches with the name mCon xxxx-..V

Ethernet Switch
 HARTING mCon 3000
 Ethernet Switches, managed,
 for mounting onto top-hat mounting rail
 in control cabinets



General Description

Features

The fully Managed Ethernet Switches of the product family HARTING mCon 3000 enable the connection of up to 10 network devices (according to type) over Twisted Pair cables and fibre-optic cables (Multi- and Singlemode). The mCon 3000 Ethernet Switch family, with its integrated LEDs on each port, supports fast and easy network diagnosis.

The mCon 3000 Ethernet Switches are designed for an effective, industrial and individual use. They support both SNMP and an easy Web interface for management functions.

- Ethernet Switch acc. to IEEE 802.3
- Store and Forward Switching Mode
- up to 10 ports, managed, non-blocking
- Auto-crossing, Auto-negotiation, Auto-polarity

Advantages

Application fields

- Metal housing
- EMC, temperature range and mechanical stability meet the highest demands
- Integrated management functions

- Industrial automation
- Automotive industry
- Wind power
- Power distribution systems

Technical characteristics

Ethernet interface RJ45

Number of ports	6x / 8x / 10x 10/100Base-T(X), 2x 10/100/1000Base-T(X)
Cable types according to IEEE 802.3	Shielded Twisted Pair (STP) or Unshielded Twisted Pair (UTP), Category 5
Data rate	10 Mbit/s, 100 Mbit/s or 1000 Mbit/s (RJ45)
Maximum cable length	100 m (Twisted Pair; with Category 5 cable acc. to DIN EN 50 173-1)
Termination	RJ45 (Twisted Pair)
Diagnostics (via LED)	<ul style="list-style-type: none"> • Status Link – Green • Data transfer (Act) – Green flashing • Data transfer rate (Speed) – 1000 Mbit/s: Green 100 Mbit/s: Yellow 10 Mbit/s: OFF
Topology	Ring, Line, Star or mixed

Power supply

Input voltage	24 V DC
Termination	5-pole screw terminal, pluggable for redundant power supply
Diagnostics (via LED)	Power supply

Alarm signalling contact

Change-over contact, potential-free, 24 V DC / 0.5 A
3-pole pluggable screw contact

Design features

Housing material	Metal (powder coated)
Dimensions (W x H x D)	60 x 132 x 104 mm (incl. cap, without connectors)
Degree of protection acc. to DIN 60529 mCon xxxx-AE	IP 30 IP 20
Mounting	<ul style="list-style-type: none"> • 35 mm top-hat rail acc. to EN 60715 • Panel mounting, vertical assembly
Weight	approx. 0.6 kg

Environmental conditions

Operating temperature	0 °C ... +70 °C / -40 °C ... +70 °C (mCon 3100 AAV only)
Storage temperature	-40 °C ... +85 °C
Relative humidity	10 % ... 95 % (non-condensing)

Technical characteristics - F.O. termination

Ethernet interface – F.O.

Number of ports	1x / 2x / 3x 100Base-FX
Cable types according to IEEE 802.3	Multimode fibre, 1300 nm; 50 / 125 µm or 62.5 / 125 µm
Data rate	100 Mbit/s
Maximum cable length	2000 m (Multimode)
Termination	SC-D female / ST female
Diagnostics (via LED)	<ul style="list-style-type: none"> • Status Link – Green • Data transfer (Act) – Green flashing
Wavelength	1300 nm
Transceive power T(X) max. (dynamic)	<ul style="list-style-type: none"> • -14 dBm (50 / 125 µm) • -14 dBm (62.5 / 125 µm)
Transmission power T(X) min.	<ul style="list-style-type: none"> • -23.5 dBm (50 / 125 µm) • -20 dBm (62.5 / 125 µm)
Receive power RX typical (dynamic)	<ul style="list-style-type: none"> • -33.9 dBm (window) • -35.2 dBm (centre)
Receive power RX max. (dynamic)	-14 dBm
Signal detection (dynamic)	-33 dBm
Topology	Line, Ring, Star or mixed



Ethernet Switch
HARTING mCon 3100-AV
 10-port Ethernet Switch for mounting onto top-hat mounting rail in control cabinets


Managed	IP 30	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
---------	-------	---	--

Number of ports, Copper / Termination	10x 10/100Base-T(X) / RJ45 (Twisted Pair)
Input voltage / Termination	24 V DC / 5-pole screw terminal, pluggable redundant power supply
Permissible range (min/max)	9.6 V ... 36 V DC
Input current	approx. 190 mA (at 24 V DC)
Alarm signalling contact	Change-over contact, potential-free, 24 V DC / 0.5 A 3-pole pluggable screw contact
Housing material	Metal (powder coated)
Dimensions (W x H x D)	60 x 132 x 104 mm (incl. cap, without connectors)
Weight	approx. 0.6 kg
Operating temperature	0 °C ... +70 °C
Approvals	UL 508
MTBF	625 000 h
Management	fully managed via Web interface and SNMP Functions see page 'Management functions'

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING mCon 3100-AV
 Ethernet Switch, managed
 10 RJ45 ports
 including
 Set for assembly on standard rail

20 76 110 4002





Ethernet Switch HARTING mCon 3100-AAV

10-port Ethernet Switch for mounting onto top-hat mounting rail
in control cabinets including 2 Gigabit ports;
with extended temperature range

Managed	IP 30	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
---------	-------	---	--

Number of ports, Copper / Termination	8x 10/100Base-T(X) / RJ45 (Twisted Pair) 2x 10/100/1000Base-T(X) / RJ45 (Twisted Pair)
Input voltage / Termination	24 / 48 V DC / 5-pole screw terminal, pluggable redundant power supply
Permissible range (min/max)	9.6 V ... 60 V DC
Input current	approx. 260 mA (at 24 V DC)
Alarm signalling contact	Change-over contact, potential-free, 24 V DC / 0.5 A 3-pole pluggable screw contact
Housing material	Metal (powder coated)
Dimensions (W x H x D)	60 x 132 x 104 mm (incl. cap, without connectors)
Weight	approx. 0.6 kg
Operating temperature	-40 °C ... +70 °C
Approvals	cUL (in preparation)
MTBF	720 000 h
Management	fully managed via Web interface and SNMP Functions see page 'Management functions'

Identification	Part number	Drawing	Dimensions in mm
HARTING mCon 3100-AAV Ethernet Switch, managed 10 RJ45 ports including Set for assembly on standard rail	20 76 110 4003		100 130 60



Ethernet Switch HARTING mCon 3061-ADV

7-port Ethernet Switch for mounting onto top-hat mounting rail
in control cabinets including 1 F.O. port (SC, MM)

Managed	IP 30	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
---------	-------	---	--


Number of ports, Copper / Termination	6x 10/100Base-T(X) / RJ45 (Twisted Pair)
Number of ports, F.O. / Termination	1x 100Base-FX / SC-D female
Input voltage / Termination	24 V DC / 5-pole screw terminal, pluggable redundant power supply
Permissible range (min/max)	9.6 V ... 36 V DC
Input current	approx. 270 mA (at 24 V DC)
Alarm signalling contact	Change-over contact, potential-free, 24 V DC / 0.5 A 3-pole pluggable screw contact
Housing material	Metal (powder coated)
Dimensions (W x H x D)	60 x 132 x 104 mm (incl. cap, without connectors)
Weight	approx. 0.6 kg
Operating temperature	0 °C ... +70 °C
Approvals	UL 508
MTBF	710 000 h
Management	fully managed via Web interface and SNMP Functions see page 'Management functions'

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING mCon 3061-ADV
Ethernet Switch, managed
6 RJ45 ports
1 SC port
including
Set for assembly on standard rail

20 76 107 4101

ST variant see catalogue 'Ethernet
Network Solutions Automation IT'





**Ethernet Switch
HARTING mCon 3063-ADV**

9-port Ethernet Switch for mounting onto top-hat mounting rail
in control cabinets including 3 F.O. ports (SC, MM)


Managed	IP 30	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
---------	-------	---	--

Number of ports, Copper / Termination	6x 10/100Base-T(X) / RJ45 (Twisted Pair)
Number of ports, F.O. / Termination	3x 100Base-FX / SC-D female
Input voltage / Termination	24 V DC / 5-pole screw terminal, pluggable redundant power supply
Permissible range (min/max)	9.6 V ... 36 V DC
Input current	approx. 320 mA (at 24 V DC)
Alarm signalling contact	Change-over contact, potential-free, 24 V DC / 0.5 A 3-pole pluggable screw contact
Housing material	Metal (powder coated)
Dimensions (W x H x D)	60 x 132 x 104 mm (incl. cap, without connectors)
Weight	approx. 0.6 kg
Operating temperature	0 °C ... +70 °C
Approvals	UL 508
MTBF	710 000 h
Management	fully managed via Web interface and SNMP Functions see page 'Management functions'

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING mCon 3063-ADV
Ethernet Switch, managed
6 RJ45 ports
3 SC ports
including
Set for assembly on standard rail

20 76 109 4101



ST variant see catalogue 'Ethernet
Network Solutions Automation IT'



**Ethernet Switch
HARTING mCon 3082-ADV**

10-port Ethernet Switch for mounting onto top-hat mounting rail
in control cabinets including 2 F.O. ports (SC, MM)


Managed	IP 30	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
---------	-------	---	--

Number of ports, Copper / Termination	8x 10/100Base-T(X) / RJ45 (Twisted Pair)
Number of ports, F.O. / Termination	2x 100Base-FX / SC-D female
Input voltage / Termination	24 V DC / 5-pole screw terminal, pluggable redundant power supply
Permissible range (min/max)	9.6 V ... 36 V DC
Input current	approx. 290 mA (at 24 V DC)
Alarm signalling contact	Change-over contact, potential-free, 24 V DC / 0.5 A 3-pole pluggable screw contact
Housing material	Metal (powder coated)
Dimensions (W x H x D)	60 x 132 x 104 mm (incl. cap, without connectors)
Weight	approx. 0.6 kg
Operating temperature	0 °C ... +70 °C
Approvals	UL 508
MTBF	560 000 h
Management	fully managed via Web interface and SNMP Functions see page 'Management functions'

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING mCon 3082-ADV
Ethernet Switch, managed
8 RJ45 ports
2 SC ports
including
Set for assembly on standard rail

20 76 110 4101



ST variant see catalogue 'Ethernet
Network Solutions Automation IT'



Ethernet Switch
HARTING mCon 4000
 Ethernet Switches, managed,
 for flat wall mounting

General Description

The Fast Ethernet Switches of the product family HARTING mCon 4000 are recommended for use in the widest range of industrial applications and support Ethernet (10 Mbit/s) and Fast Ethernet (100 Mbit/s). The product family enables the connection of up to 8 network devices over Twisted Pair cables.

Mechanical stability and temperature range meet the highest demands. The robust M12 interface shows its advantages especially in applications at risk of vibrations.

The Ethernet Switches support both SNMP and an easy Web interface for management functions.

Features

- Ethernet Switch according to IEEE 802.3
- Ethernet (10 Mbit/s) and Fast Ethernet (100 Mbit/s)
- Auto-crossing
- Auto-negotiation
- Auto-polarity
- Store and Forward Switching Mode, non blocking
- Diagnostic LEDs (Link status, Data, Power)
- Mounting onto wall, optionally onto top-hat mounting rail

Advantages

- Robust metal housing and flat housing style
- EMC, temperature range and mechanical stability meet the highest demands
- Wide range for power supply input
- Wide range for type test according to EN 50 155 and EN 50 121-3-2

Application fields

- Railway applications
- Industrial automation
- Automotive industry
- Wind power

Technical characteristics

Ethernet interface

Number of ports	8x 10/100Base-T(X)
Cable types according to IEEE 802.3	Shielded Twisted Pair (STP) or Unshielded Twisted Pair (UTP), Category 5
Data rate	10 Mbit/s or 100 Mbit/s
Maximum cable length	100 m (Twisted Pair; with Category 5 cable acc. to DIN EN 50 173-1)
Termination	M12 D-coding
Diagnostics (via LED)	<ul style="list-style-type: none"> • Status Link – ON • Data transfer (Act) – flashing • Data transfer rate (Speed) – 100 Mbit/s: Yellow / 10 Mbit/s: Green • Error – Red
Topology	Line, Ring, Star or mixed

Power supply

Input voltage	
mCon 4080-B1V	24 / 48 V DC
mCon 4080-B3V	72 / 110 V DC
Termination	M12 A-coding, male, for redundant power supply
Diagnostics (via LED)	Power supply

Design features

Housing material	Metal (powder coated)
Dimensions (W x H x D)	130 x 166 x 50 mm
Degree of protection acc. to DIN 60529	IP 40
Mounting	Wall mounting, flat
Weight	approx. 0.85 kg

Environmental conditions

Operating temperature	–40 °C ... +70 °C
Storage temperature	–40 °C ... +85 °C
Relative humidity	10 % ... 95 % (non-condensing)



Ethernet Switch
HARTING mCon 4080-B1V
 8-port Ethernet Switch for flat installation

Managed	IP 40	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
---------	-------	---	--

Number of ports, Copper / Termination 8x 10/100Base-T(X) / M12 D-coding

Input voltage / Termination 24 / 48 V DC / M12 A-coding, male, for redundant power supply

Permissible range (min/max) 12 V ... 60 V DC

Input current approx. 165 mA (at 24 V DC)

Housing material Metal (powder coated)

Dimensions (W x H x D) 130 x 166 x 50 mm

Weight approx. 0.85 kg

Operating temperature -40 °C ... +70 °C



Approvals cUL (in preparation)

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING mCon 4080-B1V

Ethernet Switch, managed,
 with 8 ports M12 D-coding
 for wall mounting

20 77 208 4001





Ethernet Switch
HARTING mCon 4080-B3V
 8-port Ethernet Switch (110 V DC) for flat installation



Managed	IP 40	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
---------	-------	---	--

Number of ports, Copper / Termination	8x 10/100Base-T(X) / M12 D-coding
Input voltage / Termination	72 / 110 V DC / M12 A-coding, male, for redundant power supply
Permissible range (min/max)	50.4 V ... 137.5 V DC
Input current	approx. 48 mA (at 110 V DC)
Housing material	Metal (powder coated)
Dimensions (W x H x D)	130 x 166 x 50 mm
Weight	approx. 0.85 kg
Operating temperature	-40 °C ... +70 °C
Approvals	cUL (in preparation)

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING mCon 4080-B3V
 Ethernet Switch, managed,
 110 V DC
 with 8 ports M12 D-coding
 for wall mounting

20 77 208 4003





Ethernet Switch HARTING mCon 9000

Ethernet Switch, managed, for installation in a 19" rack

General Description

The Ethernet Switches of the product family HARTING mCon 9000 are recommended for use in the widest range of industrial applications and support Ethernet (10 Mbit/s), Fast Ethernet (100 Mbit/s) and Gigabit Ethernet (1000 Mbit/s). The product family enables the connection of up to 10 network devices over Twisted Pair cables or F.O. cables. Optionally for some mCon 9000 Ethernet Switches additional end-devices can be connected via the DIN male connector.

The mCon 9000 Ethernet Switch family, with its integrated LEDs on each port, supports fast and easy network diagnosis. The mCon Ethernet Switch operates in Store and Forward Switching mode and supports Auto-crossing, Auto-negotiation and Auto-polarity.

Features

- Ethernet Switch acc. to IEEE 802.3
- Store and Forward Switching Mode, non-blocking
- Auto-crossing, Auto-negotiation, Auto-polarity
- Ethernet (10 Mbit/s), Fast Ethernet (100 Mbit/s) and Gigabit Ethernet (1000 Mbit/s)
- Diagnostic LEDs (Link status, Data, Power)
- Pluggable in 19" racks
- mCon 9070-BV:
Power input on the front
no backplane necessary

Advantages

- Robust metal housing
- Management function integrated
- EMC, temperature range and mechanical stability meet the highest demands
- PROFINET compatible

Application fields

- Industrial automation
- Railway applications
- Automotive industry
- Wind power
- Power distribution systems

Technical characteristics M12 D-coding

Ethernet interface

Number of ports	7x / 8x 10/100Base-T(X)
Cable types according to IEEE 802.3	Shielded Twisted Pair (STP) or Unshielded Twisted Pair (UTP), Category 5
Data rate	10 Mbit/s or 100 Mbit/s (RJ45)
Maximum cable length	100 m (Twisted Pair; with Category 5 cable acc. to DIN EN 50 173-1)
Termination, front	M12 D-coding
Diagnostics (via LED)	<ul style="list-style-type: none"> • Status Link – Green • Data transfer (Act) – Green flashing • Data transfer rate (Speed) – 100 Mbit/s: Yellow / 10 Mbit/s: OFF
Topology	Line, Ring, Star or mixed

Power supply

Input voltage	24 / 48 V DC (8 ... 60 V DC)
Diagnostics (via LED)	Power supply

Alarm signalling contact (mCon 9080-BV only)

Change-over contact, potential-free, 24 V DC / 0.5 A

Design features

Housing material	Aluminium, anodised
Degree of protection acc. to DIN 60529	IP 20 (front side IP 40, when mounted)
Mounting	19" rack, 3 U
Weight	approx. 0.6 kg

Environmental conditions

Operating temperature	–40 °C ... +70 °C
Storage temperature	–40 °C ... +85 °C
Relative humidity	10 % ... 95 % (non-condensing)



Ethernet Switch
HARTING mCon 9070-BV
 7-port Ethernet Switch for installation in a 19" rack


Managed	IP 20	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
---------	-------	---	--

Number of ports, Copper / Termination	7x 10/100Base-T(X) / M12 D-coding
Input voltage / Termination	24 / 48 V DC / M12 A-coding (on front side)
Permissible range (min/max)	8 V ... 60 V DC
Input current	approx. 130 mA (at 24 V DC)
Housing material	Aluminium, anodised
Dimensions (W x H x D)	60.6 mm (12 HP) x 128.4 mm (3 U) x 173.5 mm
Weight	approx. 0.6 kg
Operating temperature	-40 °C ... +70 °C
Approvals	cUL (in preparation)
Management	fully managed via Web interface and SNMP Functions see page 'Management functions'

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING mCon 9070-BV
 Ethernet Switch, managed
 7 ports, M12 D-coding

20 76 207 7002





Ethernet Switch
HARTING mCon 9080-BV
 8-port Ethernet Switch for installation in a 19" rack


Managed	IP 20	PROFINET compatible <input checked="" type="checkbox"/>	<input type="checkbox"/>
---------	-------	---	--------------------------

Number of ports, Copper / Termination	8x 10/100Base-T(X) / M12 D-coding
Input voltage / Termination	24 / 48 V DC / DIN frame connector, Type F
Permissible range (min/max)	8 V ... 60 V DC
Input current	approx. 130 mA (at 24 V DC)
Alarm signalling contact	Change-over contact, potential-free, 24 V DC / 0.5 A
Housing material	Aluminium, anodised
Dimensions (W x H x D)	60.6 mm (12 HP) x 128.4 mm (3 U) x 173.5 mm
Weight	approx. 0.6 kg
Operating temperature	-40 °C ... +70 °C
Approvals	cUL (in preparation)
Management	fully managed via Web interface and SNMP Functions see page 'Management functions'

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING mCon 9080-BV
 Ethernet Switch, managed
 8 ports M12 D-coding

20 76 208 7002





Industrial cable
8-wire, Cat. 5, trailing PUR

Advantages

- Suitable for generic cabling Category 5 / Class D according ISO/IEC 11801 respectively EN 50 173-1 especially for high-flexible installation (patch cords)
- Qualified for transmission up to 1 GigaBit Ethernet 1000Base-T acc. IEEE802.3ab
- Based on stranded copper wires AWG 26/19 delivers patch cord performance up to 100 MHz
- Applicable for industrial premises
- Usable as trailing cables
- Double jacket allows easy-stripping and delivers very short assembling time
- Good EMC capability based on fully screen design
- Flame retardant, halogen free and RoHS compliant

General

This high-speed data cable was designed for higher flexible installation in drag-chains and it's especially suitable for termination of HARTING RJ45 data plugs in IP 20 as well as in IP 65 / IP 67.

The four pair / eight wire TP construction allows the transmission of IT digital and analogue signals like Ethernet 10/100 Mbit/s, 1 GigaBit/s, video and voice services as well as IP-based data services.

It offers all characteristics to complete a generic cabling system according ISO/IEC 24702:2006 respectively EN 50 173-3:2007. Maximum patch cord length specified up to 20 m (part of transmission channel class D)

Transmission performance meets Cat. 5 specification up to 100 MHz for 1 GigaBit Ethernet transmission according IEEE802.3ab.

The cable is fully screened by an overall wire braid and guaranties a very protective signal transmission and high EMC performance.

PUR is used as jacket material. The cable is flame retardant, halogen free and RoHS compliant.


Identification

Part number

Industrial Cable
8-wire, Cat. 5, trailing PUR

20 m	ring
50 m	ring
100 m	ring
500 m	reel

09 45 600 0136
09 45 600 0146
09 45 600 0106
09 45 600 0156



- Wire: bare stranded copper, AWG 26/19
- Insulation: PE, Ø 1.0 mm
- Color code: gr/or, bl/rd, gn/ye, bl/br
- Inner jacket: EPDM
- Overall screen: tinned copper wire braid, braid coverage about 90 %
- Outer sheath: Polyurethane (PUR), flame retardant, halogen free, lead free
- Color of inner sheath: white
- Color of outer sheath: yellow, RAL 1021
- Overall diameter: 6.8 mm

Technical characteristics

Performance	Category 5/5e according to EN 50288-2-2:2004 / IEC 61156-6:2002
Mechanical characteristics	
Minimal bending radius	Repeated bending: 5 x diameter
Tensile strength	max. 60 N
Crush	2000 N / 100 mm
Electrical characteristics at 20 °C	
Transfer impedance 10 MHz	25 mOhm / m
Coupling attenuation up to 1000 MHz	75 dB
Conductor resistance	max. 130 Ohm / km
Insulation resistance	min. 5 GOhm*km
Mutual capacitance	50 pF / m
Signal velocity	0.68 c
Propagation delay	490 ns / 100 m
Skew (delay skew) at 100 MHz	15 ns / 100 m
Characteristic impedance at 100 MHz	100 Ohm ± 5 Ohm
Test voltage	1000 V
Operating voltage	max. 125 V
Chemical characteristics	
Flame retardant	IEC 60332-2-2
Calorific value	0.7 MJ / m
Free of hazardous substances	RoHS 2002/95/EG
Thermal characteristics	
Permissible temperature range	
Flexible operation	0 °C up to + 50 °C
Fix operation	- 40 °C up to + 85 °C
Printing	HARTING INDUSTRIAL CABLE SF/UTP ES CAT 5 PUR trailing 4x2xAWG 26/19 094560001050100 "Production lot code" "Meter marking"
Weight about	58 kg / km

Technical characteristics

Frequency MHz	Attenuation dB / 10 m		NEXT dB		PS NEXT dB		ACR dB@10 m		PS ACR dB@10 m		EL FEXT dB@10 m		PS EL FEXT dB@10 m		Return Loss dB	
	typ.	Cat 5 max*	typ.	Cat 5 min*	typ.	Cat 5 min*	typ.	Cat 5 min*	typ.	Cat 5 min*	typ.	Cat 5 min*	typ.	Cat 5 min*	typ.	Cat 5 min*
1	0.22	0.32	80	65	77	62	80	65	77	62	80	64	77	61	17	-
4	0.56	0.6	67	56	64	53	67	56	64	53	69	52	66	49	26	23
10	1.0	1.05	63	50	60	47	62	49	59	47	61	44	65	41	30	25
16	1.35	1.45	61	47	58	44	60	46	57	44	56	40	53	37	30	25
20	1.5	1.6	59	46	56	43	58	44	55	43	53	38	50	35	30	25
31.25	1.95	2.0	57	43	54	40	55	41	52	40	48	34	45	31	30	23.6
62.5	2.95	3.0	52	38	49	35	50	36	47	35	43	28	40	25	28	21.5
100	3.95	4.0	45	35	42	32	42	32	39	32	38	24	35	21	26	20.1

* according to EN 50288-2-2:2004 / IEC 61 156-6:2002



HARTING RJ Industrial® IP 20 Patch cable
Cat. 5 / Cat. 5e

Advantages

- Suitable for Gigabit Ethernet 1000 Mbit/s
- Compact and space saving plug by HARTINGs dual boot design
- Capable for multiport applications
- Very robust locking lever protection and unlocking latch
- Flame retardant and halogen-free

General

The new Cat. 5 patch cables complete HARTINGs Automation IT generic cabling system and are part of the new patch cord family. The family is marked by a unique design of the two part boot – called dual boot design. They are made for industrial environments and therefore robust and flame retardant.

The dual boot design offers a very robust handling and bending protection. Standard compliant according to ISO/IEC 24 702 resp. ISO/IEC 11 801 Cat. 5 100 MHz.

Identification

Part No.

IP 20 Patch cable
Cat. 5 / Cat. 5e

Length:	Part No.
0.2 m	09 47 474 7001
0.3 m	09 47 474 7002
0.4 m	09 47 474 7003
0.5 m	09 47 474 7004
0.6 m	09 47 474 7005
0.7 m	09 47 474 7006
0.8 m	09 47 474 7007
0.9 m	09 47 474 7008
1.0 m	09 47 474 7009
1.5 m	09 47 474 7010
2.0 m	09 47 474 7011
2.5 m	09 47 474 7012
3.0 m	09 47 474 7013
4.0 m	09 47 474 7014
5.0 m	09 47 474 7015
6.0 m	09 47 474 7016
7.0 m	09 47 474 7017
7.5 m	09 47 474 7018
8.0 m	09 47 474 7019
9.0 m	09 47 474 7020
10.0 m	09 47 474 7021
15.0 m	09 47 474 7022
20.0 m	09 47 474 7023



- RJ45 acc. to IEC 60 603-7
- Boot grey
- Locking lever protection and unlocking latch
- Cable SF/UTP AWG 26/7
- PUR chemical resistant cable jacket, yellow
- Wiring: 1:1 TIA/EIA-568-B, 8-wire
- 100 % electrical tested

Technical characteristics

Performance	Cat. 5 / Class D acc. to ISO/IEC 24 702 resp. ISO/IEC 11 801, Cat. 5e acc. to IEC 61 935-2, TIA/EIA-568-B
Mechanical characteristics	
Bending protection	
Locking lever protection	
Electrical characteristics	
Characteristic impedance	100 Ohm
Wiring	1:1 TIA/EIA-568-B
EMC	Fully shielded (aluminised foil and tinned copper braid)
Environmental characteristics	
Protection class	IP 20
Halogen-free	IEC 60754-2
Flame retardant	IEC 60332-1
Low smoke density	IEC 61034
Lead free	LSZH and RoHS compliant
Thermal characteristics	
Operating temperature	
Flexible operation	0 °C up to + 60 °C
Fix operation	- 40 °C up to + 80 °C
Tolerance cable length	
	From 0.2 m up to 5.0 m + 0.07 m
	From 6.0 m up to 20.0 m ± 1 %
Printing	RJ45 cable 8AWG 26/7, Cat. 5e PUR
Packaging	One piece in poly-bag labelled



HARTING RJ Industrial® IP 20
Patch cable Cat. 6

Advantages

- Suitable for Gigabit Ethernet 1000 Mbit/s and beyond
- Compact and space saving plug by HARTINGs dual boot design
- Capable for multiport applications
- Very robust locking lever protection and unlocking latch
- Flame retardant and halogen-free

General

The new Cat. 6 patch cables complete HARTINGs Automation IT generic cabling system and are part of the new patch cord family. The family is marked by a unique design of the two part boot – called dual boot design. They are made for industrial environments and therefore robust and flame retardant.


The dual boot design offers a very robust handling and bending protection. Standard compliant according to ISO/IEC 24 702 resp. ISO/IEC 11 801 Cat. 6 250 MHz.

Identification

Part No.

IP 20 Patch cable
Cat. 6

Length:	Part No.
0.2 m	09 47 474 7101
0.3 m	09 47 474 7102
0.4 m	09 47 474 7103
0.5 m	09 47 474 7104
0.6 m	09 47 474 7105
0.7 m	09 47 474 7106
0.8 m	09 47 474 7107
0.9 m	09 47 474 7108
1.0 m	09 47 474 7109
1.5 m	09 47 474 7110
2.0 m	09 47 474 7111
2.5 m	09 47 474 7112
3.0 m	09 47 474 7113
4.0 m	09 47 474 7114
5.0 m	09 47 474 7115
6.0 m	09 47 474 7116
7.0 m	09 47 474 7117
7.5 m	09 47 474 7118
8.0 m	09 47 474 7119
9.0 m	09 47 474 7120
10.0 m	09 47 474 7121
15.0 m	09 47 474 7122
20.0 m	09 47 474 7123



- RJ45 acc. to IEC 60 603-7
- Boot black
- Locking lever protection and unlocking latch
- Cable S/FTP AWG 26/7
- PUR chemical resistant cable jacket, yellow
- Wiring: 1:1 TIA/EIA-568-B, 8-wire
- 100 % electrical tested

Technical characteristics

Performance	Cat. 6 / Class E acc. to ISO/IEC 24 702 resp. ISO/IEC 11 801, Cat. 6 acc. to IEC 61 935-2 Note: Basically patch cords are standardised up to lengths of 10 m. For all lengths beyond RL are specified for $2 \text{ MHz} < f < 250 \text{ MHz}$.
Mechanical characteristics	
Bending protection	
Locking lever protection	
Electrical characteristics	
Characteristic impedance	100 Ohm
Wiring	1:1 TIA/EIA-568
EMC	Fully shielded (aluminised foil and tinned copper braid)
Environmental characteristics	
Protection class	IP 20
Lead free	LSZH and RoHS compliant
Flame retardant	IEC 60 332-1
Thermal characteristics	
Operating temperature	
Flexible operation	0 °C up to + 60 °C
Fix operation	- 20 °C up to + 80 °C
Tolerance cable length	From 0.2 m up to 5.0 m + 0.07 m From 6.0 m up to 20.0 m \pm 1 %
Printing	RJ45 cable 8AWG 26/7, Cat. 6 PUR
Packaging	One piece in poly-bag labelled



Hybrid cable assembly Han® 3 A hybrid RJ45

Identification	Part No.	Drawing	Dimensions in mm
<p>Hybrid cable, double ended, 4 x 2 x AWG 26/7 + 3 x 2.5 mm²</p> <p>Length: 1 m AC version DC version</p> <p>Length: 5 m AC version DC version</p> <p>Length: 10 m AC version DC version</p> <p>Length: 20 m AC version DC version</p>	<p>33 57 211 0010 001 33 57 211 0010 002</p> <p>33 57 211 0050 001 33 57 211 0050 002</p> <p>33 57 211 0100 001 33 57 211 0100 002</p> <p>33 57 211 0200 001 33 57 211 0200 002</p>	<p>double ended</p> <p>a = length</p>	
<p>Hybrid cable, single ended, 4 x 2 x AWG 26/7 + 3 x 2.5 mm²</p> <p>Length: 1 m AC version DC version</p> <p>Length: 5 m AC version DC version</p> <p>Length: 10 m AC version DC version</p> <p>Length: 20 m AC version DC version</p>	<p>33 57 111 0010 002 33 57 111 0010 001</p> <p>33 57 111 0050 002 33 57 111 0050 001</p> <p>33 57 111 0100 002 33 57 111 0100 001</p> <p>33 57 111 0200 002 33 57 111 0200 001</p>	<p>Protection level: IP 65 / IP 67</p> <p>Data part: Transmission properties in accordance with ISO/IEC 11 801:2002: Class D</p> <p>single ended</p> <p>a = length</p>	
<p>Hybrid outdoor cable</p> <p>Length: 10 m</p> <p>Length: 20 m</p> <p>Length: 500 m</p>	<p>33 57 851 0100 001</p> <p>33 57 851 0200 001</p> <p>33 57 851 5000 001</p>		<p>PVC jacket</p> <p>4 x 2 x AWG 26/7 + 3 x 2.5 mm²</p> <p>Outer diameter: 12 mm</p> <p>Min. bending radius: single: 5 x OD repeated: 10 x OD</p>

Fibre optic cable assembly HARTING PushPull LC duplex multimode






Identification	Part No.	Drawing	Dimensions in mm
<p>Fibre optic cable, double ended, multimode, 62.5 μm</p> <p>Length: a = 1 m a = 5 m a = 10 m a = 20 m a = 40 m a = 50 m a = 100 m</p>	<p>33 58 211 0010 001 33 58 211 0050 001 33 58 211 0100 001 33 58 211 0200 001 33 58 211 0400 001 33 58 211 0500 001 33 58 211 1000 001</p>	<p>double ended</p> <p>a = length</p>	
<p>Fibre optic cable, single ended, multimode, 62.5 μm</p> <p>Length: a = 1 m a = 5 m a = 10 m a = 20 m a = 40 m a = 50 m a = 100 m</p>	<p>33 58 111 0010 001 33 58 111 0050 001 33 58 111 0100 001 33 58 111 0200 001 33 58 111 0400 001 33 58 111 0500 001 33 58 111 1000 001</p>	<p>Protection level: IP 65 / IP 67</p> <p>single ended</p> <p>a = length</p>	
<p>Fibre optic breakout cable</p> <p>Length: 10 m Length: 20 m Length: 100 m</p>	<p>33 58 751 0100 001 33 58 751 0200 001 33 58 751 1000 001</p>	<p>PUR jacket 2-fibre multimode Outer diameter: Min. bending radius: Installation: Operating:</p>	<p>62.5 μm 7 mm 10.5 cm 7.0 cm</p>

Further cable lengths are available on request



Hybrid fibre optic cable assembly Han® 3 A hybrid LC duplex multimode

Identification	Part No.	Drawing	Dimensions in mm
<p>Hybrid fibre optic cable, multimode, double ended 2 x G50/125 + 3 x 2.5/3.5 mm²</p> <p>Length: 1 m AC version DC version</p> <p>Length: 5 m AC version DC version</p> <p>Length: 10 m AC version DC version</p> <p>Length: 20 m AC version DC version</p>	<p>33 57 211 0015 001 33 57 211 0015 002</p> <p>33 57 211 0055 001 33 57 211 0055 002</p> <p>33 57 211 0105 001 33 57 211 0105 002</p> <p>33 57 211 0205 001 33 57 211 0205 002</p>	<p>double ended</p>  <p>a = length</p>  <p>Protection level: IP 65 / IP 67</p>	
<p>Hybrid fibre optic cable, multimode, single ended 2 x G50/125 + 3 x 2.5/3.5 mm²</p> <p>Length: 1 m AC version DC version</p> <p>Length: 5 m AC version DC version</p> <p>Length: 10 m AC version DC version</p> <p>Length: 20 m AC version DC version</p>	<p>33 57 111 0015 001 33 57 111 0015 002</p> <p>33 57 111 0055 001 33 57 111 0055 002</p> <p>33 57 111 0105 001 33 57 111 0105 002</p> <p>33 57 111 0205 001 33 57 111 0205 002</p>	<p>single ended</p>  <p>a = length</p>	



Part No. 09 89 040 0000

Technical characteristics

Drive	electro-mechanical, servo
Press-in force	100 kN
max. PCB dimensions	600 x 1000 mm
Floor space	1200 x 1150 mm
Weight	980 kg
Power supply	208 / 380 / 400 / 415 V
Consumption	< 1 kW
Colour	on request

CPM prestige
(incl. PC, control software, barcode reader, keyboard, touch screen)

The **CPM prestige** press-in machine with a graphical user interface

The **CPM prestige** is a consequential development of the successful CPM 2001 press-in machines. The excellent design, supported by a wide range of tools presents a convenient, easy and comfortable way of processing backplanes and daughter cards. The machine is fully programmable and is supplied with a graphical user interface for control and visualisation of the complete process. The use of a microprocessor control allows the recognition and storage of different component heights, so that the pressing-in of different components is initiated simultaneously with only one button. The user-friendly touch-screen guides the user through the menu-orientated process controls.

The visualisation of the entire press-in process (the position of the connector, press-in forces etc.) allows the rapid recognition and elimination of possible error sources. The machine employs the automatic switch-off system "autosense", known worldwide for its reliability. The different connector types and the tolerances of the PCB are automatically recognised and taken into consideration at the press-in operation, thus maximising the process security. The press-in force of 100 kN allows to process more than one connector per press-in stroke and achieves a high efficiency.

The extensive operation monitor functions simplify the service and support of the machine. The embedded PC-system guaranties near 100% availability.

Quality control of press-in termination

The press-in force correlates with the diameter of the plated through hole and with the friction coefficient of the surface; therefore it can be used for a continuous monitoring of the process. The retention force, as an indirect measure of the normal force, serves to qualify the process.

Features:

- Guiding rails (carbon / spring-loaded) for the secure positioning of the PCB
- Touch-screen with integrated embedded PC (no moving parts inside)
- All dimensions allow an easy integration into production lines

Process monitoring and quality assurance:


- Touch screen interface with graphical and verbal menus for all machine functions
- Autosense: automated press-in interruption at incorrect press-in forces
- Storage and validation of all press-in parameters via quality assurance software (press-in force tolerances)
- Continuous high-precision measurement and recording of press-in forces and distances
- High flexibility through a modular tool range

Number of contacts	20-96
Contact spacing (mm)	2.54
Working current	2 A max. see current carrying capacity chart
Clearance	≥ 1.2 mm
Creepage	≥ 1.2 mm
Working voltage	according to the safety regulations of the equipment The working voltage also depends on the clearance and creepage dimensions of the PCB itself, and the associated wiring
Test voltage $U_{r.m.s.}$	1 kV
Contact resistance	≤ 15 mΩ
Insulation resistance	≥ 10 ¹² Ω
Temperature range	- 55 °C ... + 125 °C The higher temperature limit includes the local ambient and heating effects of the contacts under load - 40 °C ... + 105 °C for press-in connectors
During reflow soldering	max. + 240 °C for 15 s for SMC connectors
Electrical termination	Male and female connectors Solder pins for PCB connections Ø 1.0 ± 0.1 mm according to IEC 60 326-3 Compliant press-in terminations Diameter of PCB plated through holes see table on the right PCB thickness ≥ 1.6 mm Recommended PCB holes for press-in process in acc. to EN 60352-5
Insertion and withdrawal force	20way ≤ 20 N 30way ≤ 30 N 32way ≤ 30 N 48way ≤ 45 N 64way ≤ 60 N 96way ≤ 90 N
Materials	Mouldings Poly Cyclohexylene Terephthalate (PCT), UL 94-V0 Contacts Copper alloy
Contact surface	Contact zone Selectively plated according to performance level

Current carrying capacity

The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals. The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature.

Control and test procedures according to DIN IEC 60 512



Recommended configuration of plated through holes

In addition to the hot-air-level (HAL) other PCB surfaces are getting more important. Due to their different properties, such as mechanical strength and coefficient of friction we recommend the following configuration of PCB through holes.

<i>Tin-lead plated PCB (HAL) acc. EN 60352-5</i>	Hole-Ø	1.15±0.025 mm
	Cu	min. 25 µm
	Sn	max. 15 µm
	Plated hole-Ø	0.94-1.09 mm
<i>Chemical tin-plated PCB</i>	Hole-Ø	1.15±0.025 mm
	Cu	min. 25 µm
	Sn	min. 0.8 µm
	Plated hole-Ø	1.00-1.10 mm
<i>Au / Ni plated PCB</i>	Hole-Ø	1.15±0.025 mm
	Cu	min. 25 µm
	Ni	3-7 µm
	Au	0.05-0.12 µm
	Plated hole-Ø	1.00-1.10 mm
<i>Silver plated PCB</i>	Hole-Ø	1.15±0.025 mm
	Cu	min. 25 µm
	Ag	0.1-0.3 µm
	Plated hole-Ø	1.00-1.10 mm
<i>OSP copper plated PCB</i>	Hole-Ø	1.15±0.025 mm
	Cu	min. 25 µm
	Plated hole-Ø	1.00-1.10 mm

PCB board thickness: ≥ 1.6 mm

Number of contacts

20





Male connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.		
				3	2	1
Male connector with angled solder pins						
with fixing flange	20		Performance level 3 on request	09 24 120 6921	Performance level 1 on request	
with fixing flange, SMC	20			09 24 120 6919		
without fixing flange	20			09 24 120 6571		
without fixing flange, SMC	20			09 24 120 6579		


Dimensions

with fixing flange without fixing flange




Board drillings

Mounting side




Cross section of solder terminations



Cross area (A) of contacts row a, b: A = 0.29 - 0.33 mm²

Number of contacts

20



Female connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.	
			3	2	1
Female connector with solder pins 2.9 mm with fixing flange	20		Performance level 3 on request	09 24 220 6824	Performance level 1 on request
with fixing flange, SMC	20			09 24 220 6841	
without fixing flange, SMC	20			09 24 220 6414	
Female connector with solder pins 4.5 mm with fixing flange	20			09 24 220 6825	
Female connector with press-in pins 4.5 mm with fixing flange	20			09 24 220 6850	
without fixing flange	20			09 24 220 6870	

Number of contacts

20



Female connectors


Identification

Drawing

Dimensions in mm

Dimensions

with fixing flange without fixing flange




Board drillings


Mounting side

solder pins

press-in pins



Cross section of solder terminations



Cross area (A) of contacts row a, b: A = 0.20 - 0.23 mm²

¹⁾ for press-in connection acc. to IEC 60352-2

Number of contacts

30, 20




Male connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.		
			3	2	1	
Male connector with angled solder pins with fixing flange with fixing flange, SMC without fixing flange without fixing flange, SMC	30		Performance level 3 on request	09 25 130 6921	Performance level 1 on request	
	20			09 25 120 6921		
	30			09 25 130 6919		
	30			09 25 130 6571		
	30			09 25 130 6579		
Male connector with straight solder pins with fixing flange without fixing flange without fixing flange, SMC	30			09 25 130 6922		
	20			09 25 120 6922		
	30			09 25 130 6572		
	30			09 25 130 6590		

Number of contacts

30, 20




Male connectors

Identification


Drawing

Dimensions in mm


Dimensions



Board drillings
Mounting side




Cross section of
solder terminations



Cross area (A) of contacts row a, b, c: $A = 0.29 - 0.33 \text{ mm}^2$

Number of contacts

30, 20




Female connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.					
			3	2	1				
Female connector with solder pins 2.9 mm with fixing flange	30		Performance level 3 on request	09 25 230 6824	Performance level 1 on request				
	20			09 25 220 6824					
	30			09 25 230 6841					
	30			09 25 230 6414					
Female connector with solder pins 4.5 mm with fixing flange	30			Performance level 3 on request		09 25 230 6825	Performance level 1 on request		
	20					09 25 220 6825			
Female connector with press-in pins 4.5 mm with fixing flange	30					Performance level 3 on request		09 25 230 6850	Performance level 1 on request
	30							09 25 230 6870	

Number of contacts

30, 20



Female connectors


Identification

Drawing

Dimensions in mm

Dimensions



with fixing flange without fixing flange




Board drillings
Mounting side

solder pins

press-in pins



Cross section of solder terminations



Cross area (A) of contacts row a, b, c: A = 0.20 - 0.23 mm²

¹⁾ for press-in connection acc. to IEC 60352-2

Number of contacts

32


CTI > 400




Male connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.		
				3	2	1
Male connector with angled solder pins without clip with clip	32		Performance level 3 on request	09 22 132 6919		Performance level 1 on request
	32			09 22 332 6919		
Male connector with straight solder pins	32			09 22 132 6920		

Dimensions



Board drillings
Mounting side




Dimensions in mm

¹⁾ Recommendation for variants with clip: Drillings can be enlarged up to 3.1 mm ϕ to reduce standard mounting force

Number of contacts

32


CTI > 400




Female connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.		
				3	2	1
Female connector with solder pins 2.9 mm	32		Performance level 3 on request	09 22 232 6841	Performance level 1 on request	
Female connector with solder pins 4.5 mm	32			09 22 232 6829		


Dimensions



Board drillings
Mounting side



Cross section of solder terminations



Cross area (A) of contacts row a, b: A = 0.20 - 0.23 mm²

Number of contacts




64

CTI > 400



Male connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.	
				3	2 1
Male connector with angled solder pins	64		09 02 164 7919	09 02 164 6919	Performance level 1 on request
Male connector with straight solder pins	64		Performance level 3 on request	09 02 164 6920	



Number of contacts

64

CTI > 400



Female connectors


Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.	
				3	2 1
Female connector with solder pins 2.9 mm	64		Performance level 3 on request	09 02 264 6841	Performance level 1 on request
Female connector with solder pins 4.5 mm	64			09 02 264 6829	
Dimensions					
Panel cut out					
Board drillings Mounting side					
Cross section of solder terminations	<p>Cross area (A) of contacts row a, b: A = 0.20 - 0.23 mm²</p>				

Dimensions in mm

Number of contacts



48, 32

CTI > 400



Male connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.		
				3	2	1
Male connector with angled solder pins without clip	48		09 23 148 7919	09 23 148 6919	09 23 148 2919	
	32					
	with clip	48		09 23 348 6919	09 23 348 2919	
		32		09 23 332 6919	09 23 332 2919	
Male connector with straight solder pins	48		09 23 148 6920			
	32		09 23 132 6920			




¹⁾ Recommendation for variants with clip: Drillings can be enlarged up to 3.1 mm ϕ to reduce standard mounting force

Number of contacts

48, 32

CTI > 400



Female connectors


Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.		
				3	2	1
Female connector with solder pins 2.9 mm	48 32		Performance level 3 on request	09 23 248 6841	Performance level 1 on request	
Female connector with solder pins 4.5 mm	48 32			09 23 248 6829 09 23 232 6829		
Dimensions						
Board drillings Mounting side	<p>Cross section of solder terminations</p> <p>Cross area (A) of contacts row a, b, c: A = 0.20 - 0.23 mm²</p>					

Dimensions in mm

Number of contacts

96, 64


CTI > 400




Male connectors

Identification	Number of contacts	Contact arrangement	Part No.		Performance levels according to IEC 60 603-2.		
			2	1	2	1	
Male connector with angled solder pins without clip	96		09 03 196 6919		09 03 196 2919		
	64		09 03 696 6919 ^{c)}		09 03 164 2919		
	62 + 2▲		09 03 164 6919		09 03 164 2918		
	with clip	96		09 03 396 6919		09 03 396 2919	
		94 + 2▲		09 03 396 6918			
		64		09 03 364 6919		09 03 364 2919	
Male connector with straight solder pins	96		09 03 196 6920				


Dimensions



Board drillings
Mounting side



Cross section of solder terminations



Cross area (A) of contacts row a, b, c: A = 0.29 - 0.33 mm²

Dimensions in mm

▲ Male connectors with 2 leading contacts [(0.8 mm) pos. a1 and a32]. Lagging pins row b on request.

¹⁾ Recommendation for variants with clip: Drillings can be enlarged up to 3.1 mm ϕ to reduce standard mounting force

^{c)} Connectors with coding

Number of contacts

96, 64

CTI > 400



Female connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60603-2.						
				3	2	1				
Female connector with solder pins 2.9 mm	96 64		Performance level 3 on request	09 03 296 6841	Performance level 1 on request					
Female connector with solder pins 4.5 mm	96 64			09 03 296 6829 09 03 264 6829						
Dimensions	<table border="1" style="margin-left: auto; margin-right: auto;"> <tr><td>a</td></tr> <tr><td>2.9</td></tr> <tr><td>4.5</td></tr> </table> <p style="text-align: center;">Solder pins</p>					a	2.9	4.5		
	a									
2.9										
4.5										
Board drillings Mounting side	<p style="text-align: right;">Cross section of solder terminations</p> <p style="text-align: right;">Cross area (A) of contacts row a, b, c: A = 0.20 - 0.23 mm²</p>									

Dimensions in mm


DIN 41 612 · complementary type 2R (SMC)



Number of contacts

48, 32

CTI > 400



Male connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.		
				3	2	1
Male connector with straight solder pins 2.5 mm	48		Performance level 3 on request	09 28 148 6519	Performance level 1 on request	
	32					09 28 132 6519
Male connector with straight solder pins 4.0 mm	48			09 28 148 6520		
	32			09 28 132 6520		
Male connector with straight solder pins 13 mm	48			09 28 148 6521		

Dimensions	Solder pins					
	<table border="1"> <tr><td>a</td></tr> <tr><td>2.5</td></tr> <tr><td>4</td></tr> <tr><td>13</td></tr> </table>	a	2.5	4	13	Solder pins
a						
2.5						
4						
13						


Board drillings	Mounting side

Cross section of solder terminations
<p>Cross area (A) of contacts row a, b, c: $A = 0.35 - 0.39 \text{ mm}^2$</p>

Number of contacts

96

CTI > 400



Male connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.		
			3	2	1	

Male connector with straight solder pins 2.5 mm	96		Performance level 3 on request	09 73 196 6519	Performance level 1 on request
Male connector with straight solder pins 4.0 mm	96			09 73 196 6520	
Male connector with straight solder pins 13 mm	96			09 73 196 6521	

Dimensions	<table border="1" style="margin-left: 200px;"> <thead> <tr> <th>a</th> </tr> </thead> <tbody> <tr> <td>2.5</td> </tr> <tr> <td>4</td> </tr> <tr> <td>13</td> </tr> </tbody> </table> <p style="margin-left: 200px;">Solder pins</p>					a	2.5	4	13
a									
2.5									
4									
13									

Board drillings Mounting side					
----------------------------------	--	--	--	--	--


Cross section of solder terminations	<p>Cross area (A) of contacts row a, b, c: A = 0.35 - 0.39 mm²</p>				
--------------------------------------	---	--	--	--	--

Dimensions in mm

Number of contacts

96, 64

CTI > 400



Female connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60 603-2.	
Female connector with solder pins without clip	96		09 73 296 6804	2	
	64		09 73 264 6804		
	with clip	96		09 73 496 6804	1
		64		09 73 464 6804	
Dimensions					
Board drillings Mounting side					
Cross section of solder terminations	<p>Cross area (A) of contacts row a, b, c: A = 0.20 - 0.23 mm²</p>				

Dimensions in mm


¹⁾ Recommendation for variants with clip: Drillings can be enlarged up to 3.1 mm ϕ to reduce standard mounting force


Number of contacts	32-48
Contact spacing (mm)	5.08
Working current see current carrying capacity chart	6 A max.
Clearance	≥ 1.6 mm
Creepage	≥ 3.0 mm
Working voltage The working voltage also depends on the clearance and creepage dimensions on the PCB itself and the associated wiring	according to the safety regulations of the equipment
Test voltage $U_{r.m.s.}$	1.55 kV (contact-contact) 2.5 kV (contact-ground)
Contact resistance	≤ 15 mΩ
Insulation resistance	≥ 10 ¹² Ω
Temperature range	- 55 °C ... + 125 °C
Electrical termination Male connector	Solder pins for PCB connections Ø 1 ± 0.1 mm according to IEC 60326-3 Wrap posts 1 x 1 mm Diagonal 1.34-1.45 mm Crimp terminal 0.09-1.5 mm ²
Insertion and withdrawal force	≤ 75 N
Materials Mouldings	Special material with NFF 16-101 ≤ F2 ≤ I3 UL 94-V0
Contacts	Copper alloy
Contact surface Contact zone	Selectively plated according to performance level

Current carrying capacity


The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals. The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature.

Control and test procedures according to DIN IEC 60512






Railway classification NFF 16-101
Smoke index: F1
Flammability class: I2



Interface connectors I

Identification	Number of contacts	Contact arrangement	Part No.	Drawing	Dimensions in mm
Interface connector I with solder pins 0.6 x 0.6 mm	48		Performance level 1 09 06 048 2905		
	32		09 06 032 2905		
	32		09 06 032 2941		
Board drillings Mounting side					
Interface connector I with wrap posts 1 x 1 mm	48		Performance level 1 09 06 048 2903		
	48		09 06 048 2963		
	32		09 06 032 2903		
	32		09 06 032 2963		
Panel cut out					


Railway classification NFF 16-101
Smoke index: F1
Flammability class: I2



Interface connector I



Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
<p>Interface connector I utilising female crimp contacts</p>	<p>48</p>	<p>Performance level 1 acc. to IEC 60 603-2 09 06 048 2906</p>	<p>View from termination side</p>	
<p>Panel cut out</p> <p>Mounted in shell housing B</p>			<p>09 06 048 0503 09 06 048 0504 09 06 048 0505</p>	

Railway classification
NFF 16-101
Smoke index: F2
Flammability class: I3



Male connectors, angled

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60603-2.
Male connector without retention clip	48		09 06 148 6901 222	2 1
Male connector with retention clip	48		09 06 348 6901 222	




Dimensions in mm

Shell housing D 20 for types F, H and MH



Railway classification
NFF 16-101
Smoke index: F1
Flammability class: I2



Identification	Part No.	Drawing	Dimensions in mm
<p>Shell housing D 20/2</p> <p>Two side cable entries</p> <p>Ⓚ</p> <p>Supplied with:</p> <ul style="list-style-type: none"> Shell 1x Cover 1x Locking screw 2x Locking washer 2.3 2x Screw BZ 2.2x9.5 10x Blinding piece 2x Cable clamp 2x 	<p>20 mm</p> <p>09 06 048 0521</p>	<p>Order inserts separately</p>	
<p>Shell housing D 20/4</p> <p>Four side cable entries</p> <p>Ⓛ</p> <p>Supplied with:</p> <ul style="list-style-type: none"> Shell 1x Cover 1x Locking screw 2x Locking washer 2.3 2x Screw BZ 2.2x9.5 12x Blinding piece 3x Cable clamp 2x 	<p>20 mm</p> <p>09 06 048 0522</p>		
<p>Inserts e. g. for LED*</p> <p>for 55 mm height</p>	<p>09 06 000 9986</p>		
<p>Round cable insert* 2 x ø 11</p> <p>Ⓜ</p>	<p>09 06 000 9988</p>		

* Passend für D 20/2




IP 67 plastic hoods
IP 67 metallized plastic hoods

Identification	No. of contacts	Part No.	Drawing	Dimensions in mm
----------------	-----------------	----------	---------	------------------


Hood
Black thermoplastic

9	09 67 009 043
15	09 67 015 043
25	09 67 025 043
37	09 67 037 043
50	09 67 050 043




Metallized thermoplastic

9	09 67 009 053
15	09 67 015 053
25	09 67 025 053
37	09 67 037 053
50	09 67 050 053




Please insert digit
for screw option



Stripping dimensions

- Locking screw, thread 4-40 UNC ▶ 8
- Locking screw, thread M3 ▶ 9



Mounting instructions:

- The peeled back cable braiding must not extend over the cable clamp, in order not to damage the gasket or to impair its performance.
- Pull back cable until cable clamp snaps into shielding plate.
- Snap connector into hood.

	a	b	c	d	e	f	g	h	i
9	20	16.5	13.0	20.2	22.1	36.4	25.0	39.8	23.0
15	24	16.5	13.0	20.2	26.6	36.4	33.3	48.5	23.0
25	24	20.3	13.0	24.0	26.6	43.6	47.0	62.3	50.0
37	24	20.3	13.0	24.0	26.6	52.1	63.5	78.6	65.0
50	29	22.0	16.0	27.6	32.1	52.1	61.1	75.7	65.0


Crimp contacts



Identification	Wire gauge (mm ²)	Part No.
		turned female contacts
		Performance level 1*
Individual contacts with round bushing	AWG 22-18 0.33-0.82	09 67 000 3672
	AWG 24-20 0.25-0.52	09 67 000 8672
	AWG 28-26 0.09-0.13	09 67 000 6672

Female contacts with round bushing

	g	h	i
AWG 22-18	1.09	1.35	1.75
AWG 24-20	1.10	1.12	1.69
AWG 28-26	1.12	0.66	1.69



* Performance level 1 as per CECC 75 301-802, 500 mating cycles, 10 days 4 mixed gas test – IEC 60512


General information

HARTING offers the new Micro Card Edge connector in surface mount technology for PCBs with the thickness of 1.6 mm. The new connector is suitable for board-to-board mezzanine as well as for small „pluggable daughter card” applications. The key feature of the new connector in mezzanine applications is the achievement of flexible staple heights of parallel boards.

The HARTING Micro Card Edge connector allows data transfer rates up to 14Gbps and is suitable for high-speed applications in the telecom, medical and industrial markets. The connector is available with 40 or 100 contacts in 0.8 mm pitch.

An extremely smooth contact surface achieved by the usage of high performance stamping tools and a special surface finish ensures low insertion forces and a high contact reliability.

HARTING’s Micro Card Edge connector offers excellent features for high volume manufacturing like tape-and-reel packaging and a pad for nozzle in high volume productions.



Features

- High speed data transmission between mezzanine or daughter card boards in telecom, medical, datacom and industrial applications.
- The key feature for mezzanine application is that the distance between parallel boards is flexible by utilizing a small board between the connectors. This gives flexibility in the mechanical design of the system.
- SMT termination to boards gives good signal integrity characteristics for the card edge connector.


Technical characteristics

Rated current	1.7 A at 80 °C ambient
Rated voltage	400 V AC
Mating cycles	200
Insertion depth	4.22 mm – 5.66 mm
Number of contacts	40, 100
Card thickness	1.6 + 0.1 mm
Operating temperature	-55 °C up to +125 °C
Max processing temperature	230 °C for 60 sec. or 260 °C for 20 sec.
ROHS-compliance	yes

Materials

Contacts	CuSn8 with Ni plating
Contact zone	Au/Ni plating
Termination zone	Sn/Ni plating

Board dimensions



Micro Card Edge connector



40pin connector


Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
----------------	--------------------	----------	---------	------------------

Micro Card Edge connector


200 pieces in a "Tape and Reel" packaging

40



15 01 040 4601 040



Board layout



"Tape and Reel" packaging



Micro Card Edge connector




100pin connector

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
----------------	--------------------	----------	---------	------------------


Micro Card Edge connector
200 pieces in a "Tape and Reel" packaging

100



15 02 100 4601 040



Board layout



"Tape and Reel" packaging





Han® PushPull RJ45 Genderchanger metal
Cat. 6 / Class E

Advantages

- High degree of protection IP 65 / IP 67
- Robust metal housing
- Standard PROFINET component of the German automotive production

Application

- Allows usage of different cable types (Type B, C) e.g. in robots application
- Extension of cords according to PROFINET guideline

Identification

Part No.


Drawing

Dimensions in mm

Han® PushPull RJ45
Genderchanger metal
including housing and printed board
with 2 x RJ45 jack



09 35 221 0501



Technical characteristics

Transmission performance	Cat. 6 / Class E up to 250 MHz
Connector	Han® PushPull RJ45 (PROFINET conform)
Locking	PushPull technology acc. to IEC/PAS 61076-3-117 Variant 14
Mating face	RJ45 acc. to IEC 60603-7
Mating cycles	min. 750
Housing material	Aluminium anodized
Dimensions	83.2 x 62 x 25.2 mm (unmated)
Degree of protection acc. to DIN 60529	IP 65 / IP 67 (mated)
Mounting	Wall mountable with 4 screws (type M5)
Temperature range	-20 °C ... +70 °C
Maximum permissible humidity	30 % ... 95 % (no condensation)



Han® PushPull L Power 4/0 Genderchanger metal

Advantages

- High degree of protection IP 65 / IP 67
- Robust metal housing
- Standard PROFINET component of the German automotive production

Application

- Allows usage of different cable types (Type B,C) e.g. in robots application
- Extension of cords according to PROFINET guideline

Identification


Part No.

Drawing

Dimensions in mm


Han® PushPull L Power 4/0 Genderchanger metal including housing and printed board with 2 x male insert with solder termination

09 35 431 0501



Technical characteristics

Connector	Han® PushPull L Power 4/0
Locking	PushPull technology acc. to IEC/PAS 61 076-3-117
Electrical transmission	16 A / 24 V
Number of contacts	5
Mating cycles	min. 500
Housing material	Aluminium anodized
Dimensions	83.4 x 62 x 40.7 mm (unmated)
Degree of protection acc. to DIN 60529	IP 65 / IP 67 (mated)
Mounting	Wall mountable with 4 screws (type M5)
Temperature range	-20 °C ... +50 °C
Maximum permissible humidity	30 % ... 95 % (no condensation)



Connector, 5-poles, 24 V, 16 A

Features

- HARTING PushPull technology
- Touch-proof
- Cable side: female insert
- spring force connection
- Device side: male insert
- spring force connection
- AIDA-conform
(German Domestic Automobile Manufactures)

Technical characteristics


Locking	PushPull technology acc. to IEC/PAS 61076-3-117
Degree of protection	IP 65 / IP 67
Number of contacts	4 + PE
Electrical data acc. to DIN EN 61984	16 A, 24 V, 4 kV 3
Termination	Spring force connection
Termination cross section	0.75 ... 2.5 mm ²
Mating cycles	min. 500
Temperature range	-40 °C ... +70 °C
Cable diameter	9 – 13 mm
Housing material	Zinc die-cast, nickel plated

Identification Part No. Drawing Dimensions in mm

Connector set, metal
incl. housing
and female insert
with spring force connection




09 35 431 0401



Panel feed-through,
metal
incl. housing and male insert
with spring force connection


09 35 431 0311




Protection cover IP 65 / IP 67
for device side

09 35 004 5401

Panel cut out





Connector, 5-poles, 24 V, 16 A

Features

- HARTING PushPull technology
- Touch-proof
- Cable side: female insert
- spring force connection
- Device side: male insert
- spring force connection
- AIDA-conform
(German Domestic Automobile
Manufactures)

Technical characteristics

Locking	PushPull technology acc. to IEC/PAS 61076-3-117
Degree of protection	IP 65 / IP 67
Number of contacts	4 + PE
Electrical data acc. to DIN EN 61984	16 A, 24 V, 4 kV 3
Termination	Spring force connection
Termination cross section	0.75 ... 2.5 mm ²
Mating cycles	min. 500
Temperature range	-40 °C ... +70 °C
Cable diameter	9 – 13 mm
Housing material	Plastic, black
Flammability acc. to	UL 94 V0

Identification

Part No.

Drawing


Dimensions in mm

Connector set, plastic

incl. housing
and female insert
with spring force connection




09 35 431 0421



Panel feed-through, plastic

incl. housing and male insert
with spring force connection


09 35 431 0331




Protection cover IP 65 / IP 67 for device side

09 35 004 5401

Panel cut out





Han® PushPull,
type acc. to IEC/PAS 61 076-3-117 variant 14
Accessories

Identification	Part No.	Drawing	Dimensions in mm
Han® PushPull protection cover IP 40 for device side	09 35 002 5401		
Han® PushPull protection cover IP 40 for cable side	09 35 002 5412		
Han® PushPull protection cover IP 65 / IP 67 for device side	09 35 002 5402		
Han® PushPull protection cover IP 65 / IP 67 for cable side	09 35 002 5411		
Han® PushPull L for Power 4/0 protection cover IP 65 / IP 67 for device side	09 35 004 5401		
Han® PushPull coding pins for Power 4/0 for device and cable side	09 35 000 6190		




HARTING PushPull Technology acc. to IEC 61 076-3-106 variant 4
RJ45 panel feed-throughs and accessories

Advantages

- Small, space-saving PushPull interfaces in IP 65 / IP 67
- Easy handling of RJ45 patch cords in switch cabinets or sets
- Mounting to casings
- Category of transmission Cat. 5

Technical characteristics


Locking	PushPull Technology acc. to IEC 61 076-3-106 variant 4
Transmission rate	10/100/1000 Mbit/s
Shielding	fully shielded, 360° shielding contact
Mating cycles	min. 750
Degree of protection	IP 65 / IP 67
Temperature range	– 40 °C up to + 70 °C
Housing material	Zinc die cast
	UL approval

Identification	Part No.	Drawing	Dimensions in mm
----------------	----------	---------	------------------

Panel feed-through set


incl. housing bulkhead mounting EasyInstall with integrated seal, 2 x RJ45-jacks mounting on PCB board drillings for M3

09 45 295 1130




Housing bulkhead mounting EasyInstall with fixing clip

09 45 595 0031



Protection cover for housing bulkhead mounting with cord IP 65 / IP 67 fixing ring for M2.5
Version with active locking


for screw M2.5
09 45 845 0004



for screw M3
09 45 845 0006


Version with passive locking


09 45 845 0009



IP 40 transport protection for housing bulkhead mounting, rubber

09 45 845 0003






HARTING PushPull Technology acc. to IEC 61 076-3-106 variant 4
RJ45 connector

Advantages

- Ethernet connector based on RJ45
- Fully shielded, 360° shielding contact
- Field-assembly connector with IDC contacts (Cat. 5 versions) or piercing contacts (Cat.6 versions)

Technical characteristics

Locking	PushPull Technology acc. to IEC 61 076-3-106 variant 4
Degree of protection	IP 65 / IP 67
Mating face	RJ45 acc. to IEC 60 603-7
Cable diameter	4.9 ... 8.6 mm
Termination cross section	
Cat. 5	AWG 24/7 ... AWG 22/7 (stranded) AWG 23/1 ... AWG 22/1 (solid)
Cat. 6	AWG 24/7 ... AWG 27/7 (stranded)
Mating cycles	min. 750
Temperature range	-40 °C up to +70 °C
Housing material	Zinc die cast
	UL approval

Identification

Part No.



Drawing

Dimensions in mm

Connector, 4-poles
Cat. 5

incl. housing with RJ45 connector,
shielding and cable gland




09 45 195 1100



Connector, 8-poles
Cat. 6

incl. housing with RJ45 connector,
shielding and cable gland


09 45 195 1500




Wire manager white

Wire manager blue

09 45 195 1510



Reference note: for cat. 6 patch cords it is recommended to use 1 connector with a white wire manager and one with a blue cable manager, in order to optimise the crosstalk between different signal pairs.



HARTING PushPull Technology acc. to IEC 61 076-3-106 variant 4
LC duplex panel feed-through and connector

Advantages

- Optical PushPull connector based on LC with small form factor (requires 50 % compared to SC and ST)
- EasyInstall panel feed-through for simple device integration
- Optical module with inserts acc. to IEC 61 754-20
- One-piece LC body assures high mechanical stability
- A & B part identification for duplex according TIA 568 standard

Technical characteristics

Locking	PushPull Technology acc. to IEC 61 076-3-106 variant 4
Degree of protection	IP 65 / IP 67
Mating face	LC acc. to IEC 61 754-20
Cable diameter	4.9 ... 8.6 mm
Mating cycles	min. 200
Temperature range	-40 °C up to +70 °C
Housing material	Zinc die cast

Identification	Part No.	Drawing	Dimensions in mm
----------------	----------	---------	------------------

HARTING PushPull LC duplex


Cable side
Multimode GOF
Singlemode GOF


09 57 409 0500 000
09 57 409 0501 000

Device side EasyInstall
Multimode GOF
Singlemode GOF

09 57 468 0500 000
09 57 468 0501 000

Panel cut out





HARTING PushPull Power 4/0, type acc. to IEC 61 076-3-106 variant 4
panel feed-throughs 4-poles 48 V / 12 A

Advantages

- Power connectors for devices
- EasyInstall and Compact panel feed-through and females for simple device integration
- Compact, space-saving design
- Touch-proof according to IEC DIN EN 60529
- Polarisation with nose
- Device side: female with cable cage, crimp or solder termination
- 4 different coding variants without loss of contact

Technical characteristics

Locking	PushPull Technology acc. to IEC 61 076-3-106 variant 4
Degree of protection	IP 65 / IP 67
Number of contacts	4
Electrical data acc. to EN 61984	12 A, 48 V, 1.5 kV 3
Termination	Crimp
Termination cross section	0.75 - 2.5 mm ² (AWG 20 - 12) stranded
Termination	Solder pins
Termination diameter	1.6 mm
Termination	Cable cage
Termination cross section	0.75 - 2.5 mm ² (AWG 20 - 12) stranded
Mating cycles	min. 750
Temperature range	-40 °C up to +70 °C
Housing material	Zinc die cast

Identification	Part No.	Drawing	Dimensions in mm
----------------	----------	---------	------------------

Panel feed-through set

Housing bulkhead mounting EasyInstall
with 4 turned female contacts and insulation

with crimp termination for 1.5 mm²

with solder termination, 90° angled

with cage clamp terminal on PCB

09 46 295 4430

09 46 295 4030

09 46 295 4031

Power-female with solder termination
4-poles, 48V/12A, 90° angled

09 46 500 4400

Accessories – crimp contacts female

0.75 mm² (AWG 20 - 18)


1.5 mm² (AWG 16 - 14)

2.5 mm² (AWG 12)

09 46 500 0404

09 46 500 0402

09 46 500 0406





HARTING PushPull Power 4/0, type acc. to IEC 61076-3-106 variant 4
connector 4-poles 48 V / 12 A

Advantages

- Power connectors for devices
- EasyInstall panel feed-through for simple device integration
- Compact, space-saving design
- Touch-proof according to IEC DIN EN 60529
- Polarisation with nose
- Cable side: Male with crimp termination
- 4 different coding variants without loss of contact

Technical characteristics

Locking	PushPull Technology acc. to IEC 61076-3-106 variant 4
Degree of protection	IP 65 / IP 67
Number of contacts	4
Electrical data acc. to EN 61984	12 A, 48 V, 1.5 kV 3
Cable diameter	4.9 ... 8.6 mm
Termination	Crimp
Termination cross section	0.75 - 2.5 mm ² (AWG 20 - 12) stranded
Mating cycles	min. 750
Temperature range	-40 °C up to +70 °C
Housing material	Zinc die cast

Identification

Part No.

Drawing

Dimensions in mm

Connector set

incl. 4 turned crimp contacts (male), insulation, housing, cable gland

09 46 195 4400

Accessories – crimp contacts male

0.75 mm² (AWG 20 - 18)

09 46 500 0403

1.5 mm² (AWG 16 - 14)

09 46 500 0401

2.5 mm² (AWG 12)

09 46 500 0405

Accessories – coding pin set

To avoid accidental incorrect mating a coding system is required. This coding pins are inserted without loss of contact.

09 46 840 0000

Accessories – protection cover IP 65 / IP 67

for connector with cord

09 45 845 0010


for device side with cord


09 45 845 0009

Accessories – transport protection IP40

for housing bulkhead mounting, rubber

09 45 845 0003





Features

- Short and robust construction
- Compact design
- Easy and quick assembly
- Vibration resistant
- Use of standard D-Sub contacts is possible

Technical characteristics

Number of contacts	5
Rated current	4 A
Rated voltage	32 V
Termination	Crimp termination
Wire gauge	AWG 22 - 20 0.34 - 0.5 mm ²
Diameter of individual strands	1.5 - 2.3 mm
Wire diameter	5.0 - 8.5 mm
Flammability acc. to UL 94	V 0

Accessories

	Part-Number	Depiction
Crimping tool	09 99 000 0501	
Locator	61 03 600 0023	

Contacts

	Part-Number	Drawing	Dimensions in mm																					
Crimp contacts Turned male contacts AWG 22 - 20 / 0.33 - 0.52 AWG 26 - 22 / 0.13 - 0.35	61 03 000 0073		<table border="1"> <thead> <tr> <th></th> <th>a</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> </tr> </thead> <tbody> <tr> <td>AWG 22 - 20</td> <td>8.10</td> <td>4.0</td> <td>14.8</td> <td>1.12</td> <td>1.66</td> <td>14.4</td> </tr> <tr> <td>AWG 26 - 22</td> <td>8.10</td> <td>4.0</td> <td>14.8</td> <td>0.90</td> <td>1.66</td> <td>14.4</td> </tr> </tbody> </table>		a	b	c	d	e	f	AWG 22 - 20	8.10	4.0	14.8	1.12	1.66	14.4	AWG 26 - 22	8.10	4.0	14.8	0.90	1.66	14.4
				a	b	c	d	e	f															
AWG 22 - 20	8.10	4.0	14.8	1.12	1.66	14.4																		
AWG 26 - 22	8.10	4.0	14.8	0.90	1.66	14.4																		
61 03 000 0094																								
Turned female contacts AWG 22 - 20 / 0.33 - 0.52 AWG 26 - 22 / 0.13 - 0.35	61 03 000 0074																							
	61 03 000 0096																							



M12 Connector for Field Assembly


Identification	Part-Number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Han® M12 Crimp

Male, A-coding




21 03 812 1505



Female, A-coding





21 03 812 2505



Order crimp contacts separately

Please send me further information:

CD-ROM HARKIS® basic 
DVD HARKIS® basic 



Interface Connectors



Telecom Outdoor Solutions




Industrial Connectors Han®



Connectors DIN 41612



Ethernet Network Solutions Automation IT



Coaxial and Metric Connectors



Application brochure



TCA Connectors



Device Connectivity



Backplanes and Integrated Systems

Sender:

Company: _____

Street: _____

Department: _____

Postcode/Town: _____

Name: _____

Country: _____

Prenome: _____

Phone: _____

Function: _____

Fax: _____

Please send it by post or fax to your local HARTING representatives (see page addresses) or visit us under www.HARTING.com.

E-Mail: _____

Production plants – worldwide



Espelkamp / Germany – Plant 1



Espelkamp / Germany – Plant 2



Espelkamp / Germany – Plant 3



Espelkamp / Germany – Plant 4



Espelkamp / Germany – Plant 5

Sales partner – worldwide



Argentina

Condelectric S.A.
Hipólito Yrigoyen 2591
(B1640HFY) Martínez, Buenos Aires
Phone + Fax +54 11 4836-1053
E-Mail: info@condelectric.com.ar

Canada

HARTING Electric
Chartwell Electronics Inc.
140 Duffield Drive
Markham, Ontario L6G 1B5
Phone 905-513-7100
Toll Free 877-513-7769
Fax 905-513-7101
Internet: www.chartwell.ca

Denmark

Wexøe A/S
Lejrvej 31, DK-3500 Vaerloese
Phone +4545465800
Fax +4545465801
E-Mail: wexoe@wexoe.dk
Internet: www.wexoe.dk



Zhuhai / China



Northampton / Great Britain



Sibiu / Romania

Estonia

HARTING Electric
SKS Tehnika OÜ, Liimi 1
EE-10621 Tallinn
Tel. +372 699 0171, Fax +372 699 0170
E-Mail: tehnika@sk.fi
Internet: www.sk.fi

Finland

HARTING Electric
SKS Automaatio Oy
Martinkyläntie 50, FI-01720 Vantaa
Phone +358 (0) 20 764 61
Fax +358 (0) 20 764 6820
E-Mail: automaatio@sk.fi
Internet: www.sk.fi

Finland

HARTING Electronics
INTOTEL OY
Kutojantie 4, 02630 Espoo, Finland
P.O. Box 125, 02631 Espoo, Finland
Phone +358-9-521 300
Fax +358-9-7553581
E-Mail: into@intotel.fi
Internet: www.intotel.fi

Island

HARTING Electric
Smith & Norland, Nóatún 4
IS – 105 Reykjavík
Phone +354 520 3000
Fax +354 520 3011
E-Mail: olaf@sminor.is
Internet: www.sminor.is

Israel

HARTING Electric
MIGVAN
Technologies & Engineering Ltd.
13 Hashiloh St., P.O.Box 7022
IL – Petach Tikva 49170
Phone +972 3 9240784
Fax +972 3 9240787
E-Mail: info@mte.co.il
Internet: www.mte.co.il



Biel / Switzerland



Elgin / USA



Israel – HARTING Electronics
COMTEL
Israel Electronics Solutions Ltd.
Bet Hapamon, 20 Hataas st.
P.O.Box 66
Kefar-Saba 44425
Phone +972-9-7677240
Fax +972-9-7677243
E-Mail: sales@comtel.co.il
Internet: www.comtel.co.il

South Africa – HARTING Electric
HellermannTyton Pty Ltd.
Private Bag X158 Rivonia 2128
34 Milky Way Avenue
Linbro Business Park 2065
Johannesburg, South Africa
Phone +27(0)11879-6600
Fax +27(0)11879-6606
E-Mail: sales.jhb@hellermann.co.za

South Africa – HARTING Electronics
Cabcon Technologies (PTY)Ltd
P.O. Box 4603, Dalpark, 1543 Gauteng
Phone +27 1184533258
Fax +27 118454077
E-Mail: cabcon@mweb.co.za

Turkey
Gökhan Elektrik San. Tic. Ltd. Sti.
Perpa Elektrikçiler Is Merkezi A Blok
Kat:7-8-9 No.694
TR – 80270 Okmeydani/Istanbul
Phone +90(212) 2213236 (pbx)
Fax +90(212) 2213240
E-Mail:
gokhan@gokhanelektrik.com.tr
Internet: www.gokhanelektrik.com.tr

Distrelec AG
Grabenstrasse 6
CH-8606 Nänikon
Phone +41 1 944 99 11
Fax +41 1 944 99 88
E-Mail: info@distrelec.com
Internet: www.distrelec.com

Subsidiary companies – worldwide



Australia
HARTING Pty Ltd
Suite 11 / 2 Enterprise Drive
Bundoora 3083, AUS-Victoria
Phone +61 9466 7088, Fax +61 9466 7088
E-Mail: au@HARTING.com
www.HARTING.com

Austria
HARTING Ges. m. b. H.
Deutschstraße 19, A-1230 Wien
Phone +431 6162121
Fax +431 6162121-19
E-Mail: at@HARTING.com
Internet: www.HARTING.at

Belgium
HARTING N.V./S.A.
Z.3 Doornveld 23, B-1731 Zellik
Phone +32 2 466 0190
Fax +32 2 466 7855
E-Mail: be@HARTING.com
Internet: www.HARTING.be

Brazil
HARTING Ltda.
Av. Dr. Lino de Moraes
Pq. Jabaquara, 255
CEP 04360-001 – São Paulo – SP – Brazil
Phone +55 11 5035 0073
Fax +55 11 5034 4743
E-Mail: br@HARTING.com
Internet: www.HARTING.com.br

China
Zhuhai HARTING Limited, Shanghai branch
Room 5403, HK New World Tower
300 Huai Hai Road (M.)
Shanghai 200021, China
Phone +86 756 362 7800
Fax +86 756 362 7900
E-Mail: cn@HARTING.com
Internet: www.HARTING.com.cn

Czech Republic
HARTING spol. s.r.o.
Mlýnská 2, CZ-160 00 Praha 6
Phone +420 220 380 460
Fax +420 220 380 461
E-Mail: cz@HARTING.com
Internet: www.HARTING.cz

Finland
HARTING Oy
Teknobulevardi 3-5, PL 35
FI-01530 Vantaa
Phone +358 9 350 87 300
Fax +358 9 350 87 320
E-Mail: fi@HARTING.com
Internet: www.HARTING.fi

France
HARTING France
181 avenue des Nations, Paris Nord 2
BP 66058 Tremblay en France
F-95972 Roissy Charles de Gaulle Cédex
Phone +33 1 4938 3400
Fax +33 1 4863 2306
E-Mail: fr@HARTING.com
Internet: www.HARTING.fr

Germany
HARTING Deutschland GmbH & Co. KG
Postfach 2451, D-32381 Minden
Simeonscarré 1, D-32427 Minden
Phone +49 571 8896 0
Fax +49 571 8896 282
E-Mail: de@HARTING.com
Internet: www.HARTING.com

Office Germany
HARTING Deutschland GmbH & Co. KG
Blankenauer Straße 99
D-09113 Chemnitz
Phone +49 0371 429211
Fax +49 0371 429222
E-Mail: de.sales@HARTING.com
Internet: www.HARTING.com

Great Britain
HARTING Ltd., Caswell Road
Brackmills Industrial Estate
GB-Northampton, NN4 7PW
Phone +44 1604 827 500
Fax +44 1604 706 777
E-Mail: gb@HARTING.com
Internet: www.HARTING.co.uk

Hong Kong
HARTING (HK) Limited
Regional Office Asia Pacific
3512 Metroplaza Tower 1
223 Hing Fong Road
Kwai Fong, N. T., Hong Kong
Phone +852 2423 7338
Fax +852 2480 4378
E-Mail: ap@HARTING.com
Internet: www.HARTING.com.hk

Hungary
HARTING Magyarország Kft.
Fehérvári út 89-95, H-1119 Budapest
Phone +36 1 205 34 64
Fax +36 1 205 34 65
E-Mail: hu@HARTING.com
Internet: www.HARTING.hu

India
HARTING India Private Limited
No. D, 4th Floor, 'Doshi Towers'
No. 156 Poonamallee High Road,
Kilpauk, Chennai 600 010
Tamil Nadu, Chennai
Phone +91 44 435604 15
Fax +91 44 435604 17
E-Mail: in@HARTING.com
Internet: www.HARTING.com

Italy

HARTING SpA
Via Dell' Industria 7
I-20090 Vimodrone (Milano)
Phone +39 02 250801
Fax +39 02 2650 597
E-Mail: it@HARTING.com
Internet: www.HARTING.it

Japan

HARTING K. K.
Yusen Shin-Yokohama 1 Chome Bldg., 2F
1-7-9, Shin-Yokohama
Kohoku-ku, Yokohama
Yokohama 222-0033 Japan
Phone +81 45 476 3456
Fax +81 45 476 3466
E-Mail: jp@HARTING.com
Internet: www.HARTING.co.jp

Korea

HARTING Korea Limited
#308 Yatap Leaders Building
342-1, Yatap-dong, Bundang-gu,
Sungnam-Si Gyeonggi-Do
463-828 Republic of Korea
Phone +82 31 781 4613
Fax +82 31 781 4616
E-Mail: kr@HARTING.com
Internet: www.HARTING.com.cn/kr

The Netherlands

HARTING B.V.
Larenweg 44, NL-5234 KA 's-Hertogenbosch
Postbus 3526, NL-5203 DM 's-Hertogenbosch
Phone +31 736 410 404
Fax +31 736 440 699
E-Mail: nl@HARTING.com
Internet: www.HARTINGbv.nl

Norway

HARTING A/S
Østensjøveien 36, N-0667 Oslo
Phone +47 22 700 555
Fax +47 22 700 570
E-Mail: no@HARTING.com
Internet: www.HARTING.no

Poland

HARTING Polska Sp. z o. o.
ul. Kamińskiego 201-219
PL-51-126 Wrocław
Phone +48 71 352 81 71
Fax +48 71 320 74 44
E-Mail: pl@HARTING.com
Internet: www.HARTING.pl

Portugal

HARTING Iberia, S. A.
Avda. Josep Tarradellas, 20-30, 4ª 6ª
E-08029 Barcelona
Phone +34 93 363 84 75
Fax +34 93 419 95 85
E-Mail: es@HARTING.com
Internet: www.HARTING.es/pt

Russia

HARTING ZAO
Maily Sampsoniyevsky prospect 2A
194044 Saint Petersburg, Russia
Phone +7 095 995 9993
Fax +7 095 995 9994
E-Mail: ru@HARTING.com
Internet: www.HARTING.ru

Singapore

HARTING Singapore Pte Ltd.
25 International Business Park
#02-06 German Centre
Singapore 609916
Phone +65 6225 5285, Fax +65 6225 9947
E-Mail: sg@HARTING.com
Internet: www.HARTING.com

Spain

HARTING Iberia S.A.
Josep Tarradellas 20-30 4ª 6ª
E-08029 Barcelona
Phone +34 93 363 84 75
Fax +34 93 419 95 85
E-Mail: es@HARTING.com
Internet: www.HARTING.es

Sweden

HARTING AB
Gustavslundsvägen 141 B 4tr
S-167 51 Bromma
Phone +46 8 445 7171
Fax +46 8 445 7170
E-Mail: se@HARTING.com
Internet: www.HARTING.se

Switzerland

HARTING AG
Industriestrasse 26, CH-8604 Volketswil
Phone +41 44 908 20 60
Fax +41 44 908 20 69
E-Mail: ch@HARTING.com
Internet: www.HARTING.ch

Taiwan

HARTING R.O.C. Limited
Room 1, 5/F, 495 GuangFu South Road
RC-110 Taipei, Taiwan
Phone +886 227 586 177
Fax +886 227 587 177
E-Mail: tw@HARTING.com
Internet: www.HARTING.com.tw

USA

HARTING Inc. of North America
1370 Bowes Road,
USA-Elgin, Illinois 60123
Phone +1 (877) 741-1500 (toll free)
Fax +1 (866) 278-0307 (Inside Sales)
Fax +1 (847) 717-9430 (Sales and Marketing)
E-Mail: us@HARTING.com
Internet: www.HARTING-USA.com

Eastern-Europe

HARTING Eastern Europe GmbH
Bamberger Straße 7, D-01187 Dresden
Phone +49 351 4361 760
Fax +49 351 436 1770
E-Mail: Eastern.Europe@HARTING.com
Internet: www.HARTING.com

Distributors – worldwide

Farnell: www.farnell.com;
in US: Newark: www.newark.com

RS Components: www.rs-components.com;
in US: Allied Electronics: www.alliedelec.com

FUTURE Electronics – HARTING Electronics
www.futureelectronics.com

Other countries

HARTING Electric GmbH & Co. KG
Postfach 1473, D-32328 Espelkamp
Phone +495772/47-97100
Fax + 495772/47-495
E-Mail: electric@HARTING.com

HARTING Electronics GmbH & Co. KG
Postfach 1433, D-32328 Espelkamp
Phone +495772/47-97200
Fax +495772/47-777
E-Mail: electronics@HARTING.com

General information

It is the customer's responsibility to check whether the components illustrated in this catalogue comply with different regulations from those stated in special fields of application which we are unable to foresee.

We reserve the right to modify designs in order to improve quality, keep pace with technological advancement or meet particular requirements in production.

No part of this catalogue may be reproduced in any form (print, photocopy, microfilm or any other process) or processed, duplicated or distributed by means of electronic systems without the written permission of HARTING Electronics GmbH & Co. KG or HARTING Electric GmbH & Co. KG, Espelkamp. We are bound by the German version only.



Pushing Performance

www.HARTING.com