



Vishay


e3

RoHS

COMPLIANT

HALOGEN

SMD PTC - Nickel Thin Film Linear Thermistors



FEATURES

- Alumina substrate base with nickel based PTC thin film element
- 0603, 0805, and 1206 sizes available
- Available in tape and reel packaging
- Standard R_{25} tolerances: ± 0.5 %, ± 1 %, ± 5 %
- Operation range -55 °C to +150 °C
- · High stability over the entire temperature range
- cUL recognized component: File E148885
- Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>

QUICK REFERENCE DATA						
PARAMETER VALUE						
DESCRIPTION	TFPT0603	TFPT0805	TFPT1206	UNIT		
Resistance value at 25 °C ⁽²⁾	100 to 1K	100 to 5K	100 to 10K	Ω		
Tolerance on R_{25} -value ⁽²⁾		± 0.5; ± 1; ± 5		%		
TCR at 25 °C		4110		ppm/K		
Tolerance on TCR at 25 °C ⁽¹⁾	± 400					
Operating temperature range:						
at rated power		°C				
at zero dissipation (4)	-55 to +150					
Dissipation factor δ (for information only)	1.8 2.3 4					
Maximum rated power at 70 °C (P ₇₀)	75 100 125					
Maximum working voltage RCWV (3)	30 40 50					
Climatic category (LCT/UCT/days)	55/150/56					
Weight	2 5.5 10					

Notes

⁽¹⁾ Contact Vishay if closer TCR lot tolerance is desired


⁽²⁾ Other R_{25} -values and tolerances are available upon request

⁽³⁾ Rated continuous working voltage is maximum working voltage or $\sqrt{P_{70} \times R}$ whichever is less

⁽⁴⁾ Zero power or zero dissipation is considered as measuring power max. 1 % of rated power P_{70}

STANDARD RESISTANCE VALUES at 25 °C in Ω								
100	180	330	560	1.0K	1.8K	3.3K	5.0K	8.2K
120	220	390	680	1.2K	2.2K	3.9K	5.6K	10.0K
150	270	470	820	1.5K	2.7K	4.7K	6.8K	

Note




Revision: 22-Mar-11

Document Number: 33017


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000 DIMENSIONS in millimeters


CONSTRUCTION



www.vishay.com

PART NUMBER	Α	В	С	D	Е
TFPT 0603	1.60	0.85	0.45	0.30	0.30
	± 0.10	± 0.10	± 0.10	± 0.20	± 0.20
TFPT 0805	2.00	1.25	0.45	0.40	0.40
	± 0.15	± 0.15	± 0.10	± 0.20	± 0.20
TFPT 1206	3.20	1.60	0.55	0.50	0.50
	± 0.15	± 0.15	± 0.10	± 0.25	± 0.25





Note

Zero power is considered as measuring power max. 1 % of rated power P₇₀

PERFORMANCE ⁽¹⁾						
TEST	MAXIMUM Δ <i>R</i> / <i>R</i> ₂₅ ⁽²⁾					
High temperature exposure (100 h at 125 °C)	0.25 %					
Effects of bonding (10 s solder dip at 260 °C)	0.25 %					
Thermal shock (30 min at -55 °C, 30 min at 125 °C, 5 cycles)	0.25 %					
Low temperature operation (maximum rated power for 2 h at -55 °C)	0.25 %					
Short time overload (2.5 x RCWV for 5 s)	0.25 %					
Load life (1000 h 70 °C, maximum rated power 1.5 h "ON", 0.5 h "OFF"	0.25 %					
Solderability (95 % coverage P/F)	Р					
Leaching (physical damage P/F)	Р					

Notes

⁽¹⁾ Environmental performance specifications use test procedures as outlined in MIL-R-23648D and MIL-STD-202

(2) TFPTs are ESD sensitive



Vishay

AVERA	AVERAGE RATIO R/R ₂₅ TFPT ALL SIZES AND VALUES										
TEMP.	R/R ₂₅	TEMP.	R/R ₂₅	TEMP.	R/R ₂₅	TEMP.	R/R ₂₅	TEMP.	R/R ₂₅	TEMP.	R/R ₂₅
		-20	0.825	20	0.980	60	1.150	100	1.337	140	1.541
		-19	0.828	21	0.984	61	1.155	101	1.342	141	1.547
		-18	0.832	22	0.988	62	1.159	102	1.347	142	1.552
		-17	0.836	23	0.992	63	1.164	103	1.352	143	1.557
		-16	0.839	24	0.996	64	1.168	104	1.357	144	1.563
-55	0.702	-15	0.843	25	1.000	65	1.173	105	1.362	145	1.568
-54	0.705	-14	0.847	26	1.004	66	1.177	106	1.367	146	1.574
-53	0.708	-13	0.851	27	1.008	67	1.182	107	1.372	147	1.579
-52	0.712	-12	0.854	28	1.012	68	1.186	108	1.377	148	1.584
-51	0.715	-11	0.858	29	1.017	69	1.191	109	1.382	149	1.590
-50	0.719	-10	0.862	30	1.021	70	1.196	110	1.387	150	1.595
-49	0.722	-9	0.866	31	1.025	71	1.200	111	1.392		
-48	0.725	-8	0.869	32	1.029	72	1.205	112	1.397		
-47	0.729	-7	0.873	33	1.033	73	1.209	113	1.402		
-46	0.732	-6	0.877	34	1.037	74	1.214	114	1.407		
-45	0.736	-5	0.881	35	1.042	75	1.219	115	1.412		
-44	0.739	-4	0.885	36	1.046	76	1.223	116	1.417		
-43	0.743	-3	0.889	37	1.050	77	1.228	117	1.422		
-42	0.746	-2	0.892	38	1.054	78	1.232	118	1.427		
-41	0.749	-1	0.896	39	1.059	79	1.237	119	1.432		
-40	0.753	0	0.900	40	1.063	80	1.242	120	1.437		
-39	0.756	1	0.904	41	1.067	81	1.246	121	1.442		
-38	0.760	2	0.908	42	1.071	82	1.251	122	1.448		
-37	0.763	3	0.912	43	1.076	83	1.256	123	1.453		
-36	0.767	4	0.916	44	1.080	84	1.261	124	1.458		
-35	0.771	5	0.920	45	1.084	85	1.265	125	1.463		
-34	0.774	6	0.924	46	1.089	86	1.270	126	1.468		
-33	0.778	7	0.927	47	1.093	87	1.275	127	1.473		
-32	0.781	8	0.931	48	1.097	88	1.280	128	1.478		
-31	0.785	9	0.935	49	1.102	89	1.284	129	1.484		
-30	0.788	10	0.939	50	1.106	90	1.289	130	1.489		
-29	0.792	11	0.943	51	1.110	91	1.294	131	1.494		
-28	0.796	12	0.947	52	1.115	92	1.299	132	1.499		
-27	0.799	13	0.951	53	1.119	93	1.303	133	1.505		
-26	0.803	14	0.955	54	1.124	94	1.308	134	1.510		
-25	0.806	15	0.959	55	1.128	95	1.313	135	1.515		
-24	0.810	16	0.963	56	1.133	96	1.318	136	1.520		
-23	0.814	17	0.967	57	1.137	97	1.323	137	1.526		
-22	0.817	18	0.971	58	1.141	98	1.328	138	1.531		
-21	0.821	19	0.975	59	1.146	99	1.333	139	1.536		

RATIO FORMULA

$$\begin{split} R_{\rm T} &= R_{25} \ge (9.0014 \ge 10^{-1} + 3.87235 \ge 10^{-3} \, (^{\circ}{\rm C})^{-1} \ge T + 4.86825 \ge 10^{-6} \, (^{\circ}{\rm C})^{-2} \ge T^2 + 1.37559 \ge 10^{-9} \, (^{\circ}{\rm C})^{-3} \ge T^3) \\ T_{(^{\circ}{\rm C})} &= 28.54 \ge (R_{\rm T}/R_{25})^3 - 158.5 \ge (R_{\rm T}/R_{25})^2 + 474.8 \ge (R_{\rm T}/R_{25}) - 319.85) \end{split}$$

RATIO TOLERANCES						
LOW TEMP.	HIGH TEMP.	TOL.				
-55 °C	+150 °C	±4%				
-40 °C	+125 °C	± 3 %				
-20 °C	+85 °C	±2 %				
0 °C	+55 °C	±1%				
+12 °C	+40 °C	± 0.5 %				


RATIO TOLERANCE EXAMPLES:

At 40 °C, ratio = $1.063 \pm 0.5 \%$ (0.005) so, ratio = 1.058 to 1.068At 125 °C, ratio = $1.460 \pm 3 \%$ (0.044) so, ratio = 1.416 to 1.504

Revision: 22-Mar-11

3 For technical questions, contact: <u>nlr@vishay.com</u> Document Number: 33017

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.