

ZDU 2.5-2/3AN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

General ordering data

| | |
|------------|--|
| Version | Feed-through terminal, Tension-clamp connection, 2.5 mm ² , 800 V, 24 A, dark beige |
| Order No. | 1706010000 |
| Type | ZDU 2.5-2/3AN |
| GTIN (EAN) | 4008 1909 15377 |
| Qty. | 100 pc(s). |

Creation date 14 November 2022 08:40:02 CET

Catalogue status 04.11.2022 / We reserve the right to make technical changes.

ZDU 2.5-2/3AN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------------------------|------------|----------------|------------|
| Depth | 43 mm | Depth (inches) | 1.693 inch |
| Depth including DIN rail | 44 mm | Height | 50.5 mm |
| Height (inches) | 1.988 inch | Width | 5.1 mm |
| Width (inches) | 0.201 inch | Net weight | 6.7 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|---|
| Storage temperature | | Operating temperature range | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity |
| | -25 °C...55 °C | | |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0 | | |

Rating data IECEx/ATEX

| | | | |
|--------------------------------|---|---------------------------------|-------------------|
| Certificate No. (ATEX) | DEMKO16ATEX1808U | Certificate No. (IECEX) | IECEXULD16.0036U |
| Max. voltage (ATEX) | 550 V | Current (ATEX) | 21 A |
| Wire cross section max. (ATEX) | 4 mm ² | Max. voltage (IECEX) | 550 V |
| Current (IECEX) | 21 A | Wire cross section max. (IECEX) | 4 mm ² |
| Operating temperature range | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity | Marking EN 60079-7 | |
| | | | Ex eb II C Gb |
| Ex 2014/34/EU label | II 2 G D | | |

System specifications

| | | | |
|-------------------------------|--|-------------------------------------|-------|
| Version | Tension-clamp connection, for plug-in cross-connector, One end without connector | End cover plate required | Yes |
| Number of levels | 1 | Number of clamping points per level | 3 |
| Number of potentials per tier | 1 | Levels cross-connected internally | No |
| PE connection | No | Rail | TS 35 |

Additional technical data

| | | | |
|--------------------------|-------|-----------------------------|---------|
| Explosion-tested version | Yes | Number of similar terminals | 1 |
| Open sides | right | Type of mounting | Snap-on |

CSA rating data

| | | | |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA) | 200039-1194786 | Current size C (CSA) | 23 A |
| Voltage size C (CSA) | 600 V | Wire cross section max. (CSA) | 14 AWG |
| Wire cross section min. (CSA) | 26 AWG | | |

Conductors for clamping (rated connection)

| | |
|----------------------|----------------------|
| Blade size | 0.6 x 3.5 mm |
| Clamping range, max. | 2.5 mm ² |
| Clamping range, min. | 0.13 mm ² |

Creation date 14 November 2022 08:40:02 CET

Catalogue status 04.11.2022 / We reserve the right to make technical changes.

ZDU 2.5-2/3AN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

| | | | | |
|---|---|--|----------------------|---------------------|
| Connection cross-section, stranded, max. | 0.5 mm ² | | | |
| Connection cross-section, stranded, min. | 2.5 mm ² | | | |
| Connection direction | Inclined / angled | | | |
| Gauge to IEC 60947-1 | A2 | | | |
| Number of connections | 3 | | | |
| Stripping length | 10 mm | | | |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4 | Cross-section for conductor connection | nominal | 0.5 mm ² | |
| | | min. | 6 mm | |
| | | max. | 10 mm | |
| | Cross-section for conductor connection | nominal | 0.75 mm ² | |
| | | min. | 6 mm | |
| | | max. | 10 mm | |
| | Cross-section for conductor connection | nominal | 1 mm ² | |
| | | min. | 6 mm | |
| | | max. | 10 mm | |
| | Cross-section for conductor connection | nominal | 1.5 mm ² | |
| | | min. | 8 mm | |
| | | max. | 10 mm | |
| | Cross-section for conductor connection | nominal | 2.5 mm ² | |
| | | nominal | 8 mm | |
| | Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Cross-section for conductor connection | nominal | 0.5 mm ² |
| nominal | | | 10 mm | |
| Cross-section for conductor connection | | nominal | 0.75 mm ² | |
| | | nominal | 10 mm | |
| Cross-section for conductor connection | | nominal | 1 mm ² | |
| | | nominal | 10 mm | |
| Cross-section for conductor connection | | nominal | 1.5 mm ² | |
| | | nominal | 10 mm | |
| Cross-section for conductor connection | | nominal | 2.5 mm ² | |
| | | nominal | 10 mm | |
| Type of connection | | Tension-clamp connection | | |
| Wire connection cross section AWG, max. | | AWG 12 | | |
| Wire connection cross section AWG, min. | | AWG 26 | | |
| Wire connection cross section, finely stranded, max. | | 2.5 mm ² | | |
| Wire connection cross section, finely stranded, min. | | 0.5 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm ² | | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1.5 mm ² | | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | | | |
| Wire connection cross-section, solid core, max. | 2.5 mm ² | | | |
| Wire connection cross-section, solid core, min. | 0.5 mm ² | | | |

ZDU 2.5-2/3AN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions

| | |
|--------------|---------|
| TS 35 offset | 25.5 mm |
|--------------|---------|

General

| | | | |
|---|--------|---|---------------|
| Rail | TS 35 | Standards | IEC 60947-7-1 |
| Wire connection cross section AWG, max. | AWG 12 | Wire connection cross section AWG, min. | AWG 26 |

Rating data

| | | | |
|---------------------------------|---------------------|--|---------|
| Rated cross-section | 2.5 mm ² | Rated voltage | 800 V |
| Rated current | 24 A | Current at maximum wires | 24 A |
| Standards | IEC 60947-7-1 | Volume resistance according to IEC 60947-7-x | 1.33 mΩ |
| Rated impulse withstand voltage | 8 kV | Power loss in accordance with IEC 60947-7-x | 0.77 W |
| Pollution severity | 3 | | |

UL rating data

| | | | |
|---|--------|---|--------|
| Certificate No. (UR) | E60693 | Conductor size Factory wiring max. (UR) | 12 AWG |
| Conductor size Factory wiring min. (UR) | 26 AWG | Conductor size Field wiring max. (UR) | 12 AWG |
| Conductor size Field wiring min. (UR) | 26 AWG | Current size C (UR) | 20 A |
| Voltage size C (UR) | 600 V | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000897 | ETIM 7.0 | EC000897 |
| ETIM 8.0 | EC000897 | ECLASS 9.0 | 27-14-11-20 |
| ECLASS 9.1 | 27-14-11-20 | ECLASS 10.0 | 27-14-11-20 |
| ECLASS 11.0 | 27-14-11-20 | ECLASS 12.0 | 27-14-11-20 |

Approvals

Approvals



| | |
|---------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E60693 |
| Certificate No. (cURusEX) | E184763 |

ZDU 2.5-2/3AN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | Attestation of Conformity UKCA Ex Attestation of Conformity ATEX Certificate IECEX Certificate CB Test Certificate CB Certificate EAC certificate DNVGL certificate EAC EX Certificate CCC Ex Certificate UKCA Ex Certificate Declaration of Conformity CE Declaration of Conformity all terminals UKCA Declaration of Conformity |
| Engineering Data | CAD data – STEP |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| User Documentation | NTI ZDU/ZPE 2.5-2/3AN StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Data sheet

ZDU 2.5-2/3AN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

