

19.05mmx3.81mm LED LIGHT BAR

Part Number: KB-2450YD

YELLOW


Features

- •UNIFORM LIGHT EMITTING AREA.
- •LOW CURRENT OPERATION.
- •EASILY MOUNTED ON P.C. BOARDS.
- •FLUSH MOUNTABLE.
- ●EXCELLENT ON/OFF CONTRAST.
- •CAN BE USED WITH PANELS AND LEGEND MOUNTS.
- ●RoHS COMPLIANT.

Description

The Yellow source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Yellow Light Emitting Diode.

Package Dimensions & Internal Circuit Diagram



Notes:

- 1. All dimensions are in millimeters (inches), Tolerance is $\pm 0.25 (0.01")$ unless otherwise noted. 2. Specifications are subject to change without notice.





SPEC NO: DSAF5140 **REV NO: V.2** DATE: APR/07/2007 PAGE: 1 OF 3 APPROVED: WYNEC **CHECKED:** Joe Lee DRAWN: W.J.ZHU

Kingbright

Selection Guide

Part No.	Dice	Lens Type	Iv (mcd) [1] @ 20mA	
			Min.	Тур.
KB-2450YD	YELLOW (GaAsP/GaP)	YELLOW DIFFUSED	7	37.834

Note:

Electrical / Optical Characteristics at Ta=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Yellow	590		nm	IF=20mA
λD [1]	Dominant Wavelength	Yellow	588		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Yellow	35		nm	IF=20mA
С	Capacitance	Yellow	20		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Yellow	2.1	2.5	V	IF=20mA
lR	Reverse Current	Yellow		10	uA	VR = 5V

Notes:

Absolute Maximum Ratings at Ta=25°C

Parameter	Yellow		
Power dissipation	75	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	140	mA	
Reverse Voltage	5	V	
Operating/Storage Temperature	-40°C To +85°C		
Lead Solder Temperature [2] 260°C For 3~5 Seconds			

Notes

SPEC NO: DSAF5140 REV NO: V.2 DATE: APR/07/2007 PAGE: 2 OF 3
APPROVED: WYNEC CHECKED: Joe Lee DRAWN: W.J.ZHU

^{1.}Luminous Intensity / Luminous Flux: +/-15%.


^{1.}Wavelength: +/-1nm.

^{2.} Forward Voltage: +/-0.1V.

^{1. 1/10} Duty Cycle, 0.1ms Pulse Width.


^{2. 2}mm below package base.


Kingbright





Yellow

KB-2450YD









PAGE: 3 OF 3

SPEC NO: DSAF5140 REV NO: V.2 DATE: APR/07/2007
APPROVED: WYNEC CHECKED: Joe Lee DRAWN: W.J.ZHU