

## Hand tap sets HSS and HSS Co 5 in steel case

Description	Article no. HSS	Article no. HSS Co 5
21-piece set of hand taps M DIN 352 one three-piece set each of M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12	245 001	245 001 E
22-piece set of hand taps M DIN 352 one three-piece set each of M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 1 tap wrench DIN 1814 size 1 1/2	245 002	245 002 E
29-piece set of hand taps DIN 352 one three-piece set each of M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 twist drills DIN 338 Type N Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm + 1 tap wrench DIN 1814 size 1 1/2	245 003	245 003 E



1.06

## Thread-cutting sets HSS in wood case



Description	Article no. HSS
28-piece set of thread-cutting tools one two-piece set each of hand taps G DIN 5157 — 1/8 - 1/4 - 3/8 - 1/2 - 5/8 - 3/4 - 1" + 7 dies G DIN EN 24231 in each of the sizes 1/8 - 1/4 - 3/8 - 1/2 - 5/8 - 3/4 - 1" + 5 die stocks DIN 225 in each of the sizes 30,0 x 11,0 mm - 38,0 x 10,0 mm - 45,0 x 14,0 mm - 55,0 x 16,0 mm - 65,0 x 18,0 mm + 2 tap wrenches, size 3 and size 5 DIN 1814	245 074
35-piece set of thread-cutting tools one two-piece set each of hand taps UNF ≈ DIN 2181 — 1/4 - 5/16 - 3/8 - 7/16 - 1/2 - 5/8 - 3/4 - 7/8 - 1" + 9 dies UNF ≈ DIN EN 22568 in each of the sizes 1/4 - 5/16 - 3/8 - 7/16 - 1/2 - 5/8 - 3/4 - 7/8 - 1" + 6 die stocks DIN 225 in each of the sizes 20,0 x 7,0 - 25,0 x 9,0 - 30,0 x 11,0 - 38,0 x 10,0 - 45,0 x 14,0 - 55,0 x 16,0 mm + 2 tap wrenches, size 2 and size 4 DIN 1814	245 073
44-piece set of thread-cutting tools one three-piece set each of hand taps UNC ≈ DIN 352 — 1/4 - 5/16 - 3/8 - 7/16 - 1/2 - 5/8 - 3/4 - 7/8 - 1" + 9 dies UNC ≈ DIN EN 22568 in each of the sizes 1/4 - 5/16 - 3/8 - 7/16 - 1/2 - 5/8 - 3/4 - 7/8 - 1" + 6 die stocks DIN 225 in each of the sizes 20,0 x 7,0 mm - 25,0 x 9,0 mm - 30,0 x 11,0 mm - 38,0 x 10,0 mm - 45,0 x 14,0 mm - 55,0 x 16,0 mm + 2 tap wrenches, size 2 and size 4 DIN 1814	245 072