

Twist drill type N with soldered cemented carbide insert 4xD

For universal use up to 1500 N/mm²

ORION[®]

Application:

Universal use in all material groups up to a strength of 1500 N/mm².

Execution:

- Twist drill with universal standard geometry, soldered cemented carbide insert (K20) and driving lug on the clamp shank

Advantage:

- Cemented carbide insert, K20, for a long service life
- polished chipping spaces ensure good chip removal
- cost-effective tool for broad range of applications



| | |
|---------------------------------|------------------|
| Art. no. | 11160 160 |
| Brand | ORION |
| Manufacturer Part Number | 11160160 |
| Cutting edge diameter | 16 mm |
| Chip flute length | 80 mm |
| Length | 140 mm |
| f steel 1300 | 0.18 mm/r |
| DIN | 8037 |
| Gross Weight | 0.166 kg |
| Product Group | 140 |

EAN

4039247030088