

30°, 45°, 60° chamfer cutters for milling inserts TCMT 1102.., TCMT 16T3..


ATORN®

Application

Universal use for chamfering and deburring.

Version

- with straight shank in accordance with DIN 1835 B
- Shaft tolerance h6
- Clamping screw tightening torque (indexable insert) M2.5 = 1.2 Nm, M4 = 5.2 Nm



Art. No.	16107 532
Chamfer angle	30 Degree
Max. cutting edge diameter	32 mm
Min. cutting edge diameter	6 mm
Clearance length	38 mm
Length	100 mm
Shaft diameter	25 mm
Number of cutting edges	2 PCS
Suitable indexable insert no.	2
Suitable for indexable inserts	TC.. 16T3..

EAN-Code

4050293112153