

## Revolving high-performance tips

With reinforced bearings



### Application:

For use in conjunction with conventional turning, CNC turning, rough machining and smoothing.

### Execution:

- 60° moving point.
- For all turning operations (roughing, finishing and fine turning).
- Precision and rough machining of medium-sized components.
- Hardened and precision-ground.

### Advantage:

- Long service life.
- Concentricity guaranteed with test report.
- Maintenance-free owing to permanent lubrication.
- Reinforced and hard-wearing precision bearings to absorb radial and axial forces.

### Delivery:

1x revolving high-performance tips.



<b>Art. no.</b>	<b>22130 060</b>
<b>Brand</b>	BRUCKNER
<b>Manufacturer Part Number</b>	5009
<b>Morse taper size</b>	MK 6
<b>Programming size</b>	179 mm
<b>Programming size for housing</b>	115 mm
<b>Max. workpiece weight</b>	3500 kg
<b>Max. rotation speed</b>	2300 rpm
<b>Concentricity tolerance</b>	0.005 mm
<b>Diameter of housing</b>	120 mm
<b>Tip diameter</b>	58 mm
<b>Gross Weight</b>	13.357 kg
<b>Product Group</b>	2AA