



## SA Series • High Efficiency - High Stability Storage Chokes

**SA Series** storage chokes have been designed with Fe-based amorphous alloy which provides high flux density and low core loss which is ideal for optimizing choke design. Providing exceptional efficiency and field modulation when used as loading coils for interim energy storage with SMPS, the use of amorphous cores gives a highly stable inductance over a wide DC bias current range and high "Q" with operating frequencies to 500kHz.

### Features

- Fe-based amorphous alloy cores
- Operating frequencies to 500kHz
- Small size and high "Q"
- Highly stable inductance with changing DC bias current
- Low temperature rise
- Fully encapsulated styles available meeting class GFK (-40°C to +125°C, humidity class F) per DIN 40040
- Manufactured in ISO-9001:2000, TS-16949:2002 and ISO-14001:2004 certified Talema facility
- Fully RoHS compliant



### Electrical Specifications @ 25°C

Test frequency: Inductance measured @ 10kHz / 10mV  
 Test voltage between windings: 500Vrms  
 Operating temperature: -40°C to +125°C  
 Climatic category: IEC68-1 40/125/56

Part Number	I <sub>DC</sub> Amps	L (μH) Typ. @ Rated Current	L <sub>O</sub> (μH) ±25% No Load	DCR mOhms Typical	Energy Storage (μJ) *	Schematic	Coil Size O.D. x Ht. (a x b)	Housing Size Code		Mounting Style (Terminal Ød)		
								F	V	O	F	V
SA_-0.63-22	0.63	22	23	95	4	1	12 x 8	17	20	0.355	0.60	0.80
SA_-0.63-33		33	35	118	7	1	12 x 8	17	20	0.355	0.60	0.80
SA_-0.63-47		47	49	141	10	1	13 x 9	17	20	0.355	0.60	0.80
SA_-0.63-68		68	70	167	13	1	13 x 9	17	20	0.355	0.60	0.80
SA_-0.63-100		100	105	206	20	1	13 x 9	17	20	0.355	0.60	0.80
SA_-0.63-150		150	157	276	29	1	13 x 9	17	20	0.335	0.60	0.80
SA_-0.63-220		220	248	348	44	1	14 x 9	17	20	0.335	0.60	0.80
SA_-0.63-330		330	389	436	65	1	14 x 9	17	20	0.335	0.60	0.80
SA_-0.63-470		470	480	421	92	1	16 x 8	22	20	0.335	0.60	0.80
SA_-0.63-680		680	728	519	136	1	17 x 9	22	25	0.335	0.60	0.80
SA_-0.63-1000		1000	1105	639	197	1	17 x 9	22	25	0.335	0.60	0.80
SA_-0.63-1500		1500	1523	801	299	1	22 x 8	29	30	0.335	0.60	0.80
SA_-0.63-2200		2200	2249	974	437	1	23 x 9	29	30	0.335	0.60	0.80
SA_-0.63-3300		3300	3514	1217	655	1	24 x 10	29	30	0.335	0.60	0.80
SA_-0.63-4700		4700	5345	1501	933	1	24 x 10	29	30	0.335	0.60	0.80
SA_-0.63-6800		6800	6949	2003	1351	1	27 x 16	32	35	0.335	0.60	0.80
SA_-0.63-8200	8200	9057	2287	1618	1	28 x 17	32	40	0.335	0.60	0.80	
SA_-1.0-22	1.0	22	23	59	11	1	12 x 8	17	20	0.450	0.60	0.80
SA_-1.0-33		33	35	73	17	1	12 x 8	17	20	0.450	0.60	0.80
SA_-1.0-47		47	49	88	23	1	13 x 9	17	25	0.450	0.60	0.80
SA_-1.0-68		68	73	107	34	1	13 x 9	17	25	0.450	0.60	0.80
SA_-1.0-100		100	102	110	51	1	16 x 9	22	25	0.450	0.60	0.80
SA_-1.0-150		150	151	134	74	1	16 x 9	22	25	0.450	0.60	0.80
SA_-1.0-220		220	230	165	110	1	16 x 9	22	25	0.450	0.60	0.80
SA_-1.0-330		330	362	207	167	1	18 x 10	22	25	0.450	0.60	0.80
SA_-1.0-470		470	472	252	236	1	22 x 9	29	25	0.450	0.60	0.80
SA_-1.0-680		680	698	307	342	1	24 x 10	29	25	0.450	0.60	0.80
SA_-1.0-1000		1000	1031	373	500	1	24 x 10	29	30	0.450	0.60	0.80
SA_-1.0-1500		1500	1641	470	746	1	24 x 10	29	30	0.450	0.60	0.80
SA_-1.0-2200		2200	2589	591	1100	1	25 x 11	29	30	0.450	0.60	0.80
SA_-1.0-3300		3300	3359	788	1646	1	28 x 17	32	40	0.450	0.60	0.80
SA_-1.0-4700		4700	4968	958	2360	1	28 x 17	32	40	0.450	0.60	0.80
SA_-1.0-6800		6800	8000	1215	3400	1	29 x 18	32	40	0.450	0.60	0.80

Talema's engineering staff can assist in the design of other inductance values and sizes.

## SA Series • High Efficiency - High Stability Storage Chokes

### Electrical Specifications at 25°C

Part Number	I <sub>DC</sub> Amps	L (µH) Typ. @ Rated Current	L <sub>O</sub> (µH) ±25% No Load	DCR mOhms Typical	Energy Storage (µJ) *	Schematic	Coil Size O.D. x Ht. (a x b)	Housing Size Code		Mounting Style Terminal Ø		
								F	V	O	F	V
SA__-1.6-22	1.6	22	23	38	27	1	13 x 8	17	20	0.560	0.560	0.800
SA__-1.6-33		33	27	49	42	1	14x 9	17	25	0.560	0.560	0.800
SA__-1.6-47		47	55	60	59	1	14 x 9	17	25	0.560	0.560	0.800
SA__-1.6-68		68	67	57	84	1	17 x 9	22	25	0.560	0.560	0.800
SA__-1.6-100		100	107	73	130	1	17 x 9	22	25	0.560	0.560	0.800
SA__-1.6-150		150	169	91	195	1	17 x 9	22	25	0.560	0.560	0.800
SA__-1.6-220		220	268	115	278	1	18 x 11	22	25	0.560	0.560	0.800
SA__-1.6-330		330	343	139	426	1	23 x 9	29	25	0.560	0.560	0.800
SA__-1.6-470		470	516	170	608	1	23 x 9	29	25	0.560	0.560	0.800
SA__-1.6-680		680	765	207	872	1	24 x 11	29	30	0.560	0.560	0.800
SA__-1.6-1000		1000	1300	165	1272	1	27 x 16	32	35	0.560	0.560	0.800
SA__-1.6-1500		1500	1549	345	1923	1	27 x 16	32	35	0.560	0.560	0.800
SA__-1.6-2200		2200	2402	430	2929	1	28 x 17	32	40	0.560	0.560	0.800
SA__-1.6-3300		3300	3458	565	4205	1	33 x 17	42	40	0.560	0.560	0.800
SA__-1.6-4700		4700	4968	718	6041	1	43 x 16	49	45	0.560	0.560	0.800
SA__-1.6-5600	5600	6216	804	7161	1	45 x 18	49	--	0.560	0.560	--	
SA__-2.0-22	2.0	22	23	27	46	1	15 x 8	17	20	0.630	0.630	0.630
SA__-2.0-33		33	33	32	65	1	15 x 8	17	20	0.630	0.630	0.630
SA__-2.0-47		47	49	39	83	1	15 x 8	17	20	0.630	0.630	0.630
SA__-2.0-68		68	75	48	137	1	15 x 8	17	20	0.630	0.630	0.630
SA__-2.0-100		100	112	59	200	1	16 x 9	22	20	0.630	0.630	0.630
SA__-2.0-150		150	195	76	302	1	16 x 9	22	20	0.630	0.630	0.630
SA__-2.0-220		220	234	91	446	1	23 x 10	29	30	0.630	0.630	0.630
SA__-2.0-330		330	362	113	658	1	25 x 11	29	30	0.630	0.630	0.630
SA__-2.0-470		470	551	139	947	1	25 x 11	29	30	0.630	0.630	0.630
SA__-2.0-680		680	701	184	1374	1	27 x 16	32	35	0.630	0.630	0.630
SA__-2.0-1000		1000	1060	226	2014	1	29 x 18	32	40	0.630	0.630	0.630
SA__-2.0-1500		1500	1693	285	3013	1	29 x 17	32	40	0.630	0.630	0.630
SA__-2.0-2200		2200	2500	379	4401	1	35 x 19	49	45	0.630	0.630	0.630
SA__-2.0-3300		3300	3594	483	6612	1	46 x 19	49	--	0.630	0.630	--
SA__-2.0-3900		3900	4567	544	7855	1	46 x 19	49	--	0.630	0.630	--
SA__-2.5-22	2.5	22	23	23	70	1	16 x 8	22	20	0.670	0.670	0.670
SA__-2.5-33		33	33	28	101	1	16 x 8	22	20	0.670	0.670	0.670
SA__-2.5-47		47	52	35	150	1	18 x 10	22	25	0.670	0.670	0.670
SA__-2.5-68		68	75	42	209	1	18 x 10	22	25	0.670	0.670	0.670
SA__-2.5-100		100	123	53	307	1	18 x 10	22	25	0.670	0.670	0.670
SA__-2.5-150		150	159	65	476	1	23 x 10	32	30	0.670	0.670	0.670
SA__-2.5-220		220	242	80	688	1	23 x 10	32	30	0.670	0.670	0.670
SA__-2.5-330		330	381	100	1023	1	23 x 10	32	30	0.670	0.670	0.670
SA__-2.5-470		470	476	131	1459	1	27 x 16	32	35	0.670	0.670	0.670
SA__-2.5-680		680	720	161	2138	1	27 x 16	32	35	0.670	0.670	0.670
SA__-2.5-1000		1000	1107	200	3114	1	29 x 18	32	40	0.670	0.670	0.670
SA__-2.5-1500		1500	1786	278	4743	1	34 x 18	42	40	0.670	0.670	0.670
SA__-2.5-2200		2200	2441	345	6867	1	43 x 16	49	--	0.670	0.670	--
SA__-2.5-2700		2700	3295	401	8444	1	43 x 16	49	--	0.670	0.670	--
SA__-3.15-22		3.15	22	23	19	107	1	16 x 8	22	20	0.750	0.750
SA__-3.15-33	33		36	24	164	1	18 x 10	22	25	0.750	0.750	0.750
SA__-3.15-47	47		56	29	238	1	18 x 10	22	25	0.750	0.750	0.750
SA__-3.15-68	68		71	35	346	1	22 x 8	29	25	0.750	0.750	0.750
SA__-3.15-100	100		103	42	488	1	24 x 10	29	30	0.750	0.750	0.750
SA__-3.15-150	150		165	54	736	1	24 x 10	29	30	0.750	0.750	0.750
SA__-3.15-220	220		266	68	1107	1	24 x 10	29	30	0.750	0.750	0.750
SA__-3.15-330	330		333	89	1619	1	28 x 17	32	40	0.750	0.750	0.750
SA__-3.15-470	470		492	108	2319	1	28 x 17	32	40	0.750	0.750	0.750
SA__-3.15-680	680		799	138	3369	1	28 x 17	32	40	0.750	0.750	0.750
SA__-3.15-1000	1000		1265	190	5020	1	35 x 19	42	40	0.750	0.750	0.750
SA__-3.15-1500	1500		1656	231	7393	1	44 x 17	49	--	0.750	0.750	--

**How To Order:** Refer to SD Series data sheet for Ordering Key

## SA Series • High Efficiency • High Stability Storage Chokes

### Electrical Specifications at 25°C

Part Number	I <sub>DC</sub> Amps	L (µH) Typ. @ Rated Current	L <sub>o</sub> (µH) ±25% No Load	DCR mOhms Typical	Energy Storage (µJ) *	Schematic	Coil Size O.D. x Ht. (a x b)	Housing Size Code		Mounting Style Terminal Ød		
								F	V	O	F	V
SA_-4.0-22	4.0	22	23	15	155	1	16 X 8	22	20	0.850	0.850	0.850
SA_-4.0-33		33	39	19	260	1	18 x 11	22	25	0.850	0.850	0.850
SA_-4.0-47		47	48	22	375	1	22 x 9	29	25	0.850	0.850	0.850
SA_-4.0-68		68	75	28	556	1	24 x 11	29	30	0.850	0.850	0.850
SA_-4.0-100		100	113	35	812	1	24 x 11	29	30	0.850	0.850	0.850
SA_-4.0-150		150	157	48	1242	1	26 x 15	32	35	0.850	0.850	0.850
SA_-4.0-220		220	226	57	1752	1	28 x 17	32	40	0.850	0.850	0.850
SA_-4.0-330		330	360	72	2646	1	28 x 17	32	40	0.850	0.850	0.850
SA_-4.0-400		400	476	83	3239	1	28 x 17	32	40	0.850	0.850	0.850
SA_-4.0-470		470	508	94	3738	1	33 x 17	42	40	0.850	0.850	0.850
SA_-4.0-680		680	703	117	5515	1	44 x 17	49	--	0.850	0.850	--
SA_-4.0-1000		1000	1191	153	8006	1	44 x 17	49	--	0.850	0.850	--
SA_-5.0-22	5.0	22	28	13	281	1	19 x 11	22	25	0.950	0.950	0.950
SA_-5.0-33		33	35	15	430	1	22 x 9	29	25	0.950	0.950	0.950
SA_-5.0-47		47	51	19	596	1	22 x 9	29	25	0.950	0.950	0.950
SA_-5.0-68		68	75	23	831	1	25 x 11	29	30	0.950	0.950	0.950
SA_-5.0-100		100	100	31	1242	1	26 x 15	32	35	0.950	0.950	0.950
SA_-5.0-150		150	157	38	1882	1	26 x 15	32	35	0.950	0.950	0.950
SA_-5.0-220		220	237	47	2722	1	29 x 18	32	40	0.950	0.950	0.950
SA_-5.0-330		330	362	63	4068	1	34 x 18	42	40	0.950	0.950	0.950
SA_-5.0-470		470	492	78	5955	1	42 x 15	49	45	0.950	0.950	0.950
SA_-5.0-630		630	703	94	7914	1	45 x 18	49	--	0.950	0.950	--
SA_-5.0-680	680	845	103	8554	1	45 x 18	49	--	0.950	0.950	--	
SA_-6.3-22	6.3	22	24	9	450	1	23 x 9	29	25	1.120	1.120	1.120
SA_-6.3-33		33	35	11	635	1	23 x 9	29	25	1.120	1.120	1.120
SA_-6.3-47		47	55	14	959	1	26 x 12	29	30	1.120	1.120	1.120
SA_-6.3-68		68	68	18	1317	1	27 x 16	32	35	1.120	1.120	1.120
SA_-6.3-100		100	108	23	2051	1	27 x 16	32	35	1.120	1.120	1.120
SA_-6.3-150		150	166	28	2963	1	30 x 19	32	40	1.120	1.120	1.120
SA_-6.3-220		220	251	38	4435	1	35 x 19	42	40	1.120	1.120	1.120
SA_-6.3-330		330	357	48	6587	1	43 x 16	49	45	1.120	1.120	1.120
SA_-6.3-390		390	459	55	7842	1	46 x 19	49	--	1.120	1.120	--
SA_-8.0-22	8.0	22	24	7	695	1	23 x 10	29	30	1.250	1.250	1.250
SA_-8.0-33		33	38	9	1037	1	26 x 13	29	30	1.250	1.250	1.250
SA_-8.0-47		47	47	12	1434	1	27 x 16	32	35	1.250	1.250	1.250
SA_-8.0-68		68	74	15	2241	1	27 x 16	32	35	1.250	1.250	1.250
SA_-8.0-100		100	123	20	3188	1	30 x 19	32	40	1.250	1.250	1.250
SA_-8.0-150		150	179	26	4698	1	35 x 19	42	40	1.250	1.250	1.250
SA_-8.0-220		220	244	32	7107	1	43 x 16	49	45	1.250	1.250	1.250
SA_-8.0-270		270	330	37	8554	1	46 x 19	49	--	1.250	1.250	--
SA_-10-22	10	22	22	7	1060	1	27 x 16	32	40	1.320	1.320	1.320
SA_-10-33		33	33	9	1589	1	27 x 16	32	40	1.320	1.320	1.320
SA_-10-47		47	51	11	2406	1	27 x 16	32	40	1.320	1.320	1.320
SA_-10-68		68	80	14	3280	1	27 x 16	32	40	1.320	1.320	1.320
SA_-10-100		100	127	19	5079	1	34 x 18	42	40	1.320	1.320	1.320
SA_-10-150		150	171	24	7442	1	43 x 16	49	--	1.320	1.320	--
SA_-10-180		180	233	27	8876	1	43 x 16	49	--	1.320	1.320	--
SA_-16-22	16	22	29	5	2986	2P	30 x 19	32	40	1.180	1.180	1.180
SA_-16-33		33	36	6	4128	2P	35 x 19	42	40	1.180	1.180	1.180
SA_-16-47		47	70	10	7150	2P	43 x 16	49	45	1.180	1.180	1.180
SA_-16-68		68	83	10	8554	2P	43 x 16	49	45	1.180	1.180	1.180
SA_-20-10	20	10	10	3	2011	2P	27 x 16	32	40	1.320	1.320	1.320
SA_-20-22		22	24	4	4278	2P	32 x 16	42	40	1.320	1.320	1.320
SA_-20-33		33	38	6	6867	2P	43 x 16	49	--	1.320	1.320	--
SA_-20-47		47	53	7	8976	2P	43 x 16	49	--	1.320	1.320	--


**Notes:**

- 1) The µJoule rating ( $\frac{1}{2}LI^2$ ) is the ability of the inductor to store energy.
- 2) Inductance measured at 0.10 Vrms @ 10kHz without DC Current and 0.25 Vrms @ 10kHz with DC Current.
- 3) On larger units and units wound with finer wire additional mechanical mounting is recommended. See next page for Mounting Options.



## SD Series • High Efficiency Storage Chokes

**SD Series** storage chokes provide excellent efficiency and field modulation when used as loading coils for interim energy storage with switch mode power supplies. The use of MPP cores allows compact size, a highly stable inductance over a wide bias current range and high "Q" with operating frequencies to 200kHz.



### Features

- Operating frequency to 200kHz
- Small size and high "Q"
- Highly stable inductance with changing bias current
- Fully encapsulated styles available meeting class GFK (-40°C to +125°C, humidity class F) per DIN 40040.
- Manufactured in ISO-9001:2000, TS-16949:2002 and ISO-14001:2004 certified Talema facility
- Fully RoHS compliant

### Electrical Specifications @ 25°C

Test frequency: Inductance measured @ 10kHz / 10mV

Test voltage between windings: 500Vrms

Operating temperature: -40°C to +125°C

Climatic category: IEC68-1 40/125/56

Part Number	I <sub>DC</sub> Amps	L (μH) Typ. @ Rated Current	L <sub>O</sub> (μH) ±15% No Load	DCR mOhms Typical	Energy Storage (μJ) <sup>1</sup>	Schematic <sup>2</sup>			Coil Size O.D. x Ht. (a x b)	Housing Size Code		Mounting Style Terminals Ød		
						Mounting Style				F	V	O	F	V
						O	F	V						
SD__-0.63-400	0.63	400	474	537	79	1	1	1	15 x 7	17	20	0.250	0.600	0.800
SD__-0.63-500		500	620	670	99	1	1	1	15 x 7	17	20	0.250	0.600	0.800
SD__-0.63-630		630	820	563	12	1	1	1	15 x 7	17	20	0.280	0.600	0.800
SD__-0.63-1000		1000	1157	650	198	1	1	1	19 x 9	22	25	0.300	0.600	0.800
SD__-0.63-2000		2000	2695	992	397	1	1	1	20 x 9	22	25	0.300	0.600	0.800
SD__-0.63-2500		2500	3080	730	496	1	1	1	26 x 12	29	30	0.400	0.600	0.800
SD__-0.63-4000		4000	5625	1000	794	1	1	1	26 x 12	29	30	0.400	0.600	0.800
SD__-0.63-6000		6000	7600	1150	1191	1	1	1	30 x 15	32	35	0.40	0.600	0.800
SD__-1.0-250	1.0	250	323	354	125	1	1	1	15 x 7	17	20	0.355	0.600	0.800
SD__-1.0-500		500	580	210	250	1	1	1	19 x 9	22	25	0.450	0.600	0.800
SD__-1.0-1000		1000	1250	290	500	1	1	1	26 x 12	29	30	0.500	0.600	0.800
SD__-1.0-2500		2500	4160	550	1250	1	1	1	26 x 12	29	30	0.500	0.600	0.800
SD__-1.0-4000		4000	5970	820	2000	1	1	1	30 x 15	32	35	0.450	0.600	0.800
SD__-1.0-6000		6000	9260	970	3000	1	2R	1	37 x 15	42	40	0.500	0.500	0.800
SD__-1.6-160	1.6	160	251	127	205	1	1	1	15 x 7	17	20	0.500	0.800	0.800
SD__-1.6-315		315	443	289	408	1	1	1	19 x 8	22	25	0.355	0.800	0.800
SD__-1.6-400		400	613	266	502	1	1	1	19 x 9	22	25	0.400	0.800	0.800
SD__-1.6-500		500	695	115	640	1	1	1	26 x 12	29	30	0.710	0.800	0.800
SD__-1.6-1000		1000	1290	195	1280	1	2R	1	30 x 15	32	35	0.630	0.630	0.800
SD__-1.6-2500		2500	3670	380	3200	1	1	1	37 x 15	42	40	0.630	0.800	0.800
SD__-1.6-4000		4000	5440	450	5140	1	1	--	44 x 18	49	--	0.630	0.800	--
SD__-2.0-63	2.0	63	81	87	126	1	1	1	14 x 6	17	20	0.400	0.800	0.800
SD__-2.0-100		100	115	161	200	1	1	1	19 x 8	22	25	0.355	0.800	0.800
SD__-2.0-315		315	422	168	650	1	1	1	25 x 9	29	30	0.800	0.800	0.800
SD__-2.0-630		630	885	120	1260	1	1	1	26 x 12	29	30	0.750	0.800	0.800
SD__-2.0-1000		1000	1387	145	2000	1	1	1	30 x 15	42	35	0.750	0.800	0.800
SD__-2.0-1600		1600	2420	200	3200	1	1	1	37 x 15	42	40	0.800	0.800	0.800
SD__-2.0-2500		2500	3240	313	5000	1	1	--	46 x 20	49	--	0.850	0.850	--
SD__-2.5-63	2.5	63	99	62	197	1	1	1	14 x 6	17	20	0.500	0.800	0.800
SD__-2.5-100		100	129	122	312	1	1	1	19 x 8	22	25	0.400	0.800	0.800
SD__-2.5-160		160	241	132	489	1	1	1	19 x 8	22	25	0.450	0.800	0.800
SD__-2.5-200		200	275	70	630	1	2R	1	26 x 12	29	30	0.750	0.750	0.800
SD__-2.5-400		400	790	120	1250	1	2R	1	26 x 12	29	30	0.710	0.710	0.800
SD__-2.5-1000		1000	1521	125	3125	1	2R	1	39 x 16	42	45	0.950	0.950	1.000
SD__-3.15-63	3.15	63	80	62	312	1	1	1	19 x 8	22	25	0.500	0.800	0.800
SD__-3.15-100		100	157	60	498	1	1	1	19 x 8	22	25	0.600	0.800	0.800
SD__-3.15-160		160	234	86	794	1	1	1	25 x 10	29	30	0.600	0.800	0.800
SD__-3.15-250		250	570	85	1240	1	2P	1	26 x 12	29	30	0.560	0.560	0.800
SD__-3.15-630		630	1122	110	3125	1	2R	1	37 x 15	42	40	0.900	0.900	0.900

## SD Series • High Efficiency Storage Chokes

### Electrical Specifications at 25°C

Part Number	I <sub>DC</sub> Amps	L (μH) Typ. @ Rated Current	L <sub>0</sub> (μH) ±15% No Load	DCR mOhms Typical	Energy Storage (μJ) <sup>1</sup>	Schematic <sup>2</sup>			Coil Size O.D. x Ht. (a x b)	Housing Size Code		Mounting Style Terminals Ød		
						Mounting Style				F	V	O	F	V
						O	F	V						
SD_-4.0-47	4.0	47	65	55	376	1	1	1	20 x 9	22	25	0.500	0.800	0.800
SD_-4.0-100		100	144	68	800	1	1	1	25 x 10	29	30	0.600	0.800	0.800
SD_-4.0-160		160	240	40	1280	1	1	1	26 x 12	29	30	0.900	1.000	0.900
SD_-4.0-250		250	345	50	2000	1	1	1	30 x 15	42	45	0.950	1.000	1.000
SD_-5.0-47	5.0	47	60	44	588	1	1	1	25 x 10	29	30	0.600	0.800	0.800
SD_-5.0-63		63	91	43	797	1	1	1	25 x 10	29	30	0.670	0.800	0.800
SD_-5.0-100		100	165	27	1250	2P	2P	2P	26 x 12	29	30	0.750	0.750	0.750
SD_-5.0-250		250	357	40	3125	2R	1	1	39 x 16	42	45	1.180	1.180	1.180
SD_-6.3-47	6.3	47	76	44	946	1	1	1	26 x 11	29	30	1.000	1.000	1.000
SD_-6.3-63		63	120	17	1250	1	1	1	26 x 12	29A	30	1.180	1.180	1.180
SD_-6.3-100		100	160	28	2010	1	1	1	29 x 13	32	35	0.670	0.800	0.800
SD_-6.3-200		200	266	44	3969	2P	2P	2P	38 x 17	42	40	0.850	0.850	0.850
SD_-8.0-47	8.0	47	63	43	1507	1	1	1	29 x 13	32	35	0.670	0.800	0.800
SD_-8.0-63		63	95	12	2016	2P	2P	1	30 x 15	32	35	0.950	0.950	0.950

The Talema engineering staff can assist in the design of other inductance values and sizes including pre-designed cable lug models to 63 Amps.

1) The μJoule rating ( $\frac{1}{2}LI^2$ ) is the ability of the inductor to store energy.

2) Schematic:

1 = one winding


2P = two windings, Parallel Connection

2R = two windings, Series Connection.

3) Inductance measured at 0.10 Vrms @ 10kHz without DC Current and 0.25 Vrms @ 10kHz with DC Current.

4) On larger units and units wound with fine wire, additional mechanical mounting is recommended. See next page for Mounting Styles.

### Ordering Key



## Sales & Marketing, Design and Manufacturing Facilities

<http://www.talema-nuvotem.com>

### Eastern Europe & Czech Republic

NT MAGNETICS s.r.o.  
 Chebská 27  
 322 00 Plzeň  
 Tel: Int. + 420 377 - 338 351  
 Fax: Int. + 420 377 - 338 350  
 Email: [talema@talema.cz](mailto:talema@talema.cz)  
 Web Site: [www.ntmagnetics.cz](http://www.ntmagnetics.cz)

### Germany

TALEMAELEKTRONIK GMBH  
 Sembdnerstr. 5, Postfach 2523  
 82110 Germering  
 Tel: Int. + 49 89 - 841 00 - 0  
 Fax: Int. + 49 89 - 841 00 25  
 Email: [info@talema.de](mailto:info@talema.de)

### Ireland


NUVOTEMTEO.  
 Crollý  
 Co. Donegal  
 Tel: Int. + 353 74 - 954 8666  
 Fax: Int. + 353 74 - 954 8139  
 Email: [info@nuvotem.com](mailto:info@nuvotem.com)

### India


TALEMAELECTRONIC PVT. LTD.  
 Opposite the SIDCO Industrial Estate  
 Gins Towers  
 4/5S.H/1, Omalur Main Road  
 Salem - 636 004, Tamil Nadu  
 Tel: Int. + 91 427 - 244 1325  
 Fax: Int. + 91 427 - 243 0034  
 E-mail: [talema@talemaindia.com](mailto:talema@talemaindia.com)  
 Web Site: [www.talemaindia.com](http://www.talemaindia.com)




Mounting Style V



Mounting Style 'O' = Open Mount



Mounting Style F



Tolerance on Pin Length: ±0.3mm