

## Torque wrench with fixed built-in ratchet, adjustable from 1.5–12.5 Nm

Standard MANOSKOP® 755 R/1, without calibration certificate



### Execution:

- Display deviation of +/- 4 %
- Releasing, with double stop signal
- Adjustment with torque wrench tester
- Handle and shaft made of square steel tube
- Further load or impact against the direction of operation (up to the measuring range limit of the torque wrench) does not affect the trigger mechanism, thereby protecting it from damage
- Independent of force application point
- IMPORTANT: Key not set at factory – specify setting value and order fine adjustment separately



### Advantage:

- Particularly light and practical

<b>Art. no.</b>	<b>52280 050</b>
<b>Brand</b>	STAHlwILLE
<b>Manufacturer Part Number</b>	50100001
<b>Tip size</b>	1/4 inch
<b>Max. torque</b>	12.5 Nm
<b>Min. torque</b>	1.5 Nm
<b>Length</b>	174 mm
<b>Min./max. torque</b>	1.5-12.5 Nm
<b>Error limit (%)</b>	4 %
<b>Gross Weight</b>	0.335 kg
<b>Product Group</b>	531

### EAN

4018754096268