

Straight grinder GE 710 Compact

710 W, 230 V, 50 Hz

metabo[®]

Application:

High rotation speed makes it ideal for milling and grinding work.

Execution:

- adjustment wheel for pre-selecting the speed
- VC electronics for working at appropriate speeds for the material, speeds remain virtually constant under load
- Electronic overload protection
- Safety motor cut-off and restart protection
- Precision collet chuck for precise concentricity

Delivery:

Collet chuck, open-end spanner, in box



Art. no.	70309 007
Brand	METABO
Manufacturer Part Number	600615000
Model	GE 710 Compact
Min./max. idle speed	13000-34000 rpm
Power input	710 W
Power output	430 W
Spindle-neck diameter	43 mm
Max. clamping diameter	8 mm
Weight	1.4 kg
Gross Weight	2.182 kg
Product Group	745

EAN

4007430212313