

+ 44 (0) 208 920 2306 www.energizer-eu.com

ENERGIZER 391

ZEROMERCURY"

SILVER OXIDE



Industry Standard Dimensions

11.60 (0.457)
11.25 (0.443)

R0.90 (0.035) Ref.
Typical

O.03 (0.001) Minimum Ref.
Permissible defelection from a flat.
(Applies to top edge of gasket or

DESIGNED FOR USE ON CONTINUOUS LOW DRAIN HIGH PULSE ON DEMAND

edge of crimp, whichever is higher.)

Specifications

Chemical System: Silver Oxide (Zn/Aq₂O)

Designation: ANSI-1160SO/1170SO, IEC-SR55

Nominal Voltage: 1.55 Volts

Typical Capacity: 60 mAh* (to 1.2 volts)


Capacity Test: 15K ohm continuous drain at 21°C

Typical Weight: 0.92 grams (0.03 oz.)

Typical Volume: 0.22 cubic centimeters (0.013 cubic inch)

Impedance (40 Hz): 5 to 7 ohms


Cross Section



Typical Discharge Characteristics

Typical Performance at 21°C (70°F)


Schedule: Continuous Typical Drain @1.55V: 0.103 milliamperes Load: 15K ohm




<u>Schedule</u>	Typical Drains at 1.55V	<u>Load</u>	Cutoff 1.2V
	(milliamperes)	(ohm)	(hours)
Continuous	0.103	15K	581

Temperature Characteristics

Typical Performance at Low Discharge Rates





Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Form No. EBC - 4365A-ZEU Page 1 of 1

^{*} Varies according to the applied load, temperature, and cutoff voltage.