Squba 1.80mm- and 3.60mm-Pitch Sealed Wire-To-Wire Connector System


molex

Squba 1.80mm- and 3.60-Pitch Sealed Wire-to-Wire Connector Systems are designs that offer an IP67-seal rating and carry up to 14.0A of current to deliver reliable power in a wide range of space-constrained applications



Squba 3.600mm-Pitch Sealed Connector Family, Fully Mated, 2 to 4 Circuits

Features and Advantages



Clean-body terminalsAvoids seal punctures

Squba 1.80mm- and 3.60mm-Pitch Sealed Wire-To-Wire Connector System



Markets and Applications

Consumer

Liquid dispensing equipment

HVAC equipment

Landscaping equipment

Commercial vehicle

ATV

Marine: under-dash wiring, lighting

Forklifts

Trucks

Buses

Recreational vehicles

Industrial

Robotics

Industrial machines and motors

Food processing equipment/plants

Industrial controls

Connected Home

Security and surveillance

Smart appliance

Home health and wellness

Home automation



Security Systems



Robotic Arm



HVAC



ATV

Specifications

REFERENCE INFORMATION

Receptacle Packaging: Tray Plug Packaging: Bulk Crimp Terminal Packaging: Reels

UL File No.: TBD CSA File No.: TBD

1.80mm 3.60mm

Use With: 22 to 24 AWG 16 to 20 AWG Insulation Diameter: 0.95 to 1.40mm 1.50 to 2.40mm

Designed In: Millimeters

RoHS: Yes Halogen Free: No Glow Wire Compliant: TBD IP Rating: IP67

ELECTRICAL

 1.80mm
 3.60mm

 Voltage (max.):
 125V
 600V

 Current (max.):
 6.0A
 14.0A

Contact Resistance: 10 milliohms

Dielectric Withstanding Voltage: Leakage < 5mA Insulation Resistance (min.): 100 Megohms

MECHANICAL

Terminal Retention to Housing (min.): 30N

Mating Force (max.): 45N Unmating Force (max.): 35N Durability (max.): 10 Cycles

PHYSICAL

Housing: Plastic Contact: Copper Alloy

Plating:

Overall — Tin

Underplating — Nickel

Operating Temperature: -40 to +105°C

Ordering Information

Series No.	Component	Pitch	Circuits
207782	Receptacle	3.60mm	2, 3 and 4
207778	Plug		
207777	Receptacle Crimp Terminal	N/A	N/A
207776	Plug Crimp Terminal		

Series No.	Component	Pitch	Circuits
204220	Receptacle	1.80mm	2 to 10
204223	Plug		
<u>204301</u>	Receptacle Crimp Terminal	N/A	N/A
204226	Plug Crimp Terminal		

www.molex.com/link/squba.html