

MG 100S Kit 1

Product no.: 100-1056-ESDN



Benefits

- › High Gasfilter volume
- › Electronic filter control with filter alarm
- › Variable speed setting
- › Minimized foot print
- › Switching power supply 100 – 240 V
- › Optimized filter lifetime
- › The MG 100S kit 1 will be delivered with flexible extrctation arm 1 meter, funnel nozzle and valve. The fume extraction unit is suitable for applications with a high demand of gases. Variable speed and alarm function for filter exchange can be set via the remote control. To make installation easier, the MG 100S can be suspended at the work table with special table mounting set (780-3001-ESD).

For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning




Pre-heating plates



Technical Data

Dimensions L x W x H (mm)	460 x 210 x 610
Dimensions L x W x H (inches)	18,11 x 8,26 x 24,15
Weight (approx.) in kg	15
Voltage	110 - 240 V, 50/60 Hz
Power	100 W
Noise level (distance 1 m) dB(A)	< 52
Max. vacuum	---
Capacity m³/h	140
Pre-filter	---
Compact filter	Particle filter H13, Wide band gas filter (50 % Active carbon + 50 % Chemisorb)
Max. capacity	1-2 workstations
RS232 interface (remote control)	1 x RS232 (TTL)
USB port	---
WX-compatible	---

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE