## **Rocker Switch**

## multicomp PRO

....

Specifications					RoHS Compliant
Rating	: 16A 125V AC 1/3HP	N	lounting He	ole	Circuit Diagram
Ū	10A 250V AC 1/2HP CNus T8 10(4)A 250V & @@@ 2518 10A 125V AC, 6A 250V AC CQC	85		~	•
Contract Resistance Insulation Resistance	: 50m Ω Max. : DC 500V 100M Ω Min.	-	X		1 2
Dielectric Strength	: AC 1500V 1 minute	Thickness	X	Y	
Operation Temperature Switch Function	: -25°C to +85°C : 2 Position SPST ON-OFF	0.75-1.25	19.2-0.1		
Switch Function	. 2 Position 3P31 ON-OFF	1.25-2	19.4-0.1	13+0.1	
Material		2-3	19.8-0.1		
Frame : Nylon#66, Bla Actuator : Nylon#66, Re Printed : None	ed	21.0	15.0	٨	
		FF ON		9.9 0 0 0 0 0 2 2 4.8±0	- 11
Tolorancos ±0.3 Unloss O	thenwise Specified				Dimensions <sup>,</sup> Millimetres

Tolerances ±0.3 Unless Otherwise Specified

## Part Number Table

Description	Part Number		
Rocker Switch, SPST, On-Off, Black	MP004574		

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



**Dimensions : Millimetres**