Piezo exit switch

182 TACTILE SWITCHES

186

191 FOOT SWITCHES

193

Product overview

A vandal proof exit switch for users operating in harsh environment, high traffic areas


- Sealed in a rugged, weatherised stainless steel enclosure
- Vandal resistant, tamper resistant, weather and dust resistant to IP68
- Programmable 'door open' time, 'fail secure/fail safe' option selectable
- Green LED 'relay on' and red LED 'relay off' reversible
- 5 year guarantee






SPECIFICATION	
Input voltage	12-24VDC
Switching current	1.5A Max
Actuation force	3-5N
Make impulse time	1 to 60 seconds
Operating temperature	-20°C to 70°C
Storage temperature	-40°C to 85°C
Ingress protection	IP68
Electrical lifetime	15 million operations
Current consumption	40mA idle, 80mA active


PART NO.	ТҮРЕ
CPA-EXIT-SW	Exit switch



Positive 12-24 V DC Negative 12-24 V DC (NO-1) Normally open (COM-1) Common 1 (COM-2) Common 2 (NC-2) Normally closed (GRD) Green/yellow wire for ground

(-)





KEY FEATURES

Anti-vandal design | Multiple function | Reversable LED action

208