

**Section 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier****Product name:** JENOLITE UNIVERSAL ETCH PRIMER**Product code:** 89089 & 89099**1.2. Relevant identified uses of the substance or mixture and uses advised against****1.3. Details of the supplier of the safety data sheet****Company name:** JENOLITE UK LTD

Chater Lea Building

Icknield Way

Letchworth

Hertfordshire

SG6 1WT

England

**Tel:** 01234 924794**Email:** Sales@jenolite.net**1.4. Emergency telephone number****Section 2: Hazards identification****2.1. Classification of the substance or mixture****Classification under CLP:** Eye Irrit. 2: H319; Flam. Aerosol 1: H222; STOT SE 3: H336; -: EUH066; -: EUH208; -: H229**Most important adverse effects:** Repeated exposure may cause skin dryness or cracking. Contains n-(3-(trimethoxysilyl)propyl)ethylenediamine. May produce an allergic reaction. Extremely flammable aerosol. Pressurised container: May burst if heated. Causes serious eye irritation. May cause drowsiness or dizziness.**2.2. Label elements****Label elements:****Hazard statements:** EUH066: Repeated exposure may cause skin dryness or cracking.

EUH208: Contains n-(3-(trimethoxysilyl)propyl)ethylenediamine. May produce an allergic reaction.

H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

# SAFETY DATA SHEET

JENOLITE UNIVERSAL ETCH PRIMER - 89089 NPD9427

Page: 2

**Hazard pictograms:** GHS02: Flame

GHS07: Exclamation mark



**Signal words:** Danger

**Precautionary statements:** P102: Keep out of reach of children.

P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P211: Do not spray on an open flame or other ignition source.

P251: Do not pierce or burn, even after use.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P410+P412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

## 2.3. Other hazards

**Other hazards:** In use, may form flammable / explosive vapour-air mixture.

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

**ACETONE - REACH registered number(s): 01-2119471330-XXXX**

EINECS	CAS	PBT / WEL	CLP Classification	Percent
200-662-2	67-64-1	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	30-50%

#### DIMETHYL ETHER

204-065-8	115-10-6	Substance with a Community workplace exposure limit.	Flam. Gas 1: H220; Press. Gas: H280	30-50%
-----------	----------	--	-------------------------------------	--------

**XYLENE - REACH registered number(s): 01-2119484661-33-0004**

215-535-7	1330-20-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Skin Irrit. 2: H315	1-10%
-----------	-----------	---	--	-------

**1-METHOXY-2-PROPANOL**

203-539-1	107-98-2	-	Flam. Liq. 3: H226; STOT SE 3: H336	1-10%
-----------	----------	---	-------------------------------------	-------

[cont...]

# SAFETY DATA SHEET

JENOLITE UNIVERSAL ETCH PRIMER - 89089 NPD9427

Page: 3

## ISOBUTANOL

201-148-0	78-83-1	-	Flam. Liq. 3: H226; Acute Tox. 4: H302; STOT SE 3: H335; Skin Irrit. 2: H315; Eye Dam. 1: H318; STOT SE 3: H336	1-10%
-----------	---------	---	---	-------

## PHENOL

203-632-7	108-95-2	-	Muta. 2: H341; Acute Tox. 3: H331; Acute Tox. 3: H311; Acute Tox. 3: H301; STOT RE 2: H373; Skin Corr. 1B: H314	<1%
-----------	----------	---	---	-----

## N-(3-(TRIMETHOXYSILYL)PROPYL)ETHYLENEDIAMINE

203-632-7	1760-24-3	-	Eye Dam. 1: H318; Aquatic Chronic 2: H411; Acute Tox. 4: H302; Skin Irrit. 2: H315; Skin Sens. 1: H317; Acute Tox. 4: H332	<1%
-----------	-----------	---	--	-----

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Do not induce vomiting. Wash out mouth with water. Consult a doctor.

**Inhalation:** Move to fresh air in case of accidental inhalation of vapours.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** No data available.

**Eye contact:** No data available.

**Ingestion:** No data available.

**Inhalation:** No data available.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Eye bathing equipment should be available on the premises.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** Extremely flammable. In combustion emits toxic fumes. Forms explosive air-vapour mixture. Vapour may travel considerable distance to source of ignition and flash back.

[cont...]

# SAFETY DATA SHEET

JENOLITE UNIVERSAL ETCH PRIMER - 89089 NPD9427

Page: 4

## 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. Eliminate all sources of ignition. If outside do not approach from downwind.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Do not use equipment in clean-up procedure which may produce sparks. Clean-up should be dealt with only by qualified personnel familiar with the specific substance.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Smoking is forbidden. Use non-sparking tools. Avoid direct contact with the substance.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep away from sources of ignition. Keep container tightly closed. Keep away from direct sunlight.

**Suitable packaging:** Must only be kept in original packaging.

### 7.3. Specific end use(s)

**Specific end use(s):** No data available.

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**ACETONE**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL

[cont...]

## SAFETY DATA SHEET

JENOLITE UNIVERSAL ETCH PRIMER - 89089 NPD9427

Page: 5

UK	500ppm 1210mg/m3	1500ppm 3620mg/m3	-	-
----	------------------	-------------------	---	---

### DIMETHYL ETHER

UK	766 mg/m3	958 mg/m3	-	-
----	-----------	-----------	---	---

### XYLENE

UK	50ppm	100ppm	220mg/m3	441mg/m3
----	-------	--------	----------	----------

### 1-METHOXY-2-PROPANOL

UK	375 mg/m3	560 mg/m3	-	-
----	-----------	-----------	---	---

### ISOBUTANOL

UK	154 mg/m3	231 mg/m3	-	-
----	-----------	-----------	---	---

### PHENOL

UK	2 ppm	4 ppm	-	-
----	-------	-------	---	---

### DNEL/PNEC Values

#### Hazardous ingredients:

#### ACETONE

Type	Exposure	Value	Population	Effect
DNEL	Dermal	186mg/kg/day	Workers	Systemic
DNEL	Inhalation	2420mg/m3	Workers	Local
DNEL	Inhalation	1210mg/m3	Workers	Systemic
DNEL	Oral	62mg/kg/day	Consumers	Systemic
DNEL	Dermal	62mg/m3	Consumers	Systemic
DNEL	Inhalation	200mg/m3	Consumers	Systemic
PNEC	Fresh water	10.6mg/l	-	-
PNEC	Marine water	1.06mg/l	-	-
PNEC	Fresh water	Intermittent release	-	-
PNEC	Fresh water sediments	30.4 mg/kg	-	-
PNEC	Marine sediments	3.04mg/kg	-	-
PNEC	Soil (agricultural)	29.5mg/kg	-	-
PNEC	Microorganisms in sewage treatment	100mg/l	-	-

#### XYLENE

Type	Exposure	Value	Population	Effect
DNEL	Inhalation	289mg/m3	Workers	Systemic
DNEL	Dermal	180mg/m3	Workers	Systemic
DNEL	Inhalation	77mg/m3	Workers	Systemic

[cont...]

# SAFETY DATA SHEET

JENOLITE UNIVERSAL ETCH PRIMER - 89089 NPD9427

Page: 6

DNEL	Inhalation	174mg/m <sup>3</sup>	Consumers	Systemic
DNEL	Dermal	108mg/kg/day	Consumers	Systemic
DNEL	Inhalation	14.8mg/m <sup>3</sup>	Consumers	Systemic

## 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

**Respiratory protection:** Respiratory protection not required.

**Hand protection:** Chemically resistant gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

**Environmental:** Prevent from entering in public sewers or the immediate environment.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Aerosol

**Colour:** Grey

**Odour:** Characteristic odour

**Flash point°C:** <23

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions. Stable at room temperature.

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

### 10.4. Conditions to avoid

**Conditions to avoid:** Direct sunlight. Heat. Hot surfaces. Sources of ignition. Flames.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes.

[cont...]

# SAFETY DATA SHEET

JENOLITE UNIVERSAL ETCH PRIMER - 89089 NPD9427

Page: 7

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

#### Hazardous ingredients:

##### ACETONE

DERMAL	RAT	LD50	>7400	mg/kg
DERMAL	RBT	LD50	2000	mg/kg
ORAL	RAT	LD50	5800	mg/kg
VAPOURS	RAT	4H LC50	76000	mg/l

##### XYLENE

DERMAL	RBT	LD50	>1700	mg/kg
GASES	MUS	1H LC50	5000	ppmV
ORAL	RAT	LD50	4300	mg/kg

##### 1-METHOXY-2-PROPANOL

IVN	RAT	LD50	4200	mg/kg
ORL	MUS	LD50	11700	mg/kg
ORL	RAT	LDLO	3739	mg/kg

##### ISOBUTANOL

IVN	MUS	LD50	417	mg/kg
IVN	RAT	LD50	340	mg/kg
ORL	RAT	LD50	2460	mg/kg

##### PHENOL

ORL	MUS	LD50	270	mg/kg
ORL	RAT	LD50	317	mg/kg
SCU	RAT	LD50	460	mg/kg

#### Relevant hazards for product:

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** No data available.

**Eye contact:** No data available.

**Ingestion:** No data available.

**Inhalation:** No data available.

[cont...]

# SAFETY DATA SHEET

JENOLITE UNIVERSAL ETCH PRIMER - 89089 NPD9427

Page: 8

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

**Other information:** Not applicable.

## Section 12: Ecological information

### 12.1. Toxicity

**Hazardous ingredients:**

#### ACETONE

ALGAE	192H EC10	530	mg/l
Activated Sludge	30m EC10	1000	mg/l
DAPHNIA	48H EC50	8800	mg/l
Daphnia magna	192H EC10	2212	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	5540	mg/l

#### XYLENE

Daphnia magna	48H EC50	<10	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	41	mg/l

### 12.2. Persistence and degradability

**Persistence and degradability:** No data available.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No data available.

### 12.4. Mobility in soil

**Mobility:** No data available.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

### 12.6. Other adverse effects

**Other adverse effects:** No data available.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Recovery operations:** Not applicable.

**Disposal of packaging:** Not applicable.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

[cont...]



# SAFETY DATA SHEET

JENOLITE UNIVERSAL ETCH PRIMER - 89089 NPD9427

Page: 9

## Section 14: Transport information

### 14.1. UN number

UN number: UN1950

### 14.2. UN proper shipping name

### 14.3. Transport hazard class(es)

### 14.4. Packing group

### 14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

### 14.6. Special precautions for user

Special precautions: No special precautions.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

## Section 16: Other information

### Other information

**Other information:** according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

\* indicates text in the SDS which has changed since the last revision.

**Phrases used in s.2 and s.3:** EUH066: Repeated exposure may cause skin dryness or cracking.

EUH208: Contains n-(3-(trimethoxysilyl)propyl)ethylenediamine. May produce an allergic reaction.

H220: Extremely flammable gas.

H222: Extremely flammable aerosol.

H225: Highly flammable liquid and vapour.

H226: Flammable liquid and vapour.

H229: Pressurised container: May burst if heated.

H301: Toxic if swallowed.

H302: Harmful if swallowed.

H311: Toxic in contact with skin.

H312: Harmful in contact with skin.

H314: Causes severe skin burns and eye damage.

[cont...]

## SAFETY DATA SHEET

JENOLITE UNIVERSAL ETCH PRIMER - 89089 NPD9427

Page: 10

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H318: Causes serious eye damage.

H319: Causes serious eye irritation.

H331: Toxic if inhaled.

H332: Harmful if inhaled.

H335: May cause respiratory irritation.

H336: May cause drowsiness or dizziness.

H341: Suspected of causing genetic defects.

H373: May cause damage to organs through prolonged or repeated exposure.

H411: Toxic to aquatic life with long lasting effects.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product. Please note that due to the on-going change in regulation from CHIP to CLP, any MSDS information supplied by LMA is only considered accurate at the time of its creation. During this time classifications of substances may change. Therefore it is possible that can art work and MSDS information may differ. As such if you have any concerns we recommend you request a new MSDS from us every 6-12 months.