

Nylon Cable Ties

pro-POWER

RoHS
Compliant




Features

- Self-locking
- Corrosion resistant
- Well insulation

Specifications

Material : Nylon 66 UL 94V-2
Temperature : -35°C to +85°C

Diagram



Specification Table

Part Number	L (mm)	W (mm)	Max. Bundle Dia. (mm)	Min. Loop Tensile Strength (mm)		Colour	Pack Size
100*1.8BLK	100	1.8	22	14	6.5	Natural	100
100*1.8NAT	100	1.8	22	14	6.5	Natural	100
100X2.50MM NAT.100PK	100	2.5	22	18	8	Natural	100
100X2.5MM BLK 100PK	100	2.5	22	18	8	Natural	100
1020X9MMBLK	1020	9	295	175	80	Natural	100
1020X9MMNAT	1020	9	295	175	80	Natural	100
120X4.6MM BLK 100PK	120	4.6	26	50	22	Black	100
120X4.6MM BLK 1000PK	120	4.6	26	50	22	Black	100
1350X9MMBLK	1350	9	380	175	80	Natural	100
1350X9MMNAT	1350	9	380	175	80	Natural	100
142X2.5MM BLK 100PK	140	2.5	33	18	8	Natural	100
142X2.5MM BLK 1000PK	140	2.5	33	18	8	Natural	100
180X6.8MMBLK	180	6.8	42	85	38	Black	100
180X6.8MMNAT	180	6.8	42	85	38	Black	100
200 X 4.6MM GREY	200	4.6	53	50	22	Natural	100
203X3.6MM NAT 1000PK	200	3.6	53	40	18	Natural	100
203X4.6MM NAT 100PK	200	4.6	53	50	22	Natural	100
PPW01041	200	4.6	53	50	22	Natural	100
250X4.6MMBLK	250	4.6	65	50	22	Black	100
250X7.6MM NAT 100PK	250	7.6	63	120	55	Black	100
292X3.6MM NAT 100PK	300	3.6	80	40	18	Natural	100
300X12.70MMBLK	300	12.7	80	250	114	Natural	100

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

pro-POWER

Nylon Cable Ties



Part Number	L (mm)	W (mm)	Max. Bundle Dia. (mm)	Min. Loop Tensile Strength (mm)		Colour	Pack Size
300X12.70MMNAT	300	12.7	80	250	114	Natural	100
300X7.60MMBLK	300	7.6	80	120	55	Natural	100
350X4.8MMBLK	350	4.8	90	50	22	Natural	1000
350X4.8MMNAT	350	4.8	90	50	22	Natural	1000
370X4.8MM BLK 100PK	380	4.8	105	50	22	Natural	1000
370X4.8MM BLK 1000PK	380	4.8	105	50	22	Natural	1000
400X12.70MMBLK	400	12.7	105	250	114	Black	100
400X4.8MM NAT 100PK	400	4.8	108	50	22	Black	1000
400X7.60MMBLK	400	7.6	105	120	55	Black	100
400X7.60MMNAT	400	7.6	105	120	55	Black	100
450X4.8MMBLK	450	4.8	130	50	22	Natural	1000
450X4.8MMNAT	450	4.8	130	50	22	Natural	1000
450X7.60MMBLK	450	7.6	125	120	55	Natural	100
450X7.60MMNAT	450	7.6	125	120	55	Natural	100
450X9MMBLK	450	9	120	175	80	Natural	100
450X9MMNAT	450	9	120	175	80	Natural	100
500X4.8MM NAT 100PK	500	4.8	150	50	22	Black	1000
500X7.60MMBLK	500	7.6	145	120	55	Black	100
500X7.60MMNAT	500	7.6	145	120	55	Black	100
540X12.70MMBLK	540	12.7	155	250	114	Natural	100
540X12.70MMNAT	540	12.7	155	250	114	Natural	100
650X12MMBLK	650	12	190	250	114	Natural	100
650X12MMNAT	650	12	190	250	114	Natural	100
650X9MMBLK	650	9	190	175	80	Natural	100
650X9MMNAT	650	9	190	175	80	Natural	100
142X2.5MM NAT. 100PK	140	2.5	33	18	8	Natural	100
150X6.8MM NAT 100PK	150	6.8	33	85	38	Black	100
160X4.8MM NAT 1000PK	160	4.8	39	50	22	Natural	1000
200X2.5MM NAT 100PK	200	2.5	53	18	8	Natural	100
200X2.5MM NAT 1000PK	200	2.5	53	18	8	Natural	100
203X3.6MM NAT 100PK	200	3.6	53	40	18	Natural	100
292X3.6MM NAT 1000PK	300	3.6	80	40	18	Natural	100
300X4.6MM NAT 1000PK	300	4.6	82	50	22	Natural	100
370X3.6MM NAT 100PK	370	3.6	102	40	18	Natural	100
370X4.8MM NAT 100PK	380	4.8	105	50	22	Natural	1000
370X4.8MM NAT 1000PK	380	4.8	105	50	22	Natural	1000
370X7.6MM NAT 100PK	370	7.6	98	120	55	Natural	100

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands



Nylon Cable Ties



Part Number	L (mm)	W (mm)	Max. Bundle Dia. (mm)	Min. Loop Tensile Strength (mm)		Colour	Pack Size
142X3.2MM BLK 100PK	150	3.2	35	40	18	Black	100
142X3.2MM BLK 1000PK	150	3.2	35	40	18	Black	100
150X6.8MM BLK 100PK	150	6.8	33	85	38	Black	100
160X4.6MM BLK 100PK	180	4.6	46	50	22	Black	100
160X4.6MM BLK 1000PK	180	4.6	46	50	22	Black	100
200X2.5MM BLK 100PK	200	2.5	53	18	8	Natural	100
200X2.5MM BLK 1000PK	200	2.5	53	18	8	Natural	100
200X6.8MM BLK 100PK	200	6.8	50	85	38	Natural	100
203X3.6MM BLK 100PK	200	3.6	53	40	18	Natural	100
203X4.6MM BLK 100PK	200	4.6	53	50	22	Natural	100
203X4.6MM BLK 1000PK	200	4.6	53	50	22	Natural	100
250X7.6MM BLK 100PK	250	7.6	63	120	55	Black	100
292X3.6MM BLK 100PK	300	3.6	80	40	18	Natural	100
292X3.6MM BLK 1000PK	300	3.6	80	40	18	Natural	100
300X4.6MM BLK 100PK	300	4.6	82	50	22	Natural	100
300X4.6MM BLK 1000PK	300	4.6	82	50	22	Natural	100
370X3.6MM BLK 100PK	370	3.6	102	40	18	Natural	100
370X7.6MM BLK 100PK	370	7.6	98	120	55	Natural	100
400X4.8MM BLK 100PK	400	4.8	108	50	22	Black	1000
500X4.8MM BLK 100PK	500	4.8	150	50	22	Black	1000
100 X 2.50MM RED	100	2.5	22	18	8	Natural	100
200 X 4.60MM RED	200	4.6	53	50	22	Natural	100
300 X 4.60MM RED	300	4.6	82	50	22	Natural	100
200 X 4.6MM GREEN	200	4.6	53	50	22	Natural	100
200 X 4.6MM BLUE	200	4.6	53	50	22	Natural	100
300 X 4.6MM YELL	300	4.6	82	50	22	Natural	100
760X9MMBLK	760	9	225	175	80	Black	100
780X12.70MMBLK	780	12.7	230	250	114	Natural	100
780X12.70MMNAT	780	12.7	230	250	114	Natural	100
920X9MMBLK	920	9	265	175	80	Natural	100
920X9MMNAT	920	9	265	175	80	Natural	100
CBT7726CLR	300	7.6	80	120	55	Natural	100

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands

