

SSBC clamping holder, positive, right

For longitudinal turning with SC indexable insert

ATORN[®]

Application


For longitudinal turning with SC indexable insert, 45°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 75°, tip angle 90°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



Art. no.	17849 133
ISO name	SSBC R/L 2020 K12
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	20 mm
Programming size	17 mm
Suitable for indexable inserts	SC.. 1204..
Tool design	Left

EAN-Code

4050293563207