

3-point Inside micrometer set

Micromar 44 AS




Application:

For measuring through-bores and for blind holes and short centring shoulders.

Version:

- self-centring and self-aligning
- carbide-tipped measuring faces
- brushed chromium-plated operating and display elements
- quick drive with integrated coupling
- from \varnothing 40 mm, aluminium measuring head
- incl. setting rings



Art. no.	31914 530
Min./max. length measuring range	50-100 mm
Measuring depth	79/97 mm
Error limit	5 μ m
Digit increment	0.005 mm
Calibration Group	I
DIN	863

EAN-Code

4059192010829