50mm Compact fan



- With electronic protection against reverse polarity. The fan only operates when the polarity is correct. Impedance-protected against locked rotor and overloading.
- Fan of fibreglass reinforced plastic. PBT housing, PA impeller.
- Air exhaust over strust. Rotational direction CCW looking at rotor.
- Fitted with 3 pin molex connector (22-01-2035)
- Sensor signal for speed monitoring

Nominal data	Air flow @ free air	Air flow @ free air	Nominal voltage	Voltage range	Sound pressure level	Sintec sleeve bearings	Power input	Nominal speed	Temperature range	L ¹⁰ Service life @ 20°C / @ 60°C	
Туре	m ³ /h	CFM	VDC	VDC	dB(A)		Watt	min ⁻¹	oC.	Hours/Hours	
E10E/0 E21	20	11.0	10	10.0 10.0	20	Vac	1.0	5 000	20 . 70	E0 000 / 20 000	
512F/2-531	20	11.8	12	10.8 13.2	30	Yes	1.0	5,000	-20 +70	50,000 / 20,000	

subject to alterations

Dimensions



