

Pt100 - Pipe sensor

with hook-and-loop fastener



Application:

The pipe sensor is suitable for the fast and precise measurement of surface temperatures on pipes with a diameter of 6 to 120 mm.

Version:

- Sensor type: Pt100
- Measuring range: -50 to +120°C
- Accuracy: Class B in accordance with EN 60751
- Response time: 60 s
- Hook-and-loop fastener length 420 mm with attached Pt100 sensor
- Hook-and-loop width: 20 mm

Art. no.	46108 065
Sensor type	Pt100
Probe type	Surface probe
Probe designation	Tube contact sensor
Min./max. temperature measuring range	-50 to 120 °C
Accuracy temperature	Class B according to EN 60584-2
Response time sensor	60 s
Cable length	2.9 m
Velcro width	20 mm
Velcro length	420 mm
EN standard	60751



EAN-Code

4029547010224