


Part Number: MRG5800



COAX RF RG58 PVC

Product Description

COAX RF [0.9/2.95] RG58 STRANDED PVC

Technical Specifications

Product Overview

| Environmental Space: | Indoor - Euroclass Eca |
|------------------------|---|
| Suitable Applications: | Coaxial communication cable based on MIL-C-17 |

Physical Characteristics (Overall)

Conductor

| Stranding | Material | Constructi | on n x D | Diameter +/- Tolerance | No. of Coax |
|----------------------------------|--------------------|------------|----------|------------------------|-------------|
| Stranded | TC - Tinned Copper | 19x0.18 mr | n | 0.02 mm | 1 |
| Conductor Count: Conductor Size: | | 1 | | | |
| | | 21 AWG | | | |

Insulation

| Type | Material | Nominal Diameter | Diameter +/- Tolerance |
|------------|--------------|------------------|------------------------|
| Dielectric | Polyethylene | 2.95 mm | 0.15 mm |

Outer Shield Material

| Type | Material | Coverage [%] | Nominal Diameter | Diameter +/- Tolerance | Coverage +/- Tolerance |
|-------|-----------------------|--------------|------------------|------------------------|------------------------|
| Braid | TC - Tinned Copper | 93 % | 3.5 mm | 0.2 mm | 4 % |

Outer Jacket Material

| Material | Nominal Diameter | Diameter +/- Tolerance |
|--------------------------|------------------|--------------------------|
| PVC - Polyvinyl Chloride | 4.95 mm | 0.2 mm |
| OuterJacket1, Table Note |) : | According to EN 50290-2- |

Construction and Dimensions

| Min Elongation at Breakof Jacket: | 150 % |
|-----------------------------------|----------|
| Min Tensile Strength of Jacket: | 12.5 MPa |

Electrical Characteristics

Conductor DCR

Max. Conductor DCR 40.6 Ohm/km

Capacitance

| Nom. Capacitance | Capacitance Tolerance |
|------------------|-----------------------|
| 100 pF/m | 2 pF/m |
| Shielding: | |

Impedance

| Nominal Characteristic Impedance | Nominal Characteristic Tolerance | Regularity of Impedance |
|----------------------------------|----------------------------------|-------------------------|
| 50 Ohm | 2 Ohm | Min. 40 dB |

High Frequency (Nominal/Typical)

| Frequency [MHz] | Nom. Insertion Loss |
|-----------------|---------------------|
| 10 MHz | 4.7 dB/100m |
| 200 MHz | 23 dB/100m |
| 400 MHz | 34 dB/100m |
| 1000 MHz | 60 dB/100m |

Delay

Nominal Velocity of Propagation (VP) [%] 66 %

High Freq

| Frequency [MHz] | Min. RL (Return Loss) [dB] |
|-----------------|----------------------------|
| 5 - 30 MHz | 20 dB |
| 30 - 470 MHz | 20 dB |
| 470 - 1000 MHz | 18 dB |

High Freq Table Note: In each frequency band, 3 peak values up to 4 dB lower are allowed

Voltage

Voltage Rating [V] 4000 DC / 2000 V RMS

Temperature Range

| Installation Temp Range: | -5°C To +50°C |
|--------------------------|----------------|
| Storage Temp Range: | -40°C To +70°C |
| Operating Temp Range: | -40°C To +70°C |

Mechanical Characteristics

| Min Bend Radius (W/o Pulling Strength): | 25 mm |
|---|--------------------------|
| Crush Resistance: | Max. 1% (load of 700N) N |

Standards

| CPR Euroclass: | Eca |
|---------------------|----------------------------|
| CENELEC Compliance: | EN 50290-2-20 and EN 50289 |
| RG Type: | 58/U Type |
| MIL Spec Rating: | MIL-C-17 |
| RG / Series Type: | 58/U Type |

Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd): 1998-01-01

Part Number

Variants

| Item # | Color |
|----------------|-------|
| MRG5800.00500 | Black |
| MRG5800.00B200 | Black |
| MRG5800.01500 | Black |
| MRG5800.10100 | Black |
| MRG5800.02500 | White |
| MRG5800.12100 | White |

History

Revision Number: 6

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.