

5050935-2 ✓ ACTIVE


TE Internal #: 5050935-2

Pin Sockets, Socket Length .168 in [4.27 mm], Hole Size (Recommended) 1.04 mm [.041 in], None, Closed Bottom, 28 – 25AWG Wire Size

[View on TE.com >](#)



Connectors > Socket Connectors > Pin Sockets > Mini Spring Sockets: Closed Bottom, 3A



Socket Length: 4.27 mm [.168 in]

Hole Size (Recommended): 1.04 mm [.041 in]

Solder Process Feature: None

Socket Sleeve Style: Closed Bottom

Wire Size: 28 – 25 AWG

[All Mini Spring Sockets: Closed Bottom, 3A \(12\)](#)

Features

Product Type Features

Socket Sleeve Style	Closed Bottom
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Wire/Cable Type	Discrete Wire
Profile	Zero
Product Type	Contact

Body Features

Sleeve Material	Copper
Sleeve Plating Material	Tin

Contact Features

Contact Spring Plating Material	Tin
Contact Spring Plating Thickness	2.54 µm[30 µin]



Contact Base Material	Beryllium Copper
Contact Current Rating (Max)	3 A
Socket Type	Discrete
Contact Transmits (Typical)	Signal (Data)/Power
Contact Mating Area Plating Thickness	2.54 μ m
Contact Type	Socket

Termination Features

Insertion Method	Hand/Semi-Automatic
Termination Method to Printed Circuit Board	Through Hole - Press-Fit
Termination Method to Wire & Cable	Solder

Dimensions

Socket Length	4.27 mm [.168 in]
Hole Size (Recommended)	1.04 mm [.041 in]
Wire Size	.081 – .162 mm ²
Mating Pin Diameter Range	.33 – .51 mm [.013 – .02 in]
PCB Thickness (Recommended)	.79 – 3.18 mm [.031 – .125 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C [-85 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Solder Process Feature	None
Circuit Application	Power & Signal

Packaging Features

Packaging Quantity	2000
Packaging Method	Bag, Loose Piece

Other

Spring Material	Beryllium Copper
-----------------	------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)

Candidate List Declared Against: JAN 2021 (211)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-377-MSSCB3
Mini Spring Sockets: Closed Bottom, 3A




TE Part # 50935-6
SOCKET,MIN-SPR AU-AU SER-1

Customers Also Bought



TE Part #147444-1
Mini Spring Sockets: Closed Bottom, 3A



TE Part #1586039-4
4P VAL-U-LOK VRT HDR W/P V2



TE Part #1-1614884-5
CPF 0805 8R2 0.1% 25PPM 1K RL




TE Part #1-2176092-4
RP 2A 0.25W 909R 0.1% 25PPM 1K RL



TE Part #1437664-4
NC6-P107-02=NC6 ASSEMBLY



TE Part #103747-3
03 MODII HDR SRST B/A .100CL




TE Part #1623746-1
ER74 100R 5% AMMO PK



TE Part #1059684-1
OSP PRINTED CIRCUIT BOARD PLUG
RECEPT



TE Part #1059919-1
4763 0000 00



TE Part #91002-1
TOOL SMALL WIRE INS

Documents

Product Drawings

[SOCKET,MIN-SPR SN-SN SER-1](#)

English

CAD Files

Customer View Model

[ENG_CVM_5050935-2_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_5050935-2_O.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_5050935-2_O.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[MD_5050935-2_04232018124_dmtec](#)

English

[MD_5050935-2_04232018124_dmtec](#)

English

5050935-2

Pin Sockets, Socket Length .168 in [4.27 mm], Hole Size (Recommended) 1.04 mm [.041 in], None, Closed Bottom, 28 – 25AWG Wire Size

