








Pushbutton, classic, flat, maintained, 1 N/C, black, cable (black) with non-terminated end, 4 pole, 3.5 m

Part no. C22-DR-S-K01-P65
Catalog No. 185627

Delivery program



| | | | |
|---|--|----|--|
| Product range | | | RMQ compact solution |
| Basic function | | | Pushbutton actuators |
| Single unit/Complete unit | | | Complete unit |
| Design | | | Flat maintained |
| Connection type | | | Cable (black) with non-terminated end, 4 pole |
| Cable Length | | m | 3.5 |
| Button plate | | | |
| button plate | | | black |
| Button plate | | |  |
| | | | Blank |
| Name | | | None |
| Degree of Protection | | | IP66, IP67, IP69 (frontseitig) IP65 (on rear) |
| Front ring | | | Bezel: titanium |
| Connection to SmartWire-DT | | | no |
| Contacts | | | |
| N/C = Normally closed | | | 1 NC  |
| Notes | | |  = safety function, by positive opening to IEC/EN 60947-5-1 |
| Actuator travel and actuation force as per DIN EN 60947-5-1, K.5.4.1 | | | |
| | | mm | 4.65 |
| Maximum travel | | mm | 5.7 |
| Minimum force for positive opening | | N | 15 |
| Contact sequence | | | <p>BN</p>  <p>BK</p> |

Contact travel  = Contact closed  = Contact open

| | | |
|-----------------------|---|-------------|
| Contact diagram |  | Zw = 4.5 mm |
| Positive opening (ZW) | yes | |

Technical data


General

| | | | |
|---|--------------|--|--|
| Standards | | | IEC/EN 60947-5-1 VDE 0660 |
| Certifications | | | CE, UL, CSA |
| Operating frequency | Operations/h | |  3600 |
| Actuating force | n | |  5 |
| Tightening torque Threaded ring | Nm | | 2 |
| Climatic proofing | | | Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30 |
| Degree of Protection | | | IP66, IP67, IP69 (frontseitig) IP65 (on rear) |
| Mounting position | | | As required |
| Mechanical shock resistance, shock duration 11 ms | g | | > 30 |

Contacts

| | | | |
|---|-----------|------|--|
| Rated impulse withstand voltage | U_{imp} | V AC | 4000 |
| Rated insulation voltage | U_i | V | 250 |
| Overvoltage category/pollution degree | | | III/3 |
| Control circuit reliability | | | |
| At 17 V DC/7 mA | H_F | | N/C contact: statistically determined 1 failure per 0.9×10^6 Operations |
| Max. short-circuit protective device | | | |
| Fuse | gG/gL | A | 4 |
| Rated conditional short-circuit current | I_q | kA | 1 |

Switching capacity

| | | | |
|---------------------------|---|----|----------------|
| Rated operational current | I_e | A | |
| AC-15 | | | |
| 24 V | I_e | A | 4 |
| DC-13 | | | |
| 24 V | I_e | A | 3 |
| Cable characteristics | | | |
| Design | | | Cable end open |
| Cable Length | | m | 3.5 |
| Material characteristic | | | PUR |
| Diameter |  | mm | 4.7 |

Design verification as per IEC/EN 61439

| | | | |
|--|--|----|-----|
| Technical data for design verification | | | |
| Operating ambient temperature max. | | °C | -25 |
| Operating ambient temperature max. | | °C | 70 |

Technical data ETIM 6.0

| | | | |
|--|--|----|-------|
| Low-voltage industrial components (EG000017) / Push button, complete (EC001028) | | | |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Push-button actuator, complete unit (ecl@ss8.1-27-37-12-28 [AKF046011]) | | | |
| Number of command positions | | | 1 |
| Colour button | | | Black |
| Construction type lens | | | Round |
| Hole diameter | | mm | 22 |
| Width opening | | mm | 0 |

| | | |
|---|----|---------|
| Height meter opening | mm | 0 |
| Degree of protection (IP) | | - |
| Type of button | | Flat |
| Suitable for illumination | | No |
| Switching function latching | | Yes |
| Spring-return | | No |
| Supply voltage lamp | V | 0 |
| Number of contacts as normally open contact | | 0 |
| Number of contacts as normally closed contact | | 1 |
| Number of contacts as change-over contact | | 0 |
| Type of electric connection | | - |
| With front ring | | Yes |
| Material front ring | | Plastic |
| Colour front ring | | Grey |

Dimensions

