

## 4412HL.B




### Models Versions

4412HL.B	black w/foam
4412HL.BE	black empty
4412HL.O	orange w/foam
4412HL.OE	orange empty
4412HL.G	mil. green w/foam
4412HL.GE	mil. green empty
4412HL.D	des. sand w/foam
4412HL.DE	des. sand empty
4412HL.N	blue navy w/foam
4412HL.NE	blue navy empty
4412HL.Y	yellow w/foam
4412HL.YE	yellow empty
4412HL.BC	black w/pc bag
4412HL.GC	mil. green w/pc bag

Medium size watertight case, injected with proprietary copolymer PP that makes it more resistant and lightweight than other similar products. IP67 and MIL Stan certified to be resistant to impact, liquids, shocks. Ideal container for mechanical equipment, optical equipment and electronic devices, valuables, emergency kits and more. Can be used as a portable work station.

- Metal reinforced padlock holes
- Single block high performance injected O-ring
- Automatic pressure valve
- Soft rubber handle grip
- Removable lid
- Anti-tilt support
- Certified to grant constant performances between -33°C and +90 °C.
- Six standard colors available

Technical Features		L	W	D		
		Length	Width	Depth	Lid	Base
Internal dim.	mm	445	345	125	47	78
External dim.	mm	485	414	149		
Weight empty		Kg 2,67				
Weight w/foam		Kg 3,17				
Weight w/pc bag		Kg 3,47				
Volume		lt 19,2				
Buoyancy		Kg/max 10,8				
Temp. rating		°C min -33 max +90				



Certifications	* Designed to comply with:
	2002/95/EC Conformity with the Directive 2002/95/EC
	DEF STAN 81-41 (level J)
	IP67 Dustproof - Waterproof
	STANAG 4280 (edition 2)

\* Pending certification release